



Pliers & Cutting Tools

CoBolt® Compact Bolt Cutters

The KNIPEX CoBolt® delivers full bolt-cutting capability in a compact, pliers-sized form factor — purpose-built for cutting bolts, nails, rivets, and wire in tight spaces where a standard bolt cutter won't fit. Lever action cutting geometry multiplies hand force at the cutting edges, and induction-hardened centered cutting edges maintain their performance through repeated use on hard materials. Available in three sizes from 6.3in to 10in, chrome vanadium heavy-duty steel, forged and oil-hardened.

Features

- Compact pliers-sized form factor for access in confined spaces
- Lever action cutting geometry multiplies hand force at the cutting edges
- Induction-hardened centered cutting edges
- Cuts bolts, nails, rivets, and wire
- Chrome vanadium heavy-duty steel, forged and oil-hardened



CoBolt® Compact Bolt Cutters

Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Jaw Width	Price
<u>7101160SBA</u>		6.3in [159mm]	1.25in [31.8mm]	13/64in soft wire 11/64in medium wire 1/8in hard wire	0.55in [14.0mm]	0.55in [14.0mm]	\$59.00
<u>7101200SBA</u>		8.0in [203mm]	1.4in [35.6mm]	1/4in soft wire 13/64in medium wire 5/32in hard wire	0.75in [19.1mm]	0.75in [19.1mm]	\$78.00
<u>7101250SBA</u>		10.0in [254mm]	1.5in [38.1mm]	7/32in medium wire 5/32in hard wire	0.79in [20.0mm]	0.79in [20.0mm]	\$91.00

CoBolt® Compact Bolt Cutters Sets

Part Number	Part Image	Number of Pieces	Set Includes	Price
<u>002005US2</u>		3	(3) compact bolt cutters (6 1/4in, 8in, 10in)	\$202.00