

KNIPEX® Wire Stripping and Dismantling Tools

Electrician's Pliers

Features

- Designed for gripping and bending wire
- Ideal for cutting soft, medium, and hard wire
- Precision cutting edges induction-hardened to 60 HRC
- Vanadium electric steel; oil-hardened, and tempered





1301160



1301614SBA

Wire Stripping and Dismantling Tools								
Part Number	Description	Stripping Capacity	Cutting Capacity Ø		Length	Weight	Pcs/Pkg	Price
			Med-Hard	Hard				
1301160	4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping	20-18/ 15 / 13 AWG [0.5-0.75 / 1.5 / 2.5 mm ²]	0.10 in [2.5 mm]	0.06 in [1.6 mm]	6.30 in [160 mm]	3.95 oz [112 g]	1	\$43.50
1301614SBA	4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping	14, 12, 10 AWG [2.1 / 3.3 / 5.3 mm ²]	0.10 in [2.5 mm]	0.06 in [1.6 mm]	6.30 in [160 mm]	3.95 oz [112 g]	1	\$38.50

Inch dimensions are rounded to the nearest hundredth. HRC refers to Rockwell C Scale.



Wire Stripping Tools

Cable Stripping Tool Features

- Designed to dismantle round PVC, rubber, silicone, PTFE cables
- Self-cocking holding lever
- Replaceable blade
- Plastic housing; impact-resistant

Data Cable Stripping Tool Features

- Designed to strip UTP and STP data cables
- Double shell, folding back stripping tool
- Opening spring and locking lever
- Practical clip for safe transport
- Plastic housing; fiberglass-reinforced

Wire Stripping and Dismantling Tools							
Part Number	Description	Stripping Capacity Ø	Stripping Capacity Cross Section	Length	Weight	Pcs/Pkg	Price
1630135SB	Shock-resistant cable stripping tool, plastic body	0.24 - 1.14 in [6.0 - 29.0 mm]	N/A	5.31 in [135 mm]	4.23 oz [120 g]	1	\$71.00
1639135	Spare blade for 1630135SB	N/A	N/A	N/A	0.39 oz [11 g]	1	\$20.00
1665125SB	Data cable stripper, Cat 5, Cat 6, Cat 7, Twisted-Pair (UTP/STP)	0.18 - 0.39 in [4.5 - 10.0 mm]	24 - 11 AWG [0.2 - 4.0 mm ²]	4.92 in [125 mm]	1.76 oz [50 g]	1	\$55.00

Inch dimensions are rounded to the nearest hundredth.



1630135SB



1665125SB