



Pliers & Cutting Tools

Hose Cutters

KNIPEX Hose Cutters deliver clean, precise cuts on pneumatic tubing and flexible hose without deforming the cut end. Both models use a spring-return single-acting mechanism and feature replaceable cutting blades for extended service life. The Pneumatic Hose Cutter handles multilayer and pneumatic hoses up to 3/4in OD; the PlastiCut® handles thin-walled pipe and flexible hose up to 1in OD. Vanadium steel,

Features

- Spring-return single-acting cutting mechanism
- Replaceable cutting blades for extended service life
- Clean cuts without deforming the hose end
- Compatible with multilayer, pneumatic, and flexible hose types

Hose Clamp Crimping Tools

KNIPEX Ear Clamp Pliers crimp 1-ear and 2-ear hose clamps in a single squeeze. The slim head profile reaches into confined engine bays and equipment enclosures where standard crimping tools won't fit. The 1099i220SBA adds a side jaw for crimping at 90° — useful where straight-on access isn't possible. High-grade special tool steel, forged and oil-hardened.

Features

- Crimps 1-ear and 2-ear hose clamps
- Slim head for access in confined spaces
- High-grade special tool steel, forged and oil-hardened
- Plastic coated handles

Hose Cutters					
Part Number	Part Image	Blade Type	Overall Length	For Use On	Price
<u>9010185</u>		Straight	7.3in	Multilayer and pneumatic hoses up to 3/4in (19mm) outside diameter	\$86.00
<u>9020185</u>		Trapezoidal	7.3in	Thin walled pipes and flexible hoses up to 1in (25.4mm) outside diameter	\$75.00

Hose Clamp Crimping Tools								
Part Number	Part Image	Overall Length	Jaw Opening	Jaw Thickness	Jaw Width	Jaw Length	Jaw Profile	Price
<u>1098i220SBA</u>		8.8in [223mm]	0.96in [24.4mm]	0.80in [20.4mm]	0.80in [20.4mm]	0.7in [17.7mm]		\$27.50
<u>1099i220SBA</u>		8.8in [223mm]	0.96in [24.4mm]	0.80in [20.4mm]	0.80in [20.4mm]	0.7in [17.7mm]		\$35.50