



Pliers & Cutting Tools

Lineman's Pliers

KNIPEX High Leverage Lineman's Pliers are built around the New England head profile preferred by U.S. electricians — a compact, boxy jaw that reaches into panel knockouts and conduit boxes where longer-nosed pliers won't fit. High-leverage joint geometry reduces cutting force compared to standard lineman's pliers, and precision machined hardened cutting edges handle hard and medium wire cleanly. Available with standard, tether-compatible, and VDE 1000V-rated handle options, with two models adding an integrated fish tape puller and crimper for single-tool versatility on rough-in work. Vanadium steel, forged and multi-stage oil-hardened, DIN ISO 5746 and ASME B107.20 compliant.

Features

- New England head profile for access in panels and conduit boxes
- High-leverage joint geometry reduces cutting force vs. standard lineman's pliers
- Precision machined hardened cutting edges for hard and medium wire
- Vanadium steel, forged and multi-stage oil-hardened
- DIN ISO 5746 and ASME B107.20 compliant
- Tether-compatible handle options available for work-at-height applications
- VDE 1000V-rated insulated handle option available for live electrical work



Lineman's Pliers										
Part Number	Part Image	Handle Type	Application	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Jaw Width	Insulation Rating	Price
<u>0901240SBA</u>		Plastic coated handles	Gripping wire cutting	9.5in [241mm]	1.80in [45.8mm]	1/8in hard wire 3/16in medium wire	0.59in [15.0mm]	0.59in [15.0mm]	N/A	\$53.00
<u>0902240SBA</u>		KNIPEXTEND comfort handle	Gripping wire cutting	9.5in [241mm]	1.80in [45.8mm]	1/8in hard wire 3/16in medium wire	0.59in [15.0mm]	0.59in [15.0mm]	N/A	\$62.00
<u>0908240SBA*</u>		Insulated cushion grip handles	Gripping wire cutting	9.5in [241mm]	1.80in [45.8mm]	1/8in hard wire 3/16in medium wire	0.59in [15.0mm]	0.59in [15.0mm]	1000V	\$75.00
<u>0911240</u>		Plastic coated handles	Gripping wire cutting fish tape pulling crimping	9.5in [241mm]	1.80in [45.8mm]	1/8in hard wire 3/16in medium wire	0.59in [15.0mm]	0.59in [15.0mm]	N/A	\$67.00
<u>0912240SBA</u>		KNIPEXTEND comfort handle	Gripping wire cutting fish tape pulling crimping	9.5in [241mm]	1.80in [45.8mm]	1/8in hard wire 3/16in medium wire	0.59in [15.0mm]	0.59in [15.0mm]	N/A	\$73.00

* ASTM F1505-tested