

# KNIPEX® Water Pump Pliers

## Alligator® Pliers

### Features

- Can be used for outdoor work environments
- High stability box joint design
- Self-locking on pipes and nuts, no slipping
- Guard prevent finger pinching
- Thin V-jaw profile
- Chrome vanadium electric steel; oil-hardened and tempered
- Hardness of 61 approximately HRC



**8801300SBA**

Alligator® Pliers								
Part Number	Description	Pliers Length	Max Jaw Capacity		Adjustment Positions	Weight	Pcs/Pkg	Price
			Pipe	Nut				
<b>8801300SBA</b>	Alligator® pliers with non-slip plastic-coated handles	11.81 in [300 mm]	2.76 in [70 mm]	2.36 in [60 mm]	9	18.02 oz [511 g]	1	\$43.00

*Inch dimensions are rounded to the nearest hundredth. HRC refers to Rockwell C Scale.*



Wire Classes			
Wire Type	Examples	Tensile Strength	
		lb/in <sup>2</sup>	N/mm <sup>2</sup>
Soft wire	Copper, plastics	31,908	220
Medium-hard	Nail, wire pin	108,778	750
Hard	Wire rope strand, steel wire	261,067	1800
Piano wire	Spring steel wire	333,586	2300

# KNIPEX® Water Pump Pliers

## Raptor™ Pliers - Multiple Slip Joint Spanner

### Features

- Smooth parrot jaw design for metric and imperial nuts and screws
- Self-locking from 17 mm to 32 mm
- Zero backlash gripping of metric or imperial hexagonal head screws
- Secure and tight grabbing of bolt heads, even those with rounded edges, rusted nuts or heavily coated workpieces
- Chrome vanadium electric steel, oil-hardened and tempered

Multiple Slip Joint Spanner							
Part Number	Description	Pliers Length	Jaw Opening	Adjustment Positions	Weight	Pcs/Pkg	Price
8741250SBA	Raptor™ pliers - multiple slip joint spanner with non-slip plastic-coated handles	9.84 in [250 mm]	0.39-1.26 in [10-32 mm]	15	11.57 oz [328 g]	1	\$41.00

*Inch dimensions are rounded to the nearest hundredth.*



**8741250SBA**



# KNIPEX® Pliers Sets and Accessories

## KNIPEX® Pliers Sets and Accessories

Pliers Sets and Accessories				
Part Number	Description	Weight	Pcs/ Pkg	Price
<b>001101</b>	Twin universal control cabinet key. Two 4-way wheel wrenches connected in a space-saving way with magnets. Includes lock profiles: square (5-6, 7-8, 9-10, 11mm), triangular (7, 8-9, 10-11, 12mm), double-bit (3-5mm), half-moon (6mm), stepped square (6-9mm), reversing bit (slot 1x7mm, cross-recess PH2). Die-cast zinc material.	0.31 lb [140 g]	1	\$52.00



**001101**