



Pliers & Cutting Tools

Pliers Wrench

The KNIPEX Pliers Wrench combines the adjustability of pliers with the jaw geometry of an open-end wrench — parallel smooth jaws that grip fasteners without rounding and without marring polished or soft surfaces. Push-button adjustment sets the jaw directly on the workpiece across inch and metric sizes, effectively replacing a full set of open-end wrenches with a single tool. Available from the pocket-sized XS (4") through 12", with adjustment positions ranging from 10 to 24 per model. Chrome vanadium electric steel, forged and oil-hardened.



Features

- Parallel smooth jaws grip fasteners without rounding or marring
- Works on all inch and metric hex sizes within capacity range
- Push-button adjustment sets jaw directly on the workpiece
- No jaw angle — parallel contact on fastener flats regardless of jaw opening
- Chrome vanadium electric steel, forged and oil-hardened
- XS model: pocket-sized for EDC use

Pliers Wrenches							
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Jaw Width	Price
<u>8604100SBA</u>		4.0in [102mm]	0.69in [17.5mm]	3/4in hex	0.19in [4.8mm]	0.19in [4.8mm]	\$57.00
<u>8603150SBA</u>		6.0in [152mm]	0.85in [21.6mm]	1in hex	0.20in [5.0mm]	0.20in [5.0mm]	\$71.00
<u>8603180SBA</u>		7.3in [184mm]	1.0in [25.4mm]	1-1/2in hex	0.31in [8.0mm]	0.31in [8.0mm]	\$68.00
<u>8603250SBA</u>		10.0in [254mm]	1.28in [32.5mm]	2in hex	0.34in [8.6mm]	0.34in [8.6mm]	\$79.00
<u>8603300SBA</u>		12.0in [305mm]	1.53in [38.9mm]	2-1/2in hex	0.56in [14.2mm]	0.56in [14.2mm]	\$101.00

Pliers Wrenches Sets				
Part Number	Part Image	Number of Pieces	Set Includes	Price
<u>002006US2</u>		3	(3) adjustable push button pliers wrenches (7-1/4in, 10in, 12in), plastic tray with custom molded tool cavities	\$232.00