



Pliers & Cutting Tools

TwinGrip® Pliers

The KNIPEX TwinGrip® is the only adjustable pliers that grips from both the front and the side — giving technicians a reliable hold on round, square, hex, and flat workpieces, including stripped screws and bolts that defeat conventional pliers. A push-button adjustment mechanism locks the jaw in position the moment it's set, and the slim head profile reaches into confined spaces where bulkier pliers can't follow. Three-point contact on the front jaw ensures flat workpieces are held securely without rocking. Available in 6in, 8in, and 10in sizes.

Features

- Front and side gripping capability in a single tool
- Three-point contact system for secure grip on flat workpieces
- Push-button adjustment locks in place; slim head for confined spaces
- Hardened teeth on both front and side jaws (approx. 61 HRC)
- Pinch guard protects fingers and hands
- Box-joint design for high stability under load
- Non-slip plastic coated handles
- High-grade chrome vanadium electric steel



TwinGrip® Pliers							
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Jaw Width	Price
<u>8201150SBA</u>		6.0in [152mm]	0.70in [17.8mm]	1/8–5/8in (3.0–16.0mm)	0.37in [9.5mm]	0.37in [9.5mm]	\$36.00
<u>8201200SBA</u>		8.0in [203mm]	1.56in [39.5mm]	5/32–7/8in (4.0–22.0mm)	0.47in [11.9mm]	0.47in [11.9mm]	\$42.50
<u>8201250SBA</u>		10.0in [254mm]	1.19in [30.1mm]	3/16 to 1-1/16in (5.0–27.0mm)	0.47in [11.9mm]	0.47in [11.9mm]	\$53.00

TwinGrip® Pliers Sets				
Part Number	Part Image	Number of Pieces	Set Includes	Price
<u>002006US4</u>		3	(3) TwinGrip slip-joint push button pliers (6in, 8in, 10in)	\$121.00