

KONNECT-IT® Cross Reference



Allen-Bradley®

The following is a list of comparable products. To obtain our high-quality KONNECT-IT terminal blocks, simply find the corresponding part number of the unit you currently use. These are approximate replacements based on UL wire size, ampacity and voltage. Please consult the technical section for specifications to determine suitability for your application. Physical size varies from manufacturer to manufacturer.

| Allen-Bradley | KONNECT-IT |
|---------------|------------|
| 1492-J3 | KN-T12GRY |
| 1492-J3-B | KN-T12BLU |
| 1492-J3-BL | KN-T12BLK |
| 1492-J3-BR | KN-T12BRN |
| 1492-J3-G | KN-T12GRN |
| 1492-J3-OR | KN-T12ORG |
| 1492-J3-RE | KN-T12RED |
| 1492-J3-W | KN-T12WHT |
| 1492-J3-Y | KN-T12YEL |
| 1492-J4 | KN-T10GRY |
| 1492-J4-B | KN-T10BLU |
| 1492-J4-BL | KN-T10BLK |
| 1492-J4-BR | KN-T10BRN |
| 1492-J4-G | KN-T10GRN |
| 1492-J4-OR | KN-T10ORG |
| 1492-J4-RE | KN-T10RED |
| 1492-J4-W | KN-T10WHT |
| 1492-J4-Y | KN-T10YEL |
| 1492-J6 | KN-T8GRY |
| 1492-J6-B | KN-T8BLU |
| 1492-J6-BL | KN-T8BLK |
| 1492-J6-BR | KN-T8BRN |
| 1492-J6-G | KN-T8GRN |
| 1492-J6-OR | KN-T8ORG |
| 1492-J6-RE | KN-T8RED |
| 1492-J6-W | KN-T8WHT |
| 1492-J6-Y | KN-T8YEL |
| 1492-J10 | KN-T6GRY |
| 1492-J10-B | KN-T6BLU |
| 1492-J10-BL | KN-T6BLK |
| 1492-J10-BR | KN-T6BRN |
| 1492-J10-G | KN-T6GRN |
| 1492-J10-OR | KN-T6ORG |
| 1492-J10-RE | KN-T6RED |
| 1492-J10-W | KN-T6WHT |
| 1492-J10-Y | KN-T6YEL |

| Allen-Bradley | KONNECT-IT |
|---------------|------------|
| 1492-J16 | KN-T4GRY |
| 1492-J16-B | KN-T4BLU |
| 1492-J35 | KN-T2GRY |
| 1492-J35-B | KN-T2BLU |
| 1492-J50 | KN-T1/0GRY |
| 1492-J50-B | KN-T1/0BLU |
| 1492-J70 | KN-T2/0GRY |
| 1492-J70-B | KN-T2/0BLU |
| 1492-JD3 | KN-D12GRY |
| 1492-JD3-B | KN-D12BLU |
| 1492-JD3C | KN-D12X |
| 1492-JD3DR | KN-D12DR1 |
| 1492-JD4 | KN-D10GRY |
| 1492-JD4-B | KN-D10BLU |
| 1492-JD4C | KN-D10X |
| 1492-WTF3 | KN-TL14 |
| 1492-WTS3 | KN-TL14S |
| 1492-JT3M | KN-TG12 |
| 1492-J2Q | KN-T12SP4 |
| 1492-WM3 | KN-M12GRY |
| 1492-WM3-B | KN-M12BLU |
| 1492-WM4 | KN-M10GRY |
| 1492-WM4-B | KN-M10BLU |
| 1492-JG3 | KN-G10 |
| 1492-JG4 | KN-G10 |
| 1492-JG6 | KN-G8 |
| 1492-JG10 | KN-G8 |
| 1492-JG16 | KN-G4 |
| 1492-JG35 | KN-G2 |
| 1492-JG50 | KN-G1/0 |
| 1492-JG2Q | KN-G12SP4 |
| 1492-WMG3 | KN-MG12 |
| 1492-WMG4 | KN-MG10 |
| 1492-WFB4 | KN-F10 |
| 1492-JD3FB | KN-F10SP |

KONNECT-IT® Cross Reference



DINnectors®

The following is a list of comparable products. To obtain our high-quality KONNECT-IT terminal blocks, simply find the corresponding part number of the unit you currently use. These are approximate replacements based on UL wire size, ampacity and voltage. Please consult the technical section for specifications to determine suitability for your application. Physical size varies from manufacturer to manufacturer.

| DINnectors | KONNECT-IT |
|-------------|------------|
| DN-T12-A | KN-T12GRY |
| DN-T12B-A | KN-T12BLU |
| DN-T12BLK-A | KN-T12BLK |
| DN-T12BR-A | KN-T12BRN |
| DN-T12GRN-A | KN-T12GRN |
| DN-T12ORG-A | KN-T12ORG |
| DN-T12RED-A | KN-T12RED |
| DN-T12W-A | KN-T12WHT |
| DN-T12YEL-A | KN-T12YEL |
| DN-T10-A | KN-T10GRY |
| DN-T10B-A | KN-T10BLU |
| DN-T10BLK-A | KN-T10BLK |
| DN-T10BR-A | KN-T10BRN |
| DN-T10GRN-A | KN-T10GRN |
| DN-T10ORG-A | KN-T10ORG |
| DN-T10RED-A | KN-T10RED |
| DN-T10W-A | KN-T10WHT |
| DN-T10YEL-A | KN-T10YEL |
| DN-T8 | KN-T8GRY |
| DN-T8B | KN-T8BLU |
| DN-T8BLK | KN-T8BLK |
| DN-T8BR | KN-T8BRN |
| DN-T8GRN | KN-T8GRN |
| DN-T8ORG | KN-T8ORG |
| DN-T8RED | KN-T8RED |
| DN-T8W | KN-T8WHT |
| DN-T8YEL | KN-T8YEL |
| DN-T6 | KN-T6GRY |
| DN-T6B | KN-T6BLU |
| DN-T6BLK | KN-T6BLK |
| DN-T6BR | KN-T6BRN |
| DN-T6GRN | KN-T6GRN |
| DN-T6ORG | KN-T6ORG |
| DN-T6RED | KN-T6RED |

| DINnectors | KONNECT-IT |
|--------------|------------------------------|
| DN-T6W | KN-T6WHT |
| DN-T6YEL | KN-T6YEL |
| DN-T4 | KN-T4GRY |
| DN-T4B | KN-T4BLU |
| DN-T1/0 | KN-T1/0GRY |
| DN-T1/0B | KN-T1/0BLU |
| DN-D10-A | KN-D10GRY |
| DN-D10B | KN-D10BLU |
| DN-D10BLK | KN-D10BLK |
| DN-D10GRN | KN-D10GRN |
| DN-D10ORG | KN-D10ORG |
| DN-D10RED | KN-D10RED |
| DN-D10YEL | KN-D10YEL |
| DN-D10X-A | KN-D10X |
| DN-D10DR-A | KN-D10DR1 |
| DN-D10LED1-A | KN-D10LED-24DC |
| DN-TL14-A | KN-TL14 |
| DN-TL14S-A | KN-TL14S |
| DN-TL14SLN-A | KN-TL14SLN |
| DN-TL14SLP-A | KN-TL14SLP |
| DN-M10-A | KN-M10GRY |
| DN-M10B-A | KN-M10BLU |
| DN-G10 | KN-G10 |
| DN-G8 | KN-G8 |
| DN-G6 | KN-G6 |
| DN-G4 | KN-G4 |
| DN-G1/0 | KN-G1/0 |
| DN-MG10 | KN-MG10 |
| DN-F10 | KN-F10 |
| DN-F10L110 | KN-F10L110AC or KN-F10L110DC |
| DN-F10L220 | KN-F10L220AC or KN-F10L220DC |
| DN-F10L24 | KN-F10L24AC or KN-F10L24DC |
| DN-DIS10 | KN-F10-DCH |
| DN-KBD12 | KN-KBD10 |

KONNECT-IT® Cross Reference



Entrelec®

The following is a list of comparable products. To obtain our high-quality KONNECT-IT terminal blocks, simply find the corresponding part number of the unit you currently use. These are approximate replacements based on UL wire size, ampacity and voltage. Please consult the technical section for specifications to determine suitability for your application. Physical size varies from manufacturer to manufacturer.

| Entrelec | KONNECT-IT |
|------------|------------|
| 115 486.03 | KN-T12GRY |
| 125 486.05 | KN-T12BLU |
| 115 116.07 | KN-T10GRY |
| 125 116.01 | KN-T10BLU |
| 115 118.11 | KN-T8GRY |
| 125 118.13 | KN-T8BLU |
| 115 120.17 | KN-T6GRY |
| 125 120.11 | KN-T6BLU |
| 115 129.14 | KN-T4GRY |
| 125 129.16 | KN-T4BLU |
| 115 124.07 | KN-T2GRY |
| 125 124.01 | KN-T2BLU |
| 115 216.13 | KN-T2/0GRY |
| 125 216.15 | KN-T2/0BLU |
| 115 490.13 | KN-D12GRY |
| 125 490.15 | KN-D12BLU |
| 115 271.22 | KN-D10GRY |
| 115.541.11 | KN-TL14 |
| 115 542.12 | KN-TL14S |
| 115 643.27 | KN-DG12 |
| 110 251.05 | KN-M10GRY |
| 120 251.07 | KN-M10BLU |
| 165 488.27 | KN-G10 |
| 165 113.16 | KN-G10 |
| 165 114.17 | KN-G8 |
| 165 115.10 | KN-G8 |
| 165 130.23 | KN-G4 |
| 165 111.14 | KN-G2 |
| 160 496.26 | KN-MG10 |
| 115 657.25 | KN-F10 |
| 115 604.21 | KN-F10SP |
| 115 986.00 | KN-KBD10 |

KONNECT-It® Cross Reference



Phoenix Contact®

The following is a list of comparable products. To obtain our high-quality KONNECT-It terminal blocks, simply find the corresponding part number of the unit you currently use. These are approximate replacements based on UL wire size, ampacity and voltage. Please consult the technical section for specifications to determine suitability for your application. Physical size varies from manufacturer to manufacturer.

| Phoenix Contact | KONNECT-It |
|-----------------|----------------------------|
| 3003347 | KN-T12GRY |
| 3003350 | KN-T12BLU |
| 3004362 | KN-T10GRY |
| 3004388 | KN-T10BLU |
| 3004524 | KN-T8GRY |
| 3004977 | KN-T8BLU |
| 3005073 | KN-T6GRY |
| 3005086 | KN-T6BLU |
| 3006043 | KN-T4GRY |
| 3006056 | KN-T4BLU |
| 3074130 | KN-T2GRY |
| 3058350 | KN-T2BLU |
| 3213140 | KN-T2/0GRY |
| 3244601 | KN-T2/0BLU |
| 2771146 | KN-D10GRY |
| 3216053 | KN-D10BLU |
| 2715979 | KN-TL14 |
| 2715966 | KN-TL14S |
| 0461018 | KN-DG12 |
| 3011041 | KN-TG12 |
| 2775375 | KN-T12SP4 |
| 1413036 | KN-M12GRY |
| 1413078 | KN-M12BLU |
| 1402940 | KN-M10GRY |
| 1402982 | KN-M10BLU |
| 0441083 | KN-G10 |
| 0441504 | KN-G10 |
| 0442079 | KN-G8 |
| 3003923 | KN-G8 |
| 0443023 | KN-G4 |
| 3074143 | KN-G2 |
| 2775456 | KN-G12SP4 |
| 1413117 | KN-MG12 |
| 0452043 | KN-MG10 |
| 3004100 | KN-F10 |
| 3004126 | KN-F10L24DC or KN-F10L24AC |
| 3104013 | KN-KBD10 |

KONNECT-It® Cross Reference



Weidmuller®

The following is a list of comparable products. To obtain our high-quality KONNECT-It terminal blocks, simply find the corresponding part number of the unit you currently use. These are approximate replacements based on UL wire size, ampacity and voltage. Please consult the technical section for specifications to determine suitability for your application. Physical size varies from manufacturer to manufacturer.

| Weidmuller | KONNECT-It |
|------------|------------|
| 1020000000 | KN-T12GRY |
| 1020080000 | KN-T12BLU |
| 1020010000 | KN-T12BLK |
| 1037710000 | KN-T12BRN |
| 1020090000 | KN-T12GRN |
| 1020060000 | KN-T12ORG |
| 1020040000 | KN-T12RED |
| 1036800000 | KN-T12WHT |
| 1020020000 | KN-T12YEL |
| 1020100000 | KN-T10GRY |
| 1020180000 | KN-T10BLU |
| 1020110000 | KN-T10BLK |
| 1037810000 | KN-T10BRN |
| 1020160000 | KN-T10GRN |
| 1036760000 | KN-T10ORG |
| 1020140000 | KN-T10RED |
| 1036700000 | KN-T10WHT |
| 1020120000 | KN-T10YEL |
| 1020200000 | KN-T8GRY |
| 1020280000 | KN-T8BLU |
| 1020300000 | KN-T6GRY |
| 1020380000 | KN-T6BLU |
| 1020400000 | KN-T4GRY |
| 1020480000 | KN-T4BLU |
| 1020500000 | KN-T2GRY |

| Weidmuller | KONNECT-It |
|------------|--------------|
| 1020580000 | KN-T2BLU |
| 1021500000 | KN-D12GRY |
| 1021580000 | KN-D12BLU |
| 1041610000 | KN-D12X |
| 1041910000 | KN-D10X |
| 1784180000 | KN-TL14 |
| 7917030000 | KN-TG12 |
| 1031400000 | KN-T12SP4 |
| 0697160000 | KN-M12GRY |
| 0697180000 | KN-M12BLU |
| 9537110000 | KN-M10GRY |
| 1038680000 | KN-M10BLU |
| 1010000000 | KN-G10 |
| 1010100000 | KN-G10 |
| 1010200000 | KN-G8 |
| 1010300000 | KN-G8 |
| 1010400000 | KN-G4 |
| 1010500000 | KN-G2 |
| 1016500000 | KN-G12SP4 |
| 1303360000 | KN-MG12 |
| 0380260000 | KN-MG10 |
| 1011000000 | KN-F10 |
| 1012300000 | KN-F10L110AC |
| 1012400000 | KN-F10L220AC |
| 1011300000 | KN-F10L24DC |
| 7910180000 | KN-KBD10 |