

NEMA 12 and 13 Handy Screw Cover Wall-Mount



Applications

Designed for use where protection from dirt, dust, oil and water is needed. Particularly suitable for use with liquid-tight flexible conduit.

Construction

- Bodies and doors fabricated from 14-gauge steel
- Drawn lid that features no welded seams or sharp corners
- No holes or conduit knockouts
- Lids are sealed with closed-cell oil-resistant neoprene gasket
- Cover screws thread into neoprene gasket for maximum seal
- External mounting plates on top and bottom of enclosure
- Screw holes for cover match conventional outlet mounting criteria

Finish

- ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13
- JIC EL-1-71



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 12 and 13 Handy Screw Cover Wall-Mount

Part Number	Price	Size HxWxD
<u>JIC040202</u>	\$24.50	4.30 x 2.30 x 2.26 [109 x 58 x 57]
<u>JIC0403025</u>	\$32.00	4.55 x 3.17 x 2.89 [116 x 81 x 73]
<u>JIC040403</u>	\$41.50	4.25 x 4.25 x 3.26 [108 x 108 x 83]

Notes: Dimensions in inches [millimeters]
Letters in table correspond to letters on dimensional drawings.

Dimensions

