

NEMA 12 Single-Door Dual-Access Freestanding



Applications

Designed to protect electrical and electronic controls, components, and instruments from dust, dirt, oil and dripping water in typical industrial environments. These enclosures are used in machine tool applications for housing motor starters, drives, contactors, and PLCs, as well as a wide variety of other electrical and electronic equipment in automotive, pulp and paper, wood products, textile and similar industries.

Dual-access enclosures have identical doors on both the front and the back of the enclosures for applications where access from both sides is required.

Construction

- Continuously welded seams ground smooth.
- Heavy duty lifting eyes for easy handling.
- Grounding provisions provided.
- Heavy gauge continuous hinges support each door.
- 3-point latching mechanism with an oil-tight key locking handle is provided.
- Doors are sealed with poured in place polyurethane.
- “Uni-strut” mounting channels are welded horizontally to interior body sides and top, bottom and center to allow back panels to be positioned in enclosure.
- Optional swing, half, full and rack panels can be mounted anywhere along “uni-strut” channel and facing either door.

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL 508Type 12 [UL File E64791]
- CSA Certified, Type 12 [CSA File LL66078]
- NEMA/EEMAC Type 12

Enclosure Shipping Schedule

1 -10 days

Color indicates shipping lead time in business days.




NEMA 12 Single-Door Dual-Access Freestanding			
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
WA722424FSDA	\$1,509.00	12/12	72.12x24.12x24.25 [1832x613x616]
WA722430FSDA	\$1,660.00	12/12	72.12x24.12x30.25 [1832x613x768]
WA722436FSDA	\$1,812.00	12/12	72.12x24.12x36.25 [1832x613x921]
WA723024FSDA	\$1,660.00	12/12	72.12x30.12x24.25 [1832x765x616]
WA723624FSDA	\$1,812.00	12/12	72.12x36.12x24.25 [1832x917x616]
WA723636FSDA	\$2,154.00	12/12	72.12x36.12x36.25 [1832x917x921]
WA903624FSDA	\$2,097.00	12/10	90.12x36.12x24.25 [2289x917x616]
WA903636FSDA	\$2,496.00	12/10	90.12x36.12x36.25 [2289x917x921]

Note: Subpanels must be ordered separately. Dimensions in inches (millimeters); letters in table correspond to letters on dimensional drawings.

NEMA 12 Single-Door Dual-Access Freestanding

Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.

Standard Subpanels for Freestanding Enclosures

Enclosure Shipping Schedule

1 - 7 days

1 -10 days

Color indicates shipping lead time in business days.

Standard Subpanels for Freestanding Enclosures				
Enclosures	Standard Subpanels			
	Full Height		Half Height	
	Painted Steel	Galvanized	Painted Steel	Galvanized
WA602418FS	WA60P24F1	WA60P24F1G	WA60P24F2	WA60P24F2G
WA603624FS	WA60P36F1	WA60P36F1G	WA60P36F2	WA60P36F2G
WA722418FS	WA72P24F1	WA72P24F1G	WA72P24F2	WA72P24F2G
WA722424FS	WA72P24F1	WA72P24F1G	WA72P24F2	WA72P24F2G
WA723018FS	WA72P30F1	WA72P30F1G	WA72P30F2	WA72P30F2G
WA723024FS	WA72P30F1	WA72P30F1G	WA72P30F2	WA72P30F2G
WA723618FS	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA723624FS	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA723630FS	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA723636FS	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA902420FS	WA90P24F1	WA90P24F1G	WA90P24F2	WA90P24F2G
WA903620FS	WA90P36F1	WA90P36F1G	WA90P36F2	WA90P36F2G
WA903624FS	WA90P36F1	WA90P36F1G	WA90P36F2	WA90P36F2G
WA903636FS	WA90P36F1	WA90P36F1G	WA90P36F2	WA90P36F2G
WA604818FSD	WA60P48F1	WA60P48F1G	WA60P48F2	WA60P48F2G
WA724818FSD	WA72P48F1	WA72P48F1G	WA72P48F2	WA72P48F2G
WA724824FSD	WA72P48F1	WA72P48F1G	WA72P48F2	WA72P48F2G
WA726018FSD	WA72P60F1	WA72P60F1G	WA72P60F2	WA72P60F2G
WA726024FSD	WA72P60F1	WA72P60F1G	WA72P60F2	WA72P60F2G
WA726036FSD	WA72P60F1	WA72P60F1G	WA72P60F2	WA72P60F2G
WA727218FSD	WA72P72F1	WA72P72F1G	WA72P72F2	WA72P72F2G
WA727224FSD	WA72P72F1	-	WA72P72F2	WA72P72F2G
WA904820FSD	WA90P48F1	WA90P48F1G	WA90P48F2	WA90P48F2G
WA907220FSD	WA90P72F1	-	WA90P72F2	WA90P72F2G
WA907224FSD	WA90P72F1	-	WA90P72F2	WA90P72F2G
WA907236FSD	WA90P72F1	-	WA90P72F2	WA90P72F2G
WA722424FSDA	WA72P24F1	WA72P24F1G	WA72P24F2	WA72P24F2G
WA722430FSDA	WA72P24F1	WA72P24F1G	WA72P24F2	WA72P24F2G
WA722436FSDA	WA72P24F1	WA72P24F1G	WA72P24F2	WA72P24F2G
WA723024FSDA	WA72P30F1	WA72P30F1G	WA72P30F2	WA72P30F2G
WA723624FSDA	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA723636FSDA	WA72P36F1	WA72P36F1G	WA72P36F2	WA72P36F2G
WA903624FSDA	WA90P36F1	WA90P36F1G	WA90P36F2	WA90P36F2G
WA903636FSDA	WA90P36F1	WA90P36F1G	WA90P36F2	WA90P36F2G
WA724824FSDAD	WA72P48F1	WA72P48F1G	WA72P48F2	WA72P48F2G
WA726024FSDAD	WA72P60F1	WA72P60F1G	WA72P60F2	WA72P60F2G
WA726036FSDAD	WA72P60F1	WA72P60F1G	WA72P60F2	WA72P60F2G
WA727224FSDAD	WA72P72F1	-	WA72P72F2	WA72P72F2G
WA907224FSDAD	WA90P72F1	-	WA90P72F2	WA90P72F2G

Swing-Out Panels for Freestanding Enclosures

Enclosure Shipping Schedule

1 - 7 days

1 -10 days

Color indicates shipping lead time in business days.

Swing-Out Panels for Freestanding Enclosures				
Enclosures	Swing-Out Panels			
	Full Height		Half Height	
	Painted Steel	Galvanized	Painted Steel	Galvanized
WA602418FS	WA60SP24F3	WA60SP24F3G	WA60SP24F4	WA60SP24F4G
WA603624FS	WA60SP36F3	WA60SP36F3G	WA60SP36F4	WA60SP36F4G
WA722418FS	WA72SP24F3	WA72SP24F3G	WA72SP24F4	WA72SP24F4G
WA722424FS	WA72SP24F3	WA72SP24F3G	WA72SP24F4	WA72SP24F4G
WA723018FS	WA72SP30F3	WA72SP30F3G	WA72SP30F4	WA72SP30F4G
WA723024FS	WA72SP30F3	WA72SP30F3G	WA72SP30F4	WA72SP30F4G
WA723618FS	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA723624FS	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA723630FS	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA723636FS	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA902420FS	-	-	-	-
WA903620FS	WA90SP36F3	WA90SP36F3G	WA90SP36F4	WA90SP36F4G
WA903624FS	WA90SP36F3	WA90SP36F3G	WA90SP36F4	WA90SP36F4G
WA903636FS	WA90SP36F3	WA90SP36F3G	WA90SP36F4	WA90SP36F4G
WA604818FSD	-	-	-	-
WA724818FSD	-	-	-	-
WA724824FSD	-	-	-	-
WA726018FSD	-	-	-	-
WA726024FSD	-	-	-	-
WA726036FSD	-	-	-	-
WA727218FSD	-	-	-	-
WA727224FSD	-	-	-	-
WA904820FSD	-	-	-	-
WA907220FSD	-	-	-	-
WA907224FSD	-	-	-	-
WA907236FSD	-	-	-	-
WA722424FSDA	WA72SP24F3	WA72SP24F3G	WA72SP24F4	WA72SP24F4G
WA722430FSDA	WA72SP24F3	WA72SP24F3G	WA72SP24F4	WA72SP24F4G
WA722436FSDA	WA72SP24F3	WA72SP24F3G	WA72SP24F4	WA72SP24F4G
WA723024FSDA	WA72SP30F3	WA72SP30F3G	WA72SP30F4	WA72SP30F4G
WA723624FSDA	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA723636FSDA	WA72SP36F3	WA72SP36F3G	WA72SP36F4	WA72SP36F4G
WA903624FSDA	WA90SP36F3	WA90SP36F3G	WA90SP36F4	WA90SP36F4G
WA903636FSDA	WA90SP36F3	WA90SP36F3G	WA90SP36F4	WA90SP36F4G
WA724824FSDAD	-	-	-	-
WA726024FSDAD	-	-	-	-
WA726036FSDAD	-	-	-	-
WA727224FSDAD	-	-	-	-
WA907224FSDAD	-	-	-	-

Side-Mount Panels for Freestanding Enclosures

Enclosure Shipping Schedule

1 - 7 days

1 - 10 days

Color indicates shipping lead time in business days.

Side-Mount Panels for Freestanding Enclosures		
Enclosures	Side-Mount Panels	
	Painted Steel	Galvanized
WA602418FS	WA60SMP14	WA60SMP14G
WA603624FS	WA60SMP14	WA60SMP14G
WA722418FS	WA72SMP14	WA72SMP14G
WA722424FS	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723018FS	WA72SMP14	WA72SMP14G
WA723024FS	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723618FS	WA72SMP14	WA72SMP14G
WA723624FS	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723630FS	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723636FS	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA902420FS	WA90SMP14	WA90SMP14G
WA903620FS	WA90SMP14	WA90SMP14G
WA903624FS	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA903636FS	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA604818FSD	WA60SMP14	WA60SMP14G
WA724818FSD	WA72SMP14	WA72SMP14G
WA724824FSD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA726018FSD	WA72SMP14	WA72SMP14G
WA726024FSD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA726036FSD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA727218FSD	WA72SMP14	WA72SMP14G
WA727224FSD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA904820FSD	WA90SMP14	WA90SMP14G
WA907220FSD	WA90SMP14	WA90SMP14G
WA907224FSD	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA907236FSD	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA722424FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA722430FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA722436FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723024FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723624FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA723636FSDA	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA903624FSDA	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA903636FSDA	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G
WA724824FSDAD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA726024FSDAD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA726036FSDAD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA727224FSDAD	WA72SMP14, WA72SMP20	WA72SMP14G, WA72SMP20G
WA907224FSDAD	WA90SMP14, WA90SMP20	WA90SMP14G, WA90SMP20G

Swing-Out Racks and Center Post Supports for Freestanding Enclosures

Enclosure Shipping Schedule	
1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.	

Swing-Out Racks and Center Post Supports for Freestanding Enclosures		
Enclosures	Swing-Out Rack	Center Post Support
WA602418FS	-	-
WA603624FS	-	-
WA722418FS	-	-
WA722424FS	-	-
WA723018FS	WA7230SOF19	-
WA723024FS	WA7230SOF19	-
WA723618FS	WA7236SOF19	-
WA723624FS	WA7236SOF19	-
WA723630FS	WA7236SOF19	-
WA723636FS	WA7236SOF19	-
WA902420FS	-	-
WA903620FS	WA9036SOF19	-
WA903624FS	WA9036SOF19	-
WA903636FS	WA9036SOF19	-
WA604818FSD	-	WA60FSCPS
WA724818FSD	-	WA72FSCPS
WA724824FSD	-	WA72FSCPS
WA726018FSD	-	WA72FSCPS
WA726024FSD	-	WA72FSCPS
WA726036FSD	-	WA72FSCPS
WA727218FSD	-	WA72FSCPS
WA727224FSD	-	WA72FSCPS
WA904820FSD	-	WA90FSCPS
WA907220FSD	-	WA90FSCPS
WA907224FSD	-	WA90FSCPS
WA907236FSD	-	WA90FSCPS
WA722424FSDA	-	-
WA722430FSDA	-	-
WA722436FSDA	-	-
WA723024FSDA	WA7230SOF19	-
WA723624FSDA	WA7236SOF19	-
WA723636FSDA	WA7236SOF19	-
WA903624FSDA	WA9036SOF19	-
WA903636FSDA	WA9036SOF19	-
WA724824FSDAD	-	WA72FSCPS
WA726024FSDAD	-	WA72FSCPS
WA726036FSDAD	-	WA72FSCPS
WA727224FSDAD	-	WA72FSCPS
WA907224FSDAD	-	WA90FSCPS