

# NEMA 12 and 13 Single-Door Flush Wall-Mount



## Applications

Designed to house electrical controls, terminals and instruments. Provide protection from dirt, dust, oil and water. External frame allows enclosure to be recessed in wall. Enclosure is used in applications where external space is limited or in high traffic areas.

## Construction

- Bodies and doors fabricated from 14-gauge steel
- 10-gauge steel mounting frame extends completely around enclosure
- Continuously plasma welded seams
- Grounding provisions provided
- Collar studs provided for mounting optional subpanel
- Rolled lip around all sides of enclosure opening is provided to exclude liquids and contaminants
- Doors are sealed with a poured-in-place polyurethane gasket
- Door is held closed with captivated screws threaded into sealed wells
- Door is removable by pulling heavy gauge continuous hinge pin

## Finish

- ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50 12 and 13 [UL File E6924]
- NEMA/EEMAC 12 and 13
- JIC EL - 1 - 71



Note: Do NOT use NPxxxxC subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures. For example: Subpanel NP1612C will not fit enclosure. WA161206FM (NP1612 is the correct subpanel). Only use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures.

### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

### NEMA 12 and 13 Single-Door Flush Wall-Mount




Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Steel Subpanel	Perforated Subpanel
<b>WA161206FM</b>	\$541.00	16.00 x 12.00 x 7.13 [406 x 305 x 181]	<b>NP1612</b>	<b>NP1612SS</b>	<b>NP1612G</b>	<b>NP1612PP</b>
<b>WA202006FM</b>	\$674.00	20.00 x 20.00 x 7.13 [508 x 508 x 181]	<b>NP2020</b>	<b>NP2020SS</b>	<b>NP2020G</b>	<b>NP2020PP</b>
<b>WA242408FM</b>	\$825.00	24.00 x 24.00 x 9.13 [610 x 610 x 232]	<b>NP2424</b>	<b>NP2424SS</b>	<b>NP2424G</b>	<b>NP2424PP</b>
<b>WA302408FM</b>	\$961.00	30.00 x 24.00 x 9.13 [762 x 610 x 232]	<b>NP3024</b>	<b>NP3024SS</b>	<b>NP3024G</b>	<b>NP3024PP</b>
<b>WA363008FM</b>	\$1,293.00	36.00 x 30.00 x 9.13 [914 x 762 x 232]	<b>NP3630</b>	<b>NP3630SS</b>	<b>NP3630G</b>	<b>NP3630PP</b>

Notes: Subpanels must be ordered separately.  
 Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawings.

# NEMA 12 and 13 Single-Door Flush Wall-Mount



## Dimensions



SECTION X-X

NOTES:

1. PANELS MADE FROM 12 GA. STEEL
2. IF  $H = < 20"$ , PRINT POCKET IS 6" X 6". IF  $H = 20"$  OR MORE, PRINT POCKET IS 8" X 10".

# Enclosure Subpanels




## Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

- 12-gauge steel (perforated subpanels are 14-gauge)
- Subpanels with any side over 17 in [432 mm] have 0.25 in [6mm] flange on all sides
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint) Panels listed fit the following enclosures:
- NEMA 1 large (N1C, 42 in [1067 mm] width and wider)
- NEMA 12 single door wall-mount (N12)
- NEMA 12 two-door wall-mount (WA\_WF)
- NEMA 12 single door flush wall-mount (WA\_FM)
- NEMA 4 (N4) and 4X (SSN) single door wall-mount
- NEMA 12 operator consoles (WC9)
- NEMA 12 Wall Disconnect (SDN12\_PL and ABN12)
- NEMA 4 and 4X Wall-Mount Disconnect (SSN4 and SSN4X)



Note: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in N412 Ultimate Series enclosures with a C in the suffix.

## Dimensions



NOTE:  
SUBPANELS LARGER THAN  
20 X 20 HAVE (2) 0.31"  
GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25 in [6 mm] spacing.

# Enclosure Subpanels



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

Painted Steel	Price	Galvanized	Price	Perforated	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<a href="#">NP1212</a>	\$18.50	<a href="#">NP1212G</a>	\$26.00	—	—	—	—	12 x 12	9.00 x 9.00 [229 x 229]
<a href="#">NP1224</a>	\$45.50	<a href="#">NP1224G</a>	\$45.50	—	—	—	—	24 x 12	9.00 x 21.00 [229 x 533]
<a href="#">NP1612</a>	\$33.00	<a href="#">NP1612G</a>	\$33.00	<a href="#">NP1612PP</a>	\$33.00	<a href="#">NP1612SS</a>	\$87.00	12 x 16 16 x 12	13.00 x 9.00 [330 x 229]
<a href="#">NP1616</a>	\$40.50	<a href="#">NP1616G</a>	\$40.50	<a href="#">NP1616PP</a>	\$40.50	<a href="#">NP1616SS</a>	\$106.00	16 x 16	13.00 x 13.00 [330 x 330]
<a href="#">NP2012</a>	\$38.00	<a href="#">NP2012G</a>	\$38.00	—	—	—	—	20 x 12	17.00 x 9.00 [432 x 229]
<a href="#">NP2016</a>	\$48.00	<a href="#">NP2016G</a>	\$48.00	<a href="#">NP2016PP</a>	\$48.00	<a href="#">NP2016SS</a>	\$128.00	20 x 16	17.00 x 13.00 [432 x 330]
<a href="#">NP2020</a>	\$58.00	<a href="#">NP2020G</a>	\$58.00	<a href="#">NP2020PP</a>	\$58.00	<a href="#">NP2020SS</a>	\$165.00	20 x 20	17.00 x 17.00 [432 x 432]
<a href="#">NP2416</a>	\$56.00	<a href="#">NP2416G</a>	\$60.00	—	—	<a href="#">NP2416SS</a>	\$159.00	24 x 16	21.00 x 13.00 [533 x 330]
<a href="#">NP2420</a>	\$75.00	<a href="#">NP2420G</a>	\$75.00	<a href="#">NP2420PP</a>	\$75.00	<a href="#">NP2420SS</a>	\$200.00	24 x 20	21.00 x 17.00 [533 x 432]
<a href="#">NP2424</a>	\$86.00	<a href="#">NP2424G</a>	\$86.00	<a href="#">NP2424PP</a>	\$86.00	<a href="#">NP2424SS</a>	\$233.00	24 x 24	21.00 x 21.00 [533 x 533]
<a href="#">NP3016</a>	\$75.00	<a href="#">NP3016G</a>	\$75.00	—	—	—	—	30 x 16	27.00 x 13.00 [686 x 330]
<a href="#">NP3020</a>	\$90.00	<a href="#">NP3020G</a>	\$90.00	—	—	<a href="#">NP3020SS</a>	\$268.00	30 x 20	27.00 x 17.00 [686 x 432]
<a href="#">NP3024</a>	\$105.00	<a href="#">NP3024G</a>	\$105.00	<a href="#">NP3024PP</a>	\$105.00	<a href="#">NP3024SS</a>	\$283.00	24 x 30 30 x 24	27.00 x 21.00 [686 x 533]
<a href="#">NP3030</a>	\$147.00	<a href="#">NP3030G</a>	\$147.00	<a href="#">NP3030PP</a>	\$147.00	<a href="#">NP3030SS</a>	\$452.00	30 x 30	27.00 x 27.00 [686 x 686]
<a href="#">NP3624</a>	\$125.00	<a href="#">NP3624G</a>	\$125.00	<a href="#">NP3624PP</a>	\$125.00	<a href="#">NP3624SS</a>	\$386.00	36 x 24	33.00 x 21.00 [838 x 533]
<a href="#">NP3630</a>	\$167.00	<a href="#">NP3630G</a>	\$167.00	<a href="#">NP3630PP</a>	\$167.00	<a href="#">NP3630SS</a>	\$443.00	30 x 36 36 x 30	33.00 x 27.00 [838 x 686]
<a href="#">NP3636</a>	\$196.00	<a href="#">NP3636G</a>	\$196.00	<a href="#">NP3636PP</a>	\$196.00	<a href="#">NP3636SS</a>	\$535.00	36 x 36	33.00 x 33.00 [838 x 838]
<a href="#">NP4024</a>	\$151.00	—	—	—	—	—	—	40 x 24	37.00 x 21.00 [940 x 533]
<a href="#">NP4224</a>	\$144.00	<a href="#">NP4224G</a>	\$144.00	—	—	—	—	42 x 24	39.00 x 21.00 [991 x 533]
<a href="#">NP4230</a>	\$191.00	<a href="#">NP4230G</a>	\$191.00	<a href="#">NP4230PP</a>	\$191.00	<a href="#">NP4230SS</a>	\$563.00	42 x 30	39.00 x 27.00 [991 x 686]
<a href="#">NP4236</a>	\$225.00	<a href="#">NP4236G</a>	\$225.00	<a href="#">NP4236PP</a>	\$225.00	<a href="#">NP4236SS</a>	\$676.00	42 x 36	39.00 x 33.00 [991 x 838]
<a href="#">NP4824</a>	\$163.00	<a href="#">NP4824G</a>	\$163.00	—	—	—	—	48 x 24	45.00 x 21.00 [1143 x 533]
<a href="#">NP4830</a>	\$215.00	<a href="#">NP4830G</a>	\$215.00	—	—	—	—	48 x 30	45.00 x 27.00 [1143 x 686]
<a href="#">NP4836</a>	\$254.00	<a href="#">NP4836G</a>	\$254.00	<a href="#">NP4836PP</a>	\$254.00	<a href="#">NP4836SS</a>	\$731.00	48 x 36	45.00 x 33.00 [1143 x 838]
<a href="#">NP6030</a>	\$263.00	<a href="#">NP6030G</a>	\$285.00	—	—	—	—	60 x 30	57.00 x 27.00 [1448 x 686]
<a href="#">NP6036</a>	\$313.00	<a href="#">NP6036G</a>	\$313.00	<a href="#">NP6036PP</a>	\$313.00	<a href="#">NP6036SS</a>	\$965.00	60 x 36	57.00 x 33.00 [1448 x 838]
<a href="#">NP7230</a>	\$302.00	<a href="#">NP7230G</a>	\$327.00	—	—	—	—	72 x 30	69.00 x 27.00 [1753 x 686]
<a href="#">NP7236</a>	\$371.00	<a href="#">NP7236G</a>	\$402.00	—	—	—	—	72 x 36	69.00 x 33.00 [1753 x 838]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.