

Disconnect Handle Applications for Wall Mount Disconnect Enclosures

Designed to house the following available at AutomationDirect.com



- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_SO_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C.**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft).
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9FOCA-15A, BW9FOCA-20A, BW9FOGA-15A, BW9FOGA-20A, BW9FOHA-15A, BW9FOHA-20A, BW9FOJA-15A, and BW9FOJA-20A.**

Disconnect Enclosure Series	Available at AutomationDirect.com		
	AutomationDirect F_SO_C Series	Socomec 37299002 & 37299003	Fuji BW9F series
N412_CD Series	✓	✓	✓
N412_CDSS Series	✓	✓	✓
N412_CDSSA Series	✓	✓	✓
N412_CSTD Series	✓	✓	✓
N412_CSSSTD Series	✓	✓	✓
SDN_PL Series	✓	✓	✓
SN4 Series	✓	✓	✓
ABN12 Series	✗	✗	✗
SSN4X Series	✓	✓	✓
SSN4X_A Series	✓	✓	✓

Designed to house other brands

- Allen-Bradley** Bulletin 1494V, 1494C, 140U, & 194RC disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators.
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers.
- General Electric** Type STDA flange handles and variable depth operating.
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers.
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers.
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Disconnect Enclosures Series	Other Brands						
	Square D 9422 series	Allen-Bradley 1494F & 1494D series	Allen-Bradley 1494V, 1494C, 140U, 194RC series	ABB Controls	Eaton/Cutler-Hammer C361 & C371 series	General Electric STDA series	Siemens I-T-E Max-Flex Series
N412_CD Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSS Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSSA Series	✓	✗	✓	✓	✓	✓	✓
N412_CSTD Series	✓	✗	✓	✓	✓	✓	✓
N412_CSSSTD Series	✓	✗	✓	✓	✓	✓	✓
SDN_PL Series	✓	✗	✓	✓	✓	✓	✓
SN4 Series	✓	✗	✓	✓	✓	✓	✓
ABN12 Series	✗	✓	✗	✗	✗	✗	✗
SSN4X Series	✓	✗	✓	✓	✓	✓	✓
SSN4X_A Series	✓	✗	✓	✓	✓	✓	✓

NEMA 4, 4X, 12 and 13 Ultimate Series Single-Door Wall Mount Right-Flanged Disconnect



Construction

- CD enclosures have 14 gauge carbon steel bodies and doors.
- Large tub opening for better access
- Concealed hinges
- Interchangeable and easily removable doors
- Ground stud located in door
- Doors sealed with poured-in-place polyurethane gasket
- Mounting holes in rear
- Studs for mounting optional subpanel
- Door latching system installed on door with a slotted insert defeater mechanism
- Latching system interlocks with the disconnect handle (not included) for added safety

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Listings

- UL 508, Types 4, 12 & 13 [UL File E64791]
- CSA Certified, Types 4, 12 & 13 [CSA File LL66078]
- NEMA/EEMAC Types 4, 12 & 13



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days

Color indicates shipping lead time in business days.

Notes:

- Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.
- **Operator adapter plates are not required with this enclosure series.**
- Make sure the disconnect device you are using will fit the enclosure size you choose.

NEMA 4, 4X and 12 Ultimate Series Single-Door Wall Mount Right-Flanged Disconnect					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
N412202208CD	\$385.00	20.00 x 22.00 x 8.89 [508 x 559 x 226]	NP2020C	NP2020CG	NP2020SSC
N412242208CD	\$407.00	24.00 x 22.00 x 8.89 [610 x 559 x 226]	NP2420C	NP2420CG	NP2420SSC
N412242608CD	\$431.00	24.00 x 26.00 x 8.89 [610 x 660 x 226]	NP2424C	NP2424CG	NP2424SSC
N412302608CD	\$469.00	30.00 x 26.00 x 8.89 [762 x 660 x 226]	NP3024C	NP3024CG	NP3024SSC
N412362608CD	\$507.00	36.00 x 26.00 x 8.89 [914 x 660 x 226]	NP3624C	NP3624CG	NP3624SSC
N412363208CD	\$557.00	36.00 x 32.00 x 8.89 [914 x 813 x 226]	NP3630C	NP3630CG	NP3630SSC
N412423212CD	\$633.00	42.00 x 32.00 x 12.89 [1067 x 813 x 327]	NP4230C	-	-
N412423812CD	\$717.00	42.00 x 38.00 x 12.89 [1067 x 965 x 327]	NP4236C	NP4236CG	NP4236SSC
N412483812CD	\$774.00	48.00 x 38.00 x 12.89 [1219 x 965 x 327]	NP4836C	NP4836CG	NP4836SSC
N412603812CD	\$887.00	60.00 x 38.00 x 12.89 [1524 x 965 x 327]	NP6036C	NP6036CG	NP6036SSC

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12 and 13 Ultimate Series Single-Door Wall Mount Right-Flanged Disconnect

Ultimate Series Single-Door Wall Mount 304 Stainless Steel Disconnect					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
N412202208CDSS	\$1,100.00	20.00 x 22.00 x 8.87 [508 x 559 x 225]	NP2020C	NP2020CG	NP2020SSC
N412242208CDSS	\$1,164.00	24.00 x 22.00 x 8.87 [610 x 559 x 225]	NP2420C	NP2420CG	NP2420SSC
N412242608CDSS	\$1,256.00	24.00 x 26.00 x 8.89 [610 x 660 x 226]	NP2424C	NP2424CG	NP2424SSC
N412302608CDSS	\$1,368.00	30.00 x 26.00 x 8.89 [762 x 660 x 226]	NP3024C	NP3024CG	NP3024SSC
N412362608CDSS	\$1,411.00	36.00 x 26.00 x 8.89 [914 x 660 x 226]	NP3624C	NP3624CG	NP3624SSC
N412363208CDSS	\$1,464.00	36.00 x 32.00 x 8.89 [914 x 813 x 226]	NP3630C	NP3630CG	NP3630SSC
N412423212CDSS	\$1,970.00	42.00 x 32.00 x 12.88 [1067 x 813 x 327]	NP4230C	-	-
N412423812CDSS	\$2,086.00	42.00 x 38.00 x 12.88 [1067 x 965 x 327]	NP4236C	NP4236CG	NP4236SSC
N412483812CDSS	\$2,250.00	48.00 x 38.00 x 12.88 [1219 x 965 x 327]	NP4836C	NP4836CG	NP4836SSC
N412603812CDSS	\$2,645.00	60.00 x 38.00 x 12.88 [1524 x 965 x 327]	NP6036C	NP6036CG	NP6036SSC

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters]

Ultimate Series Single-Door Wall Mount 316L Stainless Steel Disconnect					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Stainless Steel Subpanel
N412202208CDSSA	\$786.00	20.00 x 22.00 x 8.87 [508 x 559 x 225]	NP2020C	NP2020CG	NP2020SSC
N412242208CDSSA	\$837.00	24.00 x 22.00 x 8.87 [610 x 559 x 225]	NP2420C	NP2420CG	NP2420SSC
N412242608CDSSA	\$916.00	24.00 x 26.00 x 8.89 [610 x 660 x 226]	NP2424C	NP2424CG	NP2424SSC
N412302608CDSSA	\$997.00	30.00 x 26.00 x 8.89 [762 x 660 x 226]	NP3024C	NP3024CG	NP3024SSC
N412362608CDSSA	\$1,098.00	36.00 x 26.00 x 8.89 [914 x 660 x 226]	NP3624C	NP3624CG	NP3624SSC
N412363208CDSSA	\$1,213.00	36.00 x 32.00 x 8.89 [914 x 813 x 226]	NP3630C	NP3630CG	NP3630SSC
N412423212CDSSA	\$1,516.00	42.00 x 32.00 x 12.88 [1067 x 813 x 327]	NP4230C	-	-
N412423812CDSSA	\$1,564.00	42.00 x 38.00 x 12.88 [1067 x 965 x 327]	NP4236C	NP4236CG	NP4236SSC
N412483812CDSSA	\$1,585.00	48.00 x 38.00 x 12.88 [1219 x 965 x 327]	NP4836C	NP4836CG	NP4836SSC
N412603812CDSSA	\$1,537.00	60.00 x 38.00 x 12.88 [1524 x 965 x 327]	NP6036C	NP6036CG	NP6036SSC

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawings.

Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days


Color indicates shipping lead time in business days.

See our website: www.AutomationDirect.com for complete engineering drawings.

Ultimate Series Single-Door Wall Mount Right-Flanged Disconnect Enclosures



Dimensions



See our website: www.AutomationDirect.com for complete engineering drawings.

Enclosure Subpanels




Subpanels for Ultimate Series Wall Mount Enclosures

- 12 gauge steel
- Subpanels with dimensions 30" x 30" and larger are flanged on all sides. Smaller subpanels are flanged on two sides
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)



Dimensions in [mm]



Panels listed fit all styles of N412 Ultimate Series wall mount enclosures, including slope top and disconnect enclosures.

NOTE: NPxxxxC subpanels will not fit in older NEMA 4/12 enclosures (purchased prior to 3-23-05) that do not have a C suffix. For example: Subpanel NP1212C will not fit enclosures N412121206 or N412121206SS.

Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

Subpanels for Ultimate Series Wall Mount Enclosures							
Painted Steel	Price	Galvanized	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
NP1212C	\$16.00	NP1212CG	\$16.00	—		12 x 12	10.20 x 10.20 [259 x 259]
NP1612C	\$19.50	NP1612CG	\$19.50	NP1612SSC	\$101.00	16 x 12	14.20 x 10.20 [361 x 259]
NP1616C	\$26.50	NP1616CG	\$26.50	NP1616SSC	\$70.00	16 x 16	14.20 x 14.20 [361 x 361]
NP2016C	\$26.50	NP2016CG	\$26.50	NP2016SSC	\$70.00	16 x 20 20 x 16	18.20 x 14.20 [462 x 361]
NP2020C	\$33.00	NP2020CG	\$33.00	NP2020SSC	\$93.00	20 x 20	18.20 x 18.20 [462 x 462]
NP2416C	\$37.00	NP2416CG	\$37.00	NP2416SSC	\$105.00	24 x 16	22.20 x 14.20 [564 x 361]
NP2420C	\$45.00	NP2420CG	\$45.00	NP2420SSC	\$119.00	24 x 20	22.20 x 18.20 [564 x 462]
NP2424C	\$47.50	NP2424CG	\$47.50	NP2424SSC	\$128.00	24 x 24	22.20 x 22.20 [564 x 564]
NP3020C	\$60.00	NP3020CG	\$60.00	—		30 x 20	28.20 x 18.20 [716 x 462]
NP3024C	\$57.00	NP3024CG	\$57.00	NP3024SSC	\$155.00	30 x 24	28.20 x 22.20 [716 x 564]
NP3030C	\$97.00	NP3030CG	\$97.00	NP3030SSC	\$276.00	30 x 30	28.20 x 28.20 [716 x 716]
NP3624C	\$75.00	NP3624CG	\$75.00	NP3624SSC	\$213.00	36 x 24	34.20 x 22.20 [869 x 564]
NP3630C	\$99.00	NP3630CG	\$99.00	NP3630SSC	\$263.00	36 x 30	34.20 x 28.20 [869 x 716]
NP3636C	\$117.00	NP3636CG	\$117.00	NP3636SSC	\$318.00	36 x 36	34.20 x 34.20 [869 x 869]
NP4024C	\$99.00	NP4024CG	\$99.00	—		40 x 24	38.20 x 22.20 [970 x 564]
NP4230C	\$126.00	—		—		42 x 32	40.20 x 28.20 [1021 x 716]
NP4236C	\$148.00	NP4236CG	\$148.00	NP4236SSC	\$411.00	42 x 36	40.20 x 34.20 [1021 x 869]
NP4824C	\$107.00	NP4824CG	\$107.00	—		48 x 24	46.20 x 22.20 [1173 x 564]
NP4836C	\$168.00	NP4836CG	\$168.00	NP4836SSC	\$446.00	48 x 36	46.20 x 34.20 [1173 x 869]
NP6036C	\$188.00	NP6036CG	\$188.00	NP6036SSC	\$535.00	60 x 36	58.20 x 34.20 [1478 x 869]

Notes: Dimensions in inches [millimeters].
 Letters in table correspond to letters on dimensional drawing.
 *Disconnect enclosures will be up to 2 inches [51mm] wider than width dimensions in this table.