

# NEMA 4, 12 and 13 Continuous-Hinge Wall Mount



## Application

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection in areas that are hosed down, very wet, or in outdoor applications.

## Construction

- Bodies fabricated from 14 gauge carbon steel; Doors fabricated from 16 gauge carbon steel
- Continuously welded seams ground smooth
- Poured-in-place polyurethane gasket
- External mounting feet, top and bottom
- Weldnuts are provided on models 6" x 4" and larger to secure optional subpanel
- Continuous-hinge cover is secured on three sides with stainless steel screws and clamps to ensure a watertight seal
- Cover removable by pulling stainless steel hinge pin
- Grounding provisions provided
- Optional subpanels must be ordered separately
- [Uses WABN4JIC clamp](#)

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, Types 4, 12 and 13 [UL file E6924 and E64791]
- CSA Certified, Types 4 and 12 [CSA file LL66078]
- Meets NEMA/EEMAC Types 4, 12 and 13 requirements



Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	


NEMA 4, 12 and 13 Continuous-Hinge Wall Mount					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Subpanel
<b>BN4040403CH</b>	\$44.00	4.31 x 4.31 x 3.16 [109 x 109 x 80]	–	–	–
<b>BN4060403CH</b>	\$52.00	6.31 x 4.31 x 3.16 [160 x 109 x 80]	<b>P0604</b>	<b>P0604SS</b>	<b>P0604G</b>
<b>BN4060604CH</b>	\$50.00	6.31 x 6.31 x 4.16 [160 x 160 x 106]	<b>P0606</b>	<b>P0606SS</b>	<b>P0606G</b>
<b>BN4080603CH</b>	\$64.00	8.31 x 6.31 x 3.16 [211 x 160 x 80]	<b>P0806</b>	<b>P0806SS</b>	<b>P0806G</b>
<b>BN4100804CH</b>	\$66.00	10.31 x 8.31 x 4.16 [262 x 211 x 106]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>BN4100806CH</b>	\$82.00	10.31 x 8.31 x 6.16 [262 x 211 x 156]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>BN4121005CH</b>	\$92.00	12.31 x 10.31 x 5.16 [313 x 262 x 131]	<b>P1210</b>	<b>P1210SS</b>	<b>P1210G</b>
<b>BN4121206CH</b>	\$97.00	12.31 x 12.31 x 6.16 [313 x 313 x 156]	<b>P1212</b>	<b>P1212SS</b>	<b>P1212G</b>
<b>BN4141206CH</b>	\$117.00	14.31 x 12.31 x 6.16 [363 x 313 x 156]	<b>P1412</b>	<b>P1412SS</b>	<b>P1412G</b>
<b>BN4161406CH</b>	\$126.00	16.31 x 14.31 x 6.16 [414 x 363 x 156]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>

**Notes:** Subpanels must be ordered separately.  
Dimensions in inches [millimeters].

# NEMA 4, 12 and 13 Continuous-Hinge Wall Mount



## Dimensions



*See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.*

*See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.*

# Enclosure Subpanels



## Subpanels

Subpanels are not included with most enclosures and must be purchased separately. The specifications table for each enclosure family lists the part number of the subpanel that goes with each enclosure.

## Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14 gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B\_CH, BN4, BN4\_CH, BN4\_CHQT, BN4\_SS, BN4\_CHSS, BN4\_CHSSA, BN4\_CHQTSS, BN4\_CHQTSSA ("\_" refers to dimensions).




Subpanels for B and BN4 Enclosures							
Painted Steel	Price	304 Stainless Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
P0604	\$3.00	P0604SS	\$10.75	P0604G	\$3.00	6 x 4	4.88 x 2.88 [124 x 73]
P0606	\$3.25	P0606SS	\$13.25	P0606G	\$3.25	6 x 6	4.88 x 4.88 [124 x 124]
P0806	\$4.00	P0806SS	\$15.50	P0806G	\$4.00	8 x 6	6.88 x 4.88 [175 x 124]
P0808	\$4.75	-		P0808G	\$4.75	8 x 8	6.88 x 6.88 [175 x 175]
P1008	\$5.25	P1008SS	\$22.50	P1008G	\$5.25	10 x 8	8.88 x 6.88 [226 x 175]
P1010	\$7.25	-		P1010G	\$7.25	10 x 10	8.88 x 8.88 [226 x 226]
P1206	\$5.75	-		P1206G	\$5.75	12 x 6	10.88 x 4.88 [276 x 124]
P1210	\$7.50	P1210SS	\$30.00	P1210G	\$7.50	12 x 10	10.88 x 8.88 [276 x 226]
P1212	\$9.00	P1212SS	\$37.50	P1212G	\$9.00	12 x 12	10.88 x 10.88 [276 x 276]
P1408	\$8.00	-		P1408G	\$8.00	14 x 8	12.88 x 6.88 [327 x 175]
P1412	\$9.75	P1412SS	\$43.00	P1412G	\$9.75	14 x 12	12.88 x 10.88 [327 x 276]
P1610	\$10.75	-		P1610G	\$10.75	16 x 10	14.88 x 8.88 [378 x 226]
P1614	\$12.00	P1614SS	\$57.00	P1614G	\$12.00	16 x 14	14.88 x 12.88 [378 x 327]

*Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing.*

### Dimensions

in [mm]



Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.