

NEMA 1 Single-Door Wall-Mount With Knockouts



Your Enclosure Source®



SCE-8N804NKLP

Applications

Designed to house electrical controls, instruments, and components in areas that do not require oil, water and dust-tight protection.

Construction

- 14-gauge, 16-gauge, or 18-gauge carbon steel, depending on size (see drawings for details)
- Spot weld construction
- Knockouts provided in the top, bottom, right, and left sides
- Standoffs provided for mounting optional subpanels
- Butt hinges
- Doors open 180°
- Black, 1/4-turn latches
- Latches can be opened or closed with a screwdriver
- Ground studs on door and body
- Mounting holes in back of enclosure
- Subpanel mounting hardware included
- Optional mounting straps available

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 1
- cULus Listed Type 1 [File E69392]
- IEC 60529 IP30



Knockouts are provided in the top, bottom, right, and left sides of the enclosure. Knockout sizes vary by enclosure size — refer to individual drawing links for exact knockout dimensions and locations.

NEMA 1 Single-Door Wall-Mount With Knockouts							
Part Number	Price	Nominal Size HxWxD	Drawing Link	Subpanel 1	Price	Subpanel 2	Price
SCE-8N804NKLP	\$63.00	8.00 x 8.00 x 4.00	PDF	SCE-8N8MP	\$6.50	SCE-8N8MPP	\$16.50
SCE-8N806NKLP	\$71.00	8.00 x 8.00 x 6.00	PDF	SCE-8N8MP	\$6.50	SCE-8N8MPP	\$16.50
SCE-10N804NKLP	\$70.00	10.00 x 8.00 x 4.00	PDF	SCE-10N8MP	\$7.50	SCE-10N8MPP	\$19.50
SCE-10N806NKLP	\$79.00	10.00 x 8.00 x 6.00	PDF	SCE-10N8MP	\$7.50	SCE-10N8MPP	\$19.50
SCE-10N1004NKLP	\$71.00	10.00 x 10.00 x 4.00	PDF	SCE-10N10MP	\$8.75	SCE-10N10MPP	\$22.50
SCE-10N1006NKLP	\$87.00	10.00 x 10.00 x 6.00	PDF	SCE-10N10MP	\$8.75	SCE-10N10MPP	\$22.50
SCE-12N1004NKLP	\$84.00	12.00 x 10.00 x 4.00	PDF	SCE-12N10MP	\$10.00	SCE-12N10MPP	\$25.50
SCE-12N1006NKLP	\$95.00	12.00 x 10.00 x 6.00	PDF	SCE-12N10MP	\$10.00	SCE-12N10MPP	\$25.50
SCE-12N1204NKLP	\$92.00	12.00 x 12.00 x 4.00	PDF	SCE-12N12MP	\$12.00	SCE-12N12MPP	\$26.50
SCE-12N1206NKLP	\$104.00	12.00 x 12.00 x 6.00	PDF	SCE-12N12MP	\$12.00	SCE-12N12MPP	\$26.50
SCE-12N1208NKLP	\$116.00	12.00 x 12.00 x 8.00	PDF	SCE-12N12MP	\$12.00	SCE-12N12MPP	\$26.50
SCE-14N1204NKLP	\$100.00	14.00 x 12.00 x 4.00	PDF	SCE-14N12MP	\$13.25	SCE-14N12MPP	\$29.00
SCE-14N1206NKLP	\$113.00	14.00 x 12.00 x 6.00	PDF	SCE-14N12MP	\$13.25	SCE-14N12MPP	\$29.00
SCE-14N1208NKLP	\$126.00	14.00 x 12.00 x 8.00	PDF	SCE-14N12MP	\$13.25	SCE-14N12MPP	\$29.00
SCE-16N1206NKLP	\$170.00	16.00 x 12.00 x 6.00	PDF	SCE-16N12MP	\$19.50	SCE-16N12MPP	\$32.50
SCE-16N1208NKLP	\$185.00	16.00 x 12.00 x 8.00	PDF	SCE-16N12MP	\$19.50	SCE-16N12MPP	\$32.50
SCE-16N1606NKLP	\$190.00	16.00 x 16.00 x 6.00	PDF	SCE-16N16MP	\$32.00	SCE-16N16MPP	\$38.00
SCE-16N1608NKLP	\$206.00	16.00 x 16.00 x 8.00	PDF	SCE-16N16MP	\$32.00	SCE-16N16MPP	\$38.00
SCE-20N1606NKLP	\$210.00	20.00 x 16.00 x 6.00	PDF	SCE-20N16MP	\$36.50	SCE-20N16MPP	\$44.50
SCE-20N1608NKLP	\$229.00	20.00 x 16.00 x 8.00	PDF	SCE-20N16MP	\$36.50	SCE-20N16MPP	\$44.50
SCE-20N2006NKLP	\$230.00	20.00 x 20.00 x 6.00	PDF	SCE-20N20MP	\$46.50	SCE-20N20MPP	\$51.00
SCE-20N2008NKLP	\$252.00	20.00 x 20.00 x 8.00	PDF	SCE-20N20MP	\$46.50	SCE-20N20MPP	\$51.00
SCE-24N2006NKLP	\$255.00	24.00 x 20.00 x 6.00	PDF	SCE-24N20MP	\$53.00	SCE-24N20MPP	\$61.00
SCE-24N2008NKLP	\$279.00	24.00 x 20.00 x 8.00	PDF	SCE-24N20MP	\$53.00	SCE-24N20MPP	\$61.00
SCE-30N2406NKLP	\$287.00	30.00 x 24.00 x 6.00	PDF	SCE-30N24MP	\$74.00	SCE-30N24MPP	\$114.00
SCE-30N2408NKLP	\$319.00	30.00 x 24.00 x 8.00	PDF	SCE-30N24MP	\$74.00	SCE-30N24MPP	\$114.00
SCE-30N3008NKLP	\$534.00	30.00 x 30.00 x 8.00	PDF	SCE-30N30MP	\$97.00	SCE-30N30MPP	\$143.00

Note: Dimensions in inches