



Pneumatic Fitting Accessories

NITRA Blowguns (or nozzles) are available in heavy duty palm type with safety tip, pistol grips (both aluminum and plastic).

Features

- Maximum input pressure of 120 psi
- Thread size on inlet 1/4 NPT female

NITRA Pneumatic Blow Guns					
Part No.	Price	Description	OSHA Directive No. 100-1	Parts Per Pkg	Weight
HBG-01	\$10.50	Pneumatic blow gun, heavy duty palm type with safety tip, 1/4 inch FNPT connection	yes	1	0.4
HBG-02	\$7.75	Pneumatic blow gun, plastic pistol grip with 5 inch nozzle, 1/4 inch FNPT connection	no	1	0.3
HBG-04	\$13.00	Pneumatic blow gun, cast aluminum pistol grip with 6 inch nozzle, 1/4 inch FNPT connection	no	1	1.0

O.S.H.A. Certification – Blow Gun HBG-01, conforms to the requirements of Compressed Air Standards as currently described in the U.S. Bureau of Labor Standards, standard 1910.242 (OSHA directive STD01-13-001), when pressurized at the inlet to a maximum of 100 PSIG.



HBG-01



HBG-02



HBG-04

NITRA commercial grade thread sealant tape is made with 100% virgin PTFE for strong chemical resistance. Thread sealant color is white and is USDA and FDA compliant.



NITRA PTFE Thread Sealing Tape				
Part No.	Price	Description	Parts Per Pkg	Weight
TS12-260	\$4.75	NITRA pneumatic PTFE thread sealing tape for use with pipe thread connections. 1/2 inch wide by 260 inch long roll.	1	0.02