



# Pneumatic Fitting Accessories

**NITRA** Blowguns (or nozzles) are available in heavy duty palm type with safety tip, pistol grips (both aluminum and plastic), a pocket (pencil) type, and plastic grip with flexible nozzles in various lengths.

## Features

- Maximum input pressure of 120 psi
- Thread size on inlet 1/4 NPT female (with exception of pocket model which has 1/4" male industrial interchange) quick disconnect

NITRA™ Pneumatic Blow Guns					
Part No.	Price	Description	OSHA Directive No. 100-1	Parts Per Pkg	Weight
<b>HBG-01</b>	\$7.50	Pneumatic blow gun, heavy duty palm type with safety tip, 1/4 inch FNPT connection	yes	1	0.4
<b>HBG-02</b>	\$5.75	Pneumatic blow gun, plastic pistol grip with 5 inch nozzle, 1/4 inch FNPT connection	no	1	0.3
<b>HBG-03</b>	No Match!	Pneumatic pocket blow gun with twist on/off valve, 1/4 inch industrial interchange quick-disconnect plug	no	1	0.4
<b>HBG-04</b>	\$9.75	Pneumatic blow gun, cast aluminum pistol grip with 6 inch nozzle, 1/4 inch FNPT connection	no	1	1.0
<b>HBG-05</b>	\$15.00	Pneumatic blow gun, plastic pistol grip with 4 inch flexible nozzle, 1/4 inch FNPT connection	yes	1	0.4
<b>HBG-06</b>	\$16.00	Pneumatic blow gun, plastic pistol grip with 8 inch flexible nozzle, 1/4 inch FNPT connection	yes	1	0.4
<b>HBG-07</b>	\$18.00	Pneumatic blow gun, plastic pistol grip with 12 inch flexible nozzle, 1/4 inch FNPT connection	yes	1	0.5
<b>HBG-08</b>	\$22.50	Pneumatic blow gun, plastic pistol grip with 16 inch flexible nozzle, 1/4 inch FNPT connection	yes	1	0.6

*O.S.H.A. Certification – Blow Guns HBG-01, -05, -06, -07, and -08 conform to the requirements of Compressed Air Standards as currently described in the U.S. Bureau of Labor Standards, standard 1910.242 (OSHA directive STD01-13-001), when pressurized at the inlet to a maximum of 100 PSIG.*



**HBG-01**



**HBG-02**



**HBG-03**



**HBG-04**



**HBG-05**



**HBG-06**



**HBG-07**



**HBG-08**

**NITRA** commercial grade thread sealant tape is made with 100% virgin PTFE for strong chemical resistance. Thread sealant color is white and is USDA and FDA compliant.



NITRA™ PTFE Thread Sealing Tape				
Part No.	Price	Description	Parts Per Pkg	Weight
<b>TS12-260</b>	\$1.25	NITRA pneumatic PTFE thread sealing tape for use with pipe thread connections. 1/2 inch wide by 260 inch long roll.	1	0.02