



# Pneumatic Fitting Accessories

**NITRA** Blowguns (or nozzles) are available in heavy duty palm type with safety tip, pistol grips (both aluminum and plastic).

## Features

- Maximum input pressure of 120 psi
- Thread size on inlet 1/4 NPT female

| NITRA™ Pneumatic Blow Guns |         |  |                          |               |        |
|----------------------------|---------|--|--------------------------|---------------|--------|
| Part No.                   | Price   | Description  | OSHA Directive No. 100-1 | Parts Per Pkg | Weight |
| <b>HBG-01</b>              | \$8.50  | Pneumatic blow gun, heavy duty palm type with safety tip, 1/4 inch FNPT connection         | yes                      | 1             | 0.4    |
| <b>HBG-02</b>              | \$6.50  | Pneumatic blow gun, plastic pistol grip with 5 inch nozzle, 1/4 inch FNPT connection       | no                       | 1             | 0.3    |
| <b>HBG-04</b>              | \$10.50 | Pneumatic blow gun, cast aluminum pistol grip with 6 inch nozzle, 1/4 inch FNPT connection | no                       | 1             | 1.0    |

*O.S.H.A. Certification – Blow Gun HBG-01, conforms to the requirements of Compressed Air Standards as currently described in the U.S. Bureau of Labor Standards, standard 1910.242 (OSHA directive STD01-13-001), when pressurized at the inlet to a maximum of 100 PSIG.*



**HBG-01**



**HBG-02**



**HBG-03**



**HBG-04**

**NITRA** commercial grade thread sealant tape is made with 100% virgin PTFE for strong chemical resistance. Thread sealant color is white and is USDA and FDA compliant.



| NITRA™ PTFE Thread Sealing Tape |        |   |               |        |
|---------------------------------|--------|---|---------------|--------|
| Part No.                        | Price  | Description   | Parts Per Pkg | Weight |
| <b>TS12-260</b>                 | \$3.75 | NITRA pneumatic PTFE thread sealing tape for use with pipe thread connections. 1/2 inch wide by 260 inch long roll. | 1             | 0.02   |