



Nickel-Plated Brass Push-to-Connect Fittings

Part No. [US532-B](#)

NITRA pneumatic push-to-connect union straight fittings with nickel-plated brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

NITRA™ Nickel-Plated Brass Union Straight					
Imperial Tube					
Part No.	Size	Price	Drawing Link	Qty. per pack	Weight (lb)
US532-B	(2) 5/32in (4mm) push-to-connect	\$12.50	PDF	5	0.09
US14-B	(2) 1/4in push-to-connect	\$14.50	PDF	5	0.14
US38-B	(2) 3/8in push-to-connect	\$21.50	PDF	5	0.26
US12-B	(2) 1/2in push-to-connect	\$25.50	PDF	5	0.4
Metric Tube					
US6M-B	(2) 6mm push-to-connect	\$14.00	PDF	5	0.14
US8M-B	(2) 5/16in (8mm) push-to-connect	\$17.50	PDF	5	0.18
US10M-B	(2) 10mm push-to-connect	\$19.00	PDF	5	0.25

NITRA pneumatic push-to-connect union straight reducer fittings with nickel-plated brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

Part No. [UR14-532-B](#)

NITRA™ Nickel-Plated Brass Union Straight Reducer					
Imperial Tube					
Part No.	Size	Price	Drawing Link	Qty. per pack	Weight (lb)
UR14-532-B	1/4in push-to-connect x 5/32in (4mm) push-to-connect	\$15.00	PDF	5	0.11
UR516-14-B	5/16in (8mm) push-to-connect x 1/4in push-to-connect	\$21.50	PDF	5	0.18
UR38-516-B	3/8in push-to-connect x 5/16in (8mm) push-to-connect	\$26.00	PDF	5	0.23
UR38-14-B	3/8in push-to-connect x 1/4in push-to-connect	\$26.00	PDF	5	0.21
Hybrid Imperial to Metric Tube					
UR14-6M-B	1/4in push-to-connect x 6mm push-to-connect	\$15.00	PDF	5	0.15
UR38-6M-B	3/8in push-to-connect x 6mm push-to-connect	\$26.00	PDF	5	0.22
UR38-10M-B	3/8in push-to-connect x 10mm push-to-connect	\$26.50	PDF	5	0.25
Metric Tube					
UR6M-4M-B	6mm push-to-connect x 5/32in (4mm) push-to-connect	\$15.00	PDF	5	0.12
UR8M-6M-B	5/16in (8mm) push-to-connect x 6mm push-to-connect	\$21.50	PDF	5	0.16




Nickel-Plated Brass Push-to-Connect Fittings


NITRA nickel-plated brass push-to-connect fittings are an excellent choice for many industrial applications. They have an attractive, easily maintained finish and have a higher pressure and temperature rating when compared to resin fittings.

Features

- Large selection of fitting configurations
- Inch and metric sizes available
- Hybrid Inch to metric conversion fittings available
- NPT, BSPT (R) and BSPP (G) threads available
- Nickel-plated brass bodies, threads and release rings
- Threaded elbow and tee bodies can be rotated after installation
- For use with air and water
- Working pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)



Ideal for washdown and harsh environments



Fitting Cut-away Diagram