





Quick-Disconnect Swivel Fittings

Features

- Two independent-rotation points allow a full 360° circular rotation and 45° angled rotation for better swivel action vs. traditional swivel fittings
- Prevents kinking of and strain on the supply line
- Lightweight, streamlined design
- Chrome-plated steel construction for long service life
- Thread sealant supplied on all male fittings
- Maximum pressure of 145 psi



45° Swivel Design



HS14F-14M

| NITRA™ 1/4 in. NPT Swivel Fittings | | | | |
|------------------------------------|---------|---|---------------|--------------|
| Part No. | Price | Description | Parts Per Pkg | Weight (lbs) |
| HS14F-14M | \$26.00 | Swivel fitting, chrome plated steel, 1/4 inch female NPT and 1/4 inch male NPT threaded connections | 1 | 0.2 |



HSP38-14M-S

| NITRA™ Quick-Disconnect Plug to NPT Swivel Fittings | | | | |
|---|---------|--|---------------|--------------|
| Part No. | Price | Description | Parts Per Pkg | Weight (lbs) |
| HSP14-14M-S | \$27.00 | Quick-disconnect swivel fitting, chrome plated steel, 1/4 inch industrial interchange plug and 1/4 inch male NPT threaded connection | 1 | 0.2 |
| HSP38-14M-S | \$27.00 | Quick-disconnect swivel fitting, chrome plated steel, 3/8 inch industrial interchange plug and 1/4 inch male NPT threaded connection | 1 | 0.2 |
| HSP38-38M-S | \$30.00 | Quick-disconnect swivel fitting, chrome plated steel, 3/8 inch industrial interchange plug and 3/8 inch male NPT threaded connection | 1 | 0.2 |
| HSP14-14M-T | \$30.00 | Quick-disconnect swivel fitting, chrome plated steel, 1/4 inch ARO 210 plug and 1/4 inch male NPT threaded connection | 1 | 0.1 |
| HSP14-14M-U | \$30.00 | Quick-disconnect swivel fitting, chrome plated steel, 1/4 inch Truflate plug and 1/4 inch male NPT threaded connection | 1 | 0.1 |