Heartland Series Enclosure Accessories

Heartland Series – Enclosure Pole Mount Kits

Part Number	Price	For Pole Diameter	Fits Enclosure Width
PM6-8		3.00 -12.00 [76- 305]	AH66*, AH86*, AHF66*, AHF86*, AH88*, AH108*, AHF88* and AHF108*
PM10-12			AH1010*, AH1210*, AHF1010*, AHF1210*, AHWD10106, AHWD12106, AH1412*, AHF1412* and AHWD14126
PM14-16			AH1614*, AHF1614*, AHWD16148, AH1816*, AH2016*, AHF1816*, AHF2016*, AHWD181610 and AHWD20168
PM18-24			AH2424* and AHWD242410

Note: Dimensions in inches [millimeters].

PM14-16

REV60

REV80

Heartland Series – Enclosure Vents

Part Number	Price	Description
REAH-V60		vent, 60mm, polycarbonate, maintains NEMA 3R rating.
REAH-V80		vent, 80mm, polycarbonate, not UL rated, enclosure is NEMA 1 when vent is installed

Heartland Series Enclosure Accessories

Enclosure Latch Kits

Part Number	*Price*	*Description*
AHLKSS		latch, replacement, quick-release, 304 stainless steel. Package of 2.
AHLK		latch, replacement, quick-release, polycarbonate. Package of 2.

AHLKSS

AHLK

Accessory Kit

Part Number	*Price*	*Description*
AHAK		mounting feet kit, polycarbonate. Includes (4) mounting feet and mounting hardware.

AHAK

Enclosure Replacement Fasteners

Part Number	*Price*	*Description*
AHSNK		slot nut kit, #10-32 UNF x 0.375in, Phillips pan head, zinc plated steel. Package of 2. Includes screw and galvanized steel slot nut.
AHTSKSS		thumb screw, replacement, #10-32 UNF x 0.375in, stainless steel. Package of 2. Nylon washer included.
AHTSKAL		thumb screw, replacement, #10-32 UNF x 0.375in, aluminum. Package of 2. Nylon washer included.
RE2PKTBS		trilobular self-tapping screw, replacement, #10-14 x 0.375in, Phillips pan head, aluminum. Package of 2.

AHSNK

AHTSKSS

AHTSKAL

RE2PKTBS

Enclosure Swing Panel Mounts

Part Number	*Price*	*Description*
AHSPM		AttaBox Heartland series swing panel bracket, polycarbonate. Package of 4. For use with Heartland series enclosures. Mounting screws included.

AHSPM

Heartland Series Enclosure Accessories

Mounting Flanges

Part Number	Price	Description
MFK6		mounting flanges, replacement, polycarbonate. For use with AH66*, AH86*, AHF66* and AHF86* enclosures. Includes (2) mounting flanges and mounting hardware.
MFK8		mounting flanges, replacement, polycarbonate. For use with AH88*, AH108*, AHF88* and AHF108* enclosures. Includes (2) mounting flanges and mounting hardware.
MFK10		mounting flanges, replacement, polycarbonate. For use with AH1010*, AH1210*, AHF1010*, AHF1210*, AHWD10106 and AHWD12106 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK12		mounting flanges, replacement, polycarbonate. For use with AH1412*, AHF1412* and AHWD14126 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK14		mounting flanges, replacement, polycarbonate. For use with AH1614*, AHF1614* and AHWD16148 enclosures. Includes (2) mounting flanges and mounting hardware.
MFK16		mounting flanges, replacement, polycarbonate. For use with AH1816*, AH2016*, AHF1816*, AHF2016*, AHWD181610 and AHWD20168 enclosures. Includes (2) mounting flanges and mounting hardware.

MFK6

Internal Shelf

Part Number	Price	Description
WD105		shelf, weight distribution, 10 x 5in, aluminum. (2) screws and (2) slot nuts included.
WD106		shelf, weight distribution, 10 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD12		shelf, weight distribution, 12 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD14		shelf, weight distribution, 14 x 6in, aluminum. (2) screws and (2) slot nuts included.
WD168		shelf, weight distribution, 16 x 8in, aluminum. (2) screws and (2) slot nuts included.
WD1610		shelf, weight distribution, 16 x 10in, aluminum. (2) screws and (2) slot nuts included.
WD24		shelf, weight distribution, 24 x 10in, aluminum. (2) screws and (2) slot nuts included.

WD106

Din Rail

Part Number	Price	Length	For use with
AH6DR		4.9in	AH6*, AH86*, AHF6* and AHF86* enclosures
AH8DR		6.9in	AH8*, AH108*, AHF8* and AHF108* enclosures
AH10DR		8.9in	AH10*, AH12*, AHF10*, AHF12*, AHWD10106 and AHWD12106 enclosures
AH12DR		10.8in	AH12*, AH14*, AHF12*, AHF14* and AHWD14126 enclosures
AH14DR		12.8in	AH14*, AH16*, AHF14*, AHF16* and AHWD16148 enclosures
AH16DR		14.7in	AH16*, AH18*, AH20*, AHF16*, AHF18*, AHF20*, AHWD181610 and AHWD20168 enclosures
AH18DR		16.7in	AH18* and AHF18* enclosures
AH20DR		18.6in	AH20* and AHF20* enclosures
AH24DR		22.5in	AH24* and AHWD242410 enclosures

AH8DR