

Subpanels for Freedom, MachoBox and Centurion Series Fiberglass Enclosures



Carbon steel subpanels

- Material: Carbon steel
- Finish: White polyester powder finish

Fiberglass subpanels

- Material: Fiberglass reinforced polyester (FRP)
- Color: Gray

Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt(lb)
BP64CS	<--->	4.88 x 2.88 x 0.075 [124 x 73 x 1.9]	6 x 4	0.3
BP66CS	<--->	4.88 x 4.88 x 0.075 [124 x 124 x 1.9]	6 x 6	0.5
BP76CS	Retired	6.00 x 4.88 x 0.075 [152 x 124 x 1.9]	7 x 6	0.6
BP86CS	<--->	6.75 x 4.88 x 0.075 [152 x 124 x 1.9]	8 x 6	0.8
BP88CS	<--->	6.88 x 6.88 x 0.075 [175 x 175 x 1.9]	8 x 8	0.8
BP96CS	Retired	8.25 x 4.88 x 0.075 [175 x 124 x 1.9]	9 x 6	0.9
BP108CS	<--->	8.75 x 6.88 x 0.075 [225 x 175 x 1.9]	10 x 8	1.3
BP1210CS	<--->	10.88 x 8.75 x 0.075 [276 x 225 x 1.9]	12 x 10	2.1
BP1412CS	<--->	12.88 x 10.88 x 0.075 [327 x 276 x 1.9]	14 x 12	3.0
BP1614CS	<--->	14.88 x 12.88 x 0.075 [378 x 327 x 1.9]	16 x 14	4.1
BP1816CS	<--->	16.88 x 14.88 x 0.075 [429 x 378 x 1.9]	18 x 16	5.4
BPM2016CS	<--->	18.88 x 14.88 x 0.075 [479 x 378 x 1.9]	20 x 16	6.1
BPM2020CS	<--->	18.00 x 18.00 x 0.105 [457 x 457 x 2.7]	20 x 20	9.4
BPM2420CS	<--->	22.00 x 18.00 x 0.105 [558 x 457 x 2.7]	24 x 20	11
BPM2424CS	<--->	22.00 x 22.00 x 0.105 [558 x 558 x 2.7]	24 x 24	22

Note: Dimensions in inches [millimeters].

Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt.(lb)
BP64FG	Retired	4.88 x 2.88 x 0.13 [124 x 73 x 3.2]	6 x 4	0.1
BP66FG	Retired	4.88 x 4.88 x 0.13 [124 x 124 x 3.2]	6 x 6	0.2
BP86FG	<--->	6.88 x 4.88 x 0.13 [175 x 124 x 3.2]	8 x 6	0.3
BP88FG	Retired	6.88 x 6.88 x 0.13 [175 x 175 x 3.2]	8 x 8	0.3
BP108FG	<--->	8.88 x 6.88 x 0.13 [225 x 175 x 3.2]	10 x 8	0.5
BP1210FG	<--->	10.88 x 8.88 x 0.13 [276 x 225 x 3.2]	12 x 10	0.9
BP1412FG	<--->	12.88 x 10.88 x 0.13 [327 x 276 x 3.2]	14 x 12	1.0
BP1614FG	<--->	14.88 x 12.88 x 0.13 [378 x 327 x 3.2]	16 x 14	0.8
BP1816FG	<--->	16.88 x 14.88 x 0.13 [429 x 378 x 3.2]	18 x 16	2.0
BPM2016FG	Retired	18.88 x 14.88 x 0.13 [479 x 378 x 3.2]	20 x 16	2.2
BPM2020FG	Retired	18.00 x 18.00 x 0.13 [457 x 457 x 3.2]	20 x 20	2.3
BPM2420FG	Retired	22.00 x 18.00 x 0.13 [558 x 457 x 3.2]	24 x 20	2.8
BPM2424FG	Retired	22.00 x 22.00 x 0.13 [558 x 558 x 3.2]	24 x 24	3.5

Note: Dimensions in inches [millimeters].

Subpanels for Freedom, MachoBox and Centurion Series Fiberglass Enclosures

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.




AttaBox
A ROBROY ENCLOSURES™ BRAND

Aluminum subpanels

- Material: 3003H14 aluminum
- Finish: Mill

Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt. (lb)
BP64A	<--->	4.88 x 2.88 x 0.081 [124 x 73 x 2.0]	6 x 4	0.1
BP66A	<--->	4.88 x 4.88 x 0.081 [124 x 124 x 2.0]	6 x 6	0.2
BP86A	<--->	6.88 x 4.88 x 0.081 [175 x 124 x 2.0]	8 x 6	0.3
BP108A	<--->	8.88 x 6.88 x 0.081 [225 x 175 x 2.0]	10 x 8	0.5
BP1010A	<--->	8.88 x 8.88 x 0.081 [225 x 225 x 2.0]	10 x 10	4.3
BP1210A	<--->	10.88 x 8.88 x 0.081 [276 x 225 x 2.0]	12 x 10	0.8
BP1412A	<--->	12.88 x 10.88 x 0.081 [327 x 276 x 2.0]	14 x 12	1.1
BP1614A	<--->	14.88 x 12.88 x 0.081 [378 x 327 x 2.0]	16 x 14	1.5
BP1816A	<--->	16.88 x 14.88 x 0.081 [429 x 378 x 2.0]	18 x 16	2.5
BPM2016A	<--->	18.88 x 14.88 x 0.081 [479 x 378 x 2.0]	20 x 16	2.4
BPM2020A	<--->	18.00 x 18.00 x 0.129 [457 x 457 x 3.3]	20 x 20	3.7
BPM2420A	<--->	22.00 x 18.00 x 0.129 [558 x 457 x 3.3]	24 x 20	4.5
BPM2424A	<--->	22.00 x 22.00 x 0.129 [558 x 558 x 3.3]	24 x 24	5.4
BPM3024A	<--->	27.00 x 21.00 x 0.129 [686 x 533 x 3.3]	30 x 24	7.0

Note: Dimensions in inches (millimeters).




Aluminum swing-out panel

- Swing-out panel with 8 swing-panel mounts
- Works with 30 x 24 in [762 x 610 mm] and 24 x 30 in [610 x 762 mm] MachoBox series enclosures

Part Number	Price	Panel Size HxWxD	Enclosure Nominal Size HxW	Wt. (lb)
M3024SPK	Retired	27.00 x 21.00 X 0.129 [686 X 533 X 3.3]	30 x 24	11

Dimensions



Subpanels for Triton Series Fiberglass Enclosures



AttaBox
A ROBROY ENCLOSURES™ BRAND



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

Carbon steel subpanels

- Material: Carbon steel
- Finish: White polyester powder

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Panel Type	Formed Height (F)	Wt. (lb)	
BPT1610CS	Retired	13.00 x 8.50 x 0.105 [330 x 216 x 2.7]	16 x 10	Flat	—	3.3	
BPT2016CS	<--->	17.00 x 13.00 x 0.105 [432 x 330 x 2.7]	20 x 16	Flat		6.7	
BPT2412CS	Retired	21.00 x 9.00 x 0.105 [533 x 229 x 2.7]	24 x 12	Flat		8.7	
BPT2420CS	<--->	21.00 x 17.00 x 0.105 [533 x 432 x 2.7]	24 x 20	Flat		11	
BPT2424CS	<--->	21.00 x 21.00 x 0.105 [533 x 533 x 2.7]	24 x 24	Flat		13	
BPT3020CS	Retired	27.00 x 17.00 x 0.105 [686 x 432 x 2.7]	30 x 20	Flat		14	
BPT3024CS	<--->	27.00 x 21.00 x 0.105 [686 x 533 x 2.7]	30 x 24	Flat		17	
BPT3630CS	<--->	33.00 x 27.00 x 0.105 [838 x 686 x 2.7]	36 x 30	Flat		27	
BPT4836CS	<--->	33.00 x 45.00 x 0.105 [838 x 1143 x 2.7]	48 x 36	Formed		41	
BPT6036CS	Retired	57.00 x 33.00 x 0.105 [1448 x 838 x 2.7]	60 x 36	Formed		0.50 in	60
BP2016CD	Retired	16.88 x 13.38 x 0.130 [429 x 340 x 3.3]	20 x 16	Formed		0.81 in	7.3
BP2412CD	Retired	20.88 x 9.38 x 0.13 [530 x 238 x 3.3]	24 x 12	Formed			6.6
BP2424CD	Retired	20.88 x 21.38 x 0.130 [530 x 543 x 3.3]	24 x 24	Formed			14
BP3024CD	Retired	26.88 x 21.38 x 0.130 [683 x 543 x 3.3]	30 x 24	Formed	19		
BP3630CD	Retired	32.88 x 27.38 x 0.135 [835 x 695 x 3.4]	36 x 30	Formed	28		
Note: Dimensions in inches [millimeters].							

Aluminum subpanels

- Material: 3003H14 aluminum
- Finish: Mill

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Panel Type	Formed Height (F)	Wt. (lb)	
BPT1610A	<--->	13.00 x 8.50 x 0.081 [330 x 216 x 2.0]	16 x 10	Flat	—	1.0	
BPT2016A	<--->	17.00 x 13.00 x 0.081 [432 x 330 x 2.0]	20 x 16	Flat		2.0	
BPT2412A	<--->	21.00 x 9.00 x 0.081 [533 x 229 x 2.0]	24 x 12	Flat		4.5	
BPT2420A	<--->	21.00 x 17.00 x 0.129 [533 x 432 x 3.3]	24 x 20	Flat		4.5	
BPT2424A	<--->	21.00 x 21.00 x 0.129 [533 x 533 x 3.3]	24 x 24	Flat		5.5	
BPT3020A	<--->	27.00 x 17.00 x 0.129 [686 x 432 x 3.3]	30 x 20	Flat		5.8	
BPT3024A	<--->	27.00 x 21.00 x 0.129 [686 x 533 x 3.3]	30 x 24	Flat		7.0	
BPT3630A	<--->	33.00 x 27.00 x 0.129 [838 x 686 x 3.3]	36 x 30	Flat		11	
BPT4836A	<--->	33.00 x 45.00 x 0.129 [838 x 1143 x 3.3]	48 x 36	Formed		0.50 in	22
BPT6036A	<--->	57.00 x 33.00 x 0.129 [1448 x 838 x 3.3]	60 x 36	Formed			23
Note: Dimensions in inches [millimeters].							

Subpanels for Triton Series Fiberglass Enclosures

Dimensions

