

BantamBox Series Polycarbonate Enclosures

NEMA 1, 3R, 4, 4X and 12 with Screw Cover



BB060555W



BBCC090603W

Applications

BantamBox offers an all-polycarbonate product with clear or opaque covers. These enclosures include an external flush wall design, unobstructed internal sidewalls, 304 stainless steel cover screws, and watertight seal.

Construction

- Polycarbonate for 1480 in-lb, high impact resistance per UL746C

Gray in color with gloss Finish

- Poured polyurethane seamless gasket provides watertight, dust-tight environmental seal
- Multiple depths available in most sizes
- Flush sides for a perfect fit
- Multiple molded-in bosses for a variety of equipment mounting solutions
- Lift-off cover with 4 screws
- Tightening torque: M4-9 17 lb-in, M6 17-22 lb-in

Listings

- UL/cUL File [UL File E64358]
- NEMA Ratings 1, 3R, 4, 4X, and 12
- IEC 60529 IP66 [UL File 362920]
- Flammability Rating: UL94-V2
- Non-flame propagating
- UV Exposure Rating: UL-f1
- Temperature Range: -40°F to 212°F [-40°C to 100°C]
- Certifications: cULus, REACH, CE, IEC



BantamBox Series Polycarbonate Enclosures

NEMA 1, 3R, 4, 4X and 12 with Screw Cover



Bantam Box Series Polycarbonate Enclosures

<i>Opaque Cover</i>	<i>Price</i>	<i>Clear Cover</i>	<i>Price</i>	<i>Enclosure Overall Size HxWxD</i>	<i>Subpanel</i>	<i>Drawing Link</i>
<u>BB060555W</u>		<u>BBCC060555W</u>		2.56 x 1.97 x 2.17 [65 x 50 x 55]	—	PDF
<u>BB080805W</u>		<u>BBCC080805W</u>		3.23 x 3.15 x 2.17 [82 x 80 x 55]	<u>BPB0808P</u>	PDF
<u>BB080809W</u>		—	—	3.23 x 3.15 x 3.35 [82 x 80 x 85]	<u>BPB0808P</u>	PDF
<u>BB080810W</u>		—	—	3.23 x 3.15 x 3.74 [82 x 80 x 95]	<u>BPB0808P</u>	PDF
<u>BB090603W</u>		<u>BBCC090603W</u>		3.86 x 2.52 x 1.46 [98 x 64 x 37]	—	PDF
<u>BB128055W</u>		<u>BBCC128055W</u>		4.72 x 3.15 x 2.17 [120 x 80 x 55]	<u>BPB1280P</u>	PDF
<u>BBR128080W</u>		—	—	4.72 x 3.15 x 3.15 [120 x 80 x 80]	<u>BPB1280P</u>	PDF
<u>BB128010W</u>		—	—	4.72 x 3.15 x 3.94 [120 x 80 x 100]	<u>BPB1280P</u>	PDF
<u>BB121255W</u>		—	—	4.80 x 4.72 x 2.17 [122 x 120 x 55]	<u>BPB1212P</u>	PDF
<u>BB121275W</u>		<u>BBCC121275W</u>		4.80 x 4.72 x 2.95 [122 x 120 x 75]	<u>BPB1212P</u>	PDF
<u>BB121211W</u>		<u>BBCC121211W</u>		4.80 x 4.72 x 4.13 [122 x 120 x 105]	<u>BPB1212P</u>	PDF
<u>BB168055W</u>		—	—	6.30 x 3.15 x 2.17 [160 x 80 x 55]	<u>BPB1680P</u>	PDF
<u>BB168090W</u>		<u>BBCC168090W</u>		6.30 x 3.15 x 3.54 [160 x 80 x 90]	<u>BPB1680P</u>	PDF
<u>BB161255W</u>		<u>BBCC161255W</u>		6.30 x 4.72 x 2.17 [160 x 120 x 55]	<u>BPB1612P</u>	PDF
<u>BB161290W</u>		<u>BBCC161290W</u>		6.30 x 4.72 x 3.54 [160 x 120 x 90]	<u>BPB1612P</u>	PDF
<u>BB161214W</u>		<u>BBCC161214W</u>		6.30 x 4.72 x 5.51 [160 x 120 x 140]	<u>BPB1612P</u>	PDF
<u>BB201275W</u>		<u>BBCC201275W</u>		7.87 x 4.72 x 2.95 [200 x 120 x 75]	<u>BPB2012P</u>	PDF
<u>BB201290W</u>		—	—	7.87 x 4.72 x 3.54 [200 x 120 x 90]	<u>BPB2012P</u>	PDF
<u>BB201510W</u>		<u>BBCC201510W</u>		7.87 x 5.91 x 3.94 [200 x 150 x 100]	<u>BPB2015P</u>	PDF
<u>BB201513W</u>		<u>BBCC201513W</u>		7.87 x 5.91 x 4.92 [200 x 150 x 125]	<u>BPB2015P</u>	PDF
<u>BB251690W</u>		—	—	9.84 x 6.30 x 3.54 [250 x 160 x 90]	<u>BPB2516P</u>	PDF
<u>BB251611W</u>		—	—	9.84 x 6.30 x 4.53 [250 x 160 x 115]	<u>BPB2516P</u>	PDF
<u>BB251612W</u>		<u>BBCC251612W</u>		9.84 x 6.30 x 4.72 [250 x 160 x 120]	<u>BPB2516P</u>	PDF
<u>BB251615W</u>		<u>BBCC251615W</u>		9.84 x 6.30 x 5.91 [250 x 160 x 150]	<u>BPB2516P</u>	PDF

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].

Subpanels for BantamBox Series Enclosures



AttaBox
A ROBROY ENCLOSURES™ BRAND

Phenolic Resin Hard Paper Subpanels

Lightweight, durable and electrically resistant. Includes mounting hardware.



BPB0808P

BantamBox Series Subpanels		
<i>Part Number</i>	<i>Price</i>	<i>Subpanel Size</i>
<u>BPB0808P</u>		2.83 x 2.76 [72 x 70]
<u>BPB1280P</u>		4.33 x 2.76 [110 x 70]
<u>BPB1680P</u>		5.91 x 2.76 [150 x 70]
<u>BPB1212P</u>		4.41 x 4.33 [112 x 110]
<u>BPB1612P</u>		5.94 x 4.41 [151 x 112]
<u>BPB2012P</u>		7.44 x 4.29 [189 x 109]
<u>BPB2015P</u>		7.52 x 5.59 [191 x 142]
<u>BPB2516P</u>		9.53 x 5.98 [242 x 152]

Note: Dimensions in inches [millimeters].