

# Enclosure Accessories – Universal Deep-Hinged Window Door



WADW131602



WADW131602SS

## Applications

The Wiegmann Universal Deep Hinged Door is styled after their N 412 Ultimate Series Enclosures. Doors are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

Deep-hinged window doors provide some protection for HMIs or other operator interface devices that are installed on electrical enclosures. This allows for easy access to the devices with a hinged door and 1/4-turn latches. Viewing windows allow the operator to monitor the devices while the door is latched shut, keeping them protected during operation.

## Construction

- Quarter-turn style latching for easy access
- Latch type can be changed using N41214 series latches (sold separately)
- Concealed hinges with removable pins
- Fabricated from 14-gauge carbon steel or 14-gauge 304 stainless steel

## Finish

- Carbon steel models have an ANSI 61 gray light-textured polyester powder finish
- Stainless steel models have a #3 intermediate polished finish
- Polycarbonate viewing window for clear visibility
- Drill template and mounting hardware provided
- Door and mounting surface are sealed with poured-in-place polyurethane gasket

## Listings

- UL Recognized type 3R, 4, 12, and 4X (SS only) [UL File E64791]
- IP66
- CSA Type 3R, 4, 12 and 4X (SS only) [CSA File 222873]



Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1-10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Enclosure Accessories – Universal Deep-Hinged Window Door									
ANSI 61 Gray Steel	Price	304 Stainless Steel	Price	Height	Width	Depth	Window Height	Window Width	Wt. (lb)
WADW131602	—	WADW131602SS	—	12.75 [324]	15.88 [403]	2.75 [70]	8.68 [220]	9.83 [250]	11.0
WADW150902	Retired	WADW150902SS	Retired	14.75 [375]	9.5 [241]		10.68 [271]	3.41 [87]	8.0
WADW191302	Retired	WADW191302SS	Retired	18.75 [476]	13.5 [343]		14.68 [373]	7.41 [188]	14.0
WADW231302	Retired	WADW231302SS	Retired	22.75 [578]	13.5 [343]		18.68 [474]	7.41 [188]	17.0
WADW231702	Retired	WADW231702SS	Retired	22.75 [578]	17.5 [445]		18.68 [474]	11.41 [290]	21.0
WADW232602	Retired	WADW232602SS	Retired	22.75 [578]	26.25 [667]		18.68 [474]	20.22 [514]	32.0
WADW292002	Retired	WADW292002SS	Retired	28.75 [731]	20.25 [514]		24.68 [627]	14.22 [361]	31.0

Notes: Dimensions in inches [millimeters].  
Cutout dimension: Height - 3 [76], Width - 3 [76]

## Dimensions

