



Drive Couplings

Accessories – Bore Reducers



Features

- For use in all SureMotion drive coupling hubs to reduce bore size
- Split-collar design with 2 set screw flats will not mark shaft
- 25% greater holding power than standard split collar
- Hardened stainless steel

Bore Reducers – Stainless Steel Clamping Type						
Part Number	Price	Outside Diameter		Inside Diameter		Length
		Nominal	Actual	Nominal	Actual	
DC-BRS04-02		1/4 in	0.250 in	1/8 in	0.125 in	0.221 in
DC-BRS04-04M				4mm	4mm	
DC-BRS04-03				3/16 in	0.1875 in	
DC-BRS04-05M				5mm	5mm	
DC-BRS08-06M		1/2 in	0.500 in	6mm	6mm	0.449 in
DC-BRS08-04				1/4 in	0.25 in	
DC-BRS08-05				5/16 in	0.3125 in	
DC-BRS08-08M				8mm	8mm	
DC-BRS08-06				3/8 in	0.375 in	
DC-BRS08-10M		5/8 in	0.625 in	10mm	10mm	0.460 in
DC-BRS10-10M				10mm	10mm	
DC-BRS10-07				7/16 in	0.4375 in	
DC-BRS10-12M				12mm	12mm	
DC-BRS10-08				1/2 in	0.5 in	
DC-BRS10-14M				14mm	14mm	
DC-BRS10-09		3/4 in	0.750 in	9/16 in	0.5625 in	0.646 in
DC-BRS12-06				3/8 in	0.375 in	
DC-BRS12-12M				12mm	12mm	
DC-BRS12-08				1/2 in	0.5 in	
DC-BRS12-10				5/8 in	0.625 in	
DC-BRS12-16M				16mm	16mm	
DC-BRS12-11		7/8 in	0.875 in	11/16 in	0.6875 in	0.755 in
DC-BRS14-14M				14mm	14mm	
DC-BRS14-10				5/8 in	0.625 in	
DC-BRS14-16M				16mm	16mm	
DC-BRS14-11				11/16 in	0.6875 in	
DC-BRS14-18M				18mm	18mm	
DC-BRS14-12		1 in	1.000 in	3/4 in	0.75 in	0.773 in
DC-BRS16-10				5/8 in	0.625 in	
DC-BRS16-18M				18mm	18mm	
DC-BRS16-12				3/4 in	0.75 in	
DC-BRS16-20M				20mm	20mm	
DC-BRS16-13				13/16 in	0.8125 in	
DC-BRS16-14		1-1/4 in	1.250 in	7/8 in	0.875 in	0.793 in
DC-BRS20-22M				22mm	22mm	
DC-BRS20-24M				24mm	24mm	
DC-BRS20-25M				25mm	25mm	
DC-BRS20-16				1 in	1.0 in	
DC-BRS20-17				1-1/16 in	1.0625 in	
DC-BRS20-18				1-1/8 in	1.125 in	