

Enclosure Subpanels



Subpanels for Two-Door Floor-Mount Enclosures

- Subpanels are fabricated from 10-gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor-mount enclosures and some double-door wall-mount enclosures



Subpanels for Two-door Floor-Mount Enclosures			
Painted Steel	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<u>NPDD4242</u>		42 x 42	39.00 x 39.00 [991 x 991]
<u>NPDD4842</u>		48 x 42	45.00 x 39.00 [1143 x 991]
<u>NPDD4848</u>		48 x 48	44.00 x 44.00 [1118 x 1118]
<u>NPDD5442</u>		54 x 42	50.00 x 38.00 [1270 x 965]
<u>NPDD6048</u>		60 x 48	44.00 x 56.00 [1118 x 1422]
<u>NPDD6060</u>		60 x 60	56.00 x 56.00 [1422 x 1422]
<u>NPDD7260</u>		72 x 60	56.00 x 68.00 [1422 x 1727]
<u>NPDD7272</u>		72 x 72	68.00 x 68.00 [1727 x 1727]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing. *Some floor-mount enclosures may be up to 2 in [51 mm] taller than height listed in this table. Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions listed in this table.			

Dimensions

