



GCV Valves Replacement Coils

Water Valve Accessory Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS4YN02</u>	120 VAC	10 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4YN04</u>	240 VAC	10 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4YN24</u>	24 VAC	10 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4YN16</u>	24 VDC	10 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves		0.6
	<u>HS4GN02A24</u>	120 VAC	10 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4GN04A24</u>	240 VAC	10 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4GN24A24</u>	24 VAC	10 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S201, NS201, S301 and NS301 valves		0.6
	<u>HS4GN16A24</u>	24 VDC	10 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves		0.6
	<u>HS3YN02</u>	120 VAC	8 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S211, NS211 and NS71 valves		0.5
	<u>HS3YN04</u>	240 VAC	8 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S211, NS211 and NS71 valves		0.5
	<u>HS3YN24</u>	24 VAC	8 W	Class H: 180 °C (356 °F)	18 mm (DIN 43650A) style wiring plug	N/A	S211, NS211 and NS71 valves		0.5
	<u>HS3GN02A24</u>	120 VAC	8 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S211, NS211 and NS71 valves		0.5
	<u>HS3GN04A24</u>	240 VAC	8 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S211, NS211 and NS71 valves		0.5
	<u>HS3GN24A24</u>	24 VAC	8 W	Class H: 180 °C (356 °F)	1/2in conduit 24in 18 AWG pigtail	24in	S211, NS211 and NS71 valves		0.5



GCV Valve Replacement Coils

GCV Valve Replacement Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS3GN16A24</u>	24 VDC	9 W	Class H: 180 °C (356 °F)	1/2in conduit w/ 18 AWG pigtail	24in	S211, NS211 and NS71 valves		0.54
	<u>HS3YN16</u>	24VDC	9 W	Class H: 180 °C (356 °F)	18 mm DIN style wiring plug	N/A	S211, NS211 and NS71 valves		0.49