

Perforated Steel Panels for 19-Inch Racks



Application

Install in unused 19 in [483 mm] wide rack space to improve both cooling efficiency and allow 25% air recirculation.

Features


- Fits standard EIA compliant rails.
- Allows 25% airflow through panel.

Construction

- Constructed of 16-gauge steel.
- Finished in smooth powder coat.

Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Perforated Steel Panels for 19-Inch Racks

Gloss Black	RAL7035 Gray	Price	Rack Units	Panel Height	Drawing Link
PPFS19001BK2	PPFS19001LG2		1U	1.75 [44]	PDF
PPFS19003BK2	PPFS19003LG2		2U	3.50 [89]	PDF
PPFS19005BK2	PPFS19005LG2		3U	5.25 [133]	PDF
PPFS19007BK2	PPFS19007LG2		4U	7.00 [178]	PDF
PPFS19008BK2	PPFS19008LG2		5U	8.75 [222]	PDF
PPFS19010BK2	PPFS19010LG2		6U	10.50 [267]	PDF

Note: Dimensions in inches [millimeters].