

# Enclosure Accessories - Hole Seals and Plugs



## Hole Seals for Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in metal enclosures from dirt, dust, oil and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in. conduit actual diameter = 1.315 in.)



### Enclosure Shipping Schedule

Same day

Color indicates shipping lead time in business days.

| Steel Hole Seals with ANSI 61 Gray Polyester Powder | Price   | Stainless Steel Hole Seals with Grained Finish | Price   | Description  | Hole Diameter in [mm] | Wt. [lb] |
|---|---------|--|---------|--|-----------------------|----------|
| <b>WAS050</b>                                       | \$5.50  | <b>WAS050SS</b>                                | \$15.25 | Hubbell-Wiegmann conduit hole seal, 1/2 inch, quick wing nut, oil-resistant gasket           | 0.87 [22]             | 0.1      |
| <b>WAS075</b>                                       | \$7.00  | <b>WAS075SS</b>                                | \$20.00 | Hubbell-Wiegmann conduit hole seal, 3/4 inch, quick wing nut, oil-resistant gasket           | 1.14 [29]             |          |
| <b>WAS100</b>                                       | \$8.25  | <b>WAS100SS</b>                                | \$24.50 | Hubbell-Wiegmann conduit hole seal, 1 inch, quick wing nut, oil-resistant gasket             | 1.38 [35]             |          |
| <b>WAS125</b>                                       | \$10.50 | <b>WAS125SS</b>                                | \$28.00 | Hubbell-Wiegmann conduit hole seal, 1.25 inch, quick wing nut, oil-resistant gasket          | 1.61 [41]             | 0.2      |
| <b>WAS150</b>                                       | \$12.00 | <b>WAS150SS</b>                                | \$32.00 | Hubbell-Wiegmann conduit hole seal, 1.5 inch, quick wing nut, oil-resistant gasket           | 2.00 [51]             |          |
| <b>WAS200</b>                                       | \$13.25 | <b>WAS200SS</b>                                | \$35.00 | Hubbell-Wiegmann conduit hole seal, 2 inch, quick wing nut, oil-resistant gasket             | 2.52 [64]             | 0.3      |
| <b>WAS250</b>                                       | \$17.25 | -  | \$11.50 | Hubbell-Wiegmann conduit hole seal, 2.5 inch, quick wing nut, oil-resistant gasket           | 3.00 [76]             | 0.4      |
| <b>WAS300</b>                                       | \$22.50 | -  | \$11.50 | Hubbell-Wiegmann conduit hole seal, 3 inch, quick wing nut, oil-resistant gasket             | 3.62 [92]             | 0.5      |
| <b>WAS350</b>                                       | \$29.00 | -  | \$11.50 | Hubbell-Wiegmann conduit hole seal, 3.5 inch, quick wing nut, oil-resistant gasket           | 4.13 [105]            |          |
| <b>WAS400</b>                                       | \$37.50 | -  | \$11.50 | Hubbell-Wiegmann conduit hole seal, 4 inch, quick wing nut, oil-resistant gasket             | 4.64 [118]            | 0.6      |
| <b>WASPB</b>  | \$7.50  | <b>WASPBSS</b>                                 | \$20.00 | Hubbell-Wiegmann hole seal, for 30mm pushbutton cutout, quick wing nut, oil-resistant gasket | 1.18 [30]             | 0.1      |
| <b>WASPBG</b>                                       | \$5.50  | <b>WASPBGSS</b>                                | \$14.25 | Hubbell-Wiegmann hole seal, for 22mm pushbutton cutout, quick wing nut, oil-resistant gasket | 0.87 [22]             |          |

Note: Dimensions in inches [millimeters]

# Enclosure Accessories - Hole Seals and Plugs



## Hole Plugs for Non-Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in AttaBox fiberglass enclosures from dirt, dust, oil, and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in. conduit actual diameter = 1.315 in.)



| Hole Plugs           | Price   | Description   | Nominal Hole Diameter Range in [mm] | Wt. [oz] |
|----------------------|---------|---|-------------------------------------|----------|
| <b>REHPSERIES1</b>   | \$3.50  | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2- to 3/4-inch hole in non-metallic enclosure  | 0.50 - 0.81<br>[12.7 - 20.6]        | 2        |
| <b>REHPSERIES1.5</b> | \$4.75  | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 1/2in conduit holes in non-metallic enclosures.                                 | 0.88<br>[22.4]                      | 2        |
| <b>REHPSERIES2</b>   | \$4.00  | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2- to 3/4-inch conduit holes and 22 or 30mm pushbutton holes in non-metallic enclosure | 0.88 - 1.28<br>[22.4 - 32.5]        | 2        |
| <b>REHPSERIES3</b>   | \$6.25  | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1 to 1-1/4 inch conduit holes in non-metallic enclosure                                  | 1.38 - 1.75<br>[35.1 - 44.5]        | 2        |
| <b>REHPSERIES4</b>   | \$8.00  | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1-1/2 to 2-inch conduit holes in non-metallic enclosure                                  | 2.00 - 2.56<br>[50.1 - 65.0]        | 2        |
| <b>REHPSERIES5</b>   | \$14.75 | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 2-1/2in conduit holes in non-metallic enclosures.                               | 3.00<br>[76.2]                      | 2        |
| <b>REHPSERIES6</b>   | \$19.75 | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 3in conduit holes in non-metallic enclosures.                                   | 3.62<br>[92.0]                      | 2        |
| <b>REHPSERIES7</b>   | \$25.50 | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 3-1/2in conduit holes in non-metallic enclosures.                               | 4.12<br>[104.7]                     | 2        |
| <b>REHPSERIES8</b>   | \$33.00 | AttaBox hole plug, fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 4in conduit holes in non-metallic enclosures.                                   | 4.62<br>[117.4]                     | 2        |

## Agency Approvals

- Fiberglass hole plug for UL Types 1, 3R, 4, 4X, 6, 6P, 12 Industrial control panel enclosures.  
[UL File E64358]
- CSA Types 1, 12, 3, 3R, 4, 4X, 6, 6P:  
IEC Code IP66, IP67, IP68  
[CSA File LR069014]

| Enclosure Shipping Schedule                          |            |             |             |
|--|------------|-------------|-------------|
| Same day   | 1 - 5 days | 1 - 15 days | 1 - 20 days |
| Color indicates shipping lead time in business days. |            |             |             |