

RUKO Drill Bits



214214RO

Drill Bit Sets		
Part #	Price	Description
<u>101026USRO</u>		Three-piece Step Drill Bit Set High Speed Steel, bright finish, spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
<u>101026USERO</u>		Three-piece Step Drill Bit Set HSS-Co5 spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
<u>101026USTRO</u>		Three-piece Step Drill Bit Set HSS-TiN coated spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
<u>214850RO</u>		21-piece jobber Length Drill Set Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel, 118 degrees point
<u>214851RO</u>		29-piece jobber Length Drill Set Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel, 118 degrees point.