

KNIPEX® Wire Stripping and Dismantling Tools

Electrician's Pliers

Features

- Designed for gripping and bending wire
- Ideal for cutting soft, medium, and hard wire
- Precision cutting edges induction-hardened to 60 HRC
- Vanadium electric steel; oil-hardened, and tempered

**1301160****1301614SBA**

Wire Stripping and Dismantling Tools								
Part Number	Description	Stripping Capacity	Cutting Capacity Ø		Length	Weight	Pcs/ Pkg	Price
			Med-Hard	Hard				
1301160	4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping	20-18/ 15 / 13 AWG [0.5-0.75 / 1.5 / 2.5 mm ²]	0.10 in [2.5 mm]	0.06 in [1.6 mm]	6.30 in [160 mm]	3.95 oz [112 g]	1	
1301614SBA	4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping	14, 12, 10 AWG [2.1 / 3.3 / 5.3 mm ²]	0.10 in [2.5 mm]	0.06 in [1.6 mm]	6.30 in [160 mm]	3.95 oz [112 g]	1	

Inch dimensions are rounded to the nearest hundredth. HRC refers to Rockwell C Scale.

