

KNIPEX® Pliers Sets and Accessories

KNIPEX® Pliers Sets and Accessories

Pliers Sets and Accessories				
Part Number	Description	Weight	Pcs/Pkg	Price
002005US	Set of 3 high-leverage diagonal cutters; 6¼" diagonal cutter (p/n 7401160SBA), 10" diagonal cutter (p/n 7401250SBA), and 8" angled diagonal cutter (p/n 7421200SBA)	2.15 lb [975 g]	3	
002006US1	Set of 3 Cobra® pliers, non-slip, plastic-coated handles, push-button adjustment, thin jaw profile, self-gripping; 7" (p/n 8701180SBA), 10" (p/n 8701250SBA), and 12" (p/n 8701300SBA) lengths.	2.6 lb [1179 g]	3	
002006US2	Set of 3 Pliers Wrenches, push-button adjustment, box joint, self-ratcheting, non-slip plastic-coated handles, chrome vanadium steel; 7" (p/n 8603180SBA), 10" (p/n 8603250SBA), 12" (p/n 8603300SBA) lengths	2.34 lb [1061 g]	3	
002007US1	Set of 3 Alligator® pliers, chrome vanadium steel, self-gripping, thin jaw profile, non-slip plastic-coated handles; 7" (p/n 8801180SBA), 10" (p/n 8801250SBA), and 12" (p/n 8801300SBA) lengths	2.15 lb [975 g]	3	
002072V01	2-Piece mini pliers set in practical belt pouch. Includes (1) 6" Wrench Pliers (p/n 8603150SBA and (1) 5" (p/n 8701125SBA) mini Cobra® pliers	0.77 lb [349 g]	2	
001101	Twin universal control cabinet key. Two 4-way wheel wrenches connected in a space-saving way with magnets. Includes lock profiles: square (5-6, 7-8, 9-10, 11mm), triangular (7, 8-9, 10-11, 12mm), double-bit (3-5mm), half-moon (6mm), stepped square (6-9mm), reversing bit (slot 1x7mm, cross-recess PH2). Die-cast zinc material.	0.31 lb [140 g]	1	



002005US



002006US1




002006US2



002007US1



002072V01



001101