

KNIPEX® Water Pump Pliers

Raptor™ Pliers - Multiple Slip Joint Spanner

Features

- Smooth parrot jaw design for metric and imperial nuts and screws
- Self-locking from 17 mm to 32 mm
- Zero backlash gripping of metric or imperial hexagonal head screws
- Secure and tight grabbing of bolt heads, even those with rounded edges, rusted nuts or heavily coated workpieces
- Chrome vanadium electric steel, oil-hardened and tempered

Multiple Slip Joint Spanner							
Part Number	Description	Pliers Length	Jaw Opening	Adjustment Positions	Weight	Pcs/Pkg	Price
8741250SBA	Raptor™ pliers - multiple slip joint spanner with non-slip plastic-coated handles	9.84 in [250 mm]	0.39-1.26 in [10-32 mm]	15	11.57 oz [328 g]	1	

Inch dimensions are rounded to the nearest hundredth.




8741250SBA



KNIPEX® Pliers Sets and Accessories

KNIPEX® Pliers Sets and Accessories

Pliers Sets and Accessories				
Part Number	Description	Weight	Pcs/ Pkg	Price
001101	Twin universal control cabinet key. Two 4-way wheel wrenches connected in a space-saving way with magnets. Includes lock profiles: square (5-6, 7-8, 9-10, 11mm), triangular (7, 8-9, 10-11, 12mm), double-bit (3-5mm), half-moon (6mm), stepped square (6-9mm), reversing bit (slot 1x7mm, cross-recess PH2). Die-cast zinc material.	0.31 lb [140 g]	1	



001101