

Machine Taps

Machine Taps

Choose from nine sizes in coarse or fine thread machine taps.

- High-speed steel cobalt-alloyed (HSS-Co5)
- Spiral point
- Chamfer type B, 4-5 threads with progressive tip
- Reinforced shank for through threads



265050UNC

High-Speed Steel Machine Taps											
Unified Coarse Thread	Part #	Pcs/ Pkg	Price	Thread Size	Use With	Unified Fine Thread	Part #	Pcs/ Pkg	Price	Thread Size	Use With
	265040UNC	1		4-40	2149043						
	265060UNC	1		6-32	2149036						
	265080UNC	1		8-32	2149029						
	265100UNC	1		10-24	2149025		265100UNF	1		10-32	2149021
	265120UNC	1		12-24	2149016						
	265014UNC	1		1/4-20	2149007		265014UNF	1		1/4-28	2149003
	265516UNC	1		5/16-18	214900F						
	265038UNC	1		3/8-16	214817 , 250817T						

Drill and Tap Selection Guide					
Machine Screw Size	Tap Drill Size	Drill P/N	Tap P/N	Clearance Hole (in.)	Clearance Drill P/N
#4-40	#43	2149043	265040UNC	0.125	214805 , 250805T , 215805
#4-48	#42	2149042	-265040UNF	0.125	214805 , 250805T , 215805
#5-40	#38	2149038	265050UNC	0.136	2149029
#5-44	#37	2149037	-265040UNF	0.136	2149029
#6-32	#36	2149036	265060UNC	0.149	2149025
#6-40	#33	2149033	-265040UNF	0.149	2149025
#8-32	#29	2149029	265080UNC	0.187	214809 , 250809T , 215809
#8-36	#29	2149029	-265040UNF	0.187	214809 , 250809T , 215809
#10-24	#25	2149025	265100UNC	0.219	214811 , 250811T , 215811
#10-32	#21	2149021	265100UNF	0.219	214811 , 250811T , 215811
#12-24	#16	2149016	-265040UNF	0.234	214812 , 250812T , 215812
#12-28	#14	2149014	265120UNF	0.234	214812 , 250812T , 215812
1/4-20	#7	2149007	265014UNC	0.281	214815 , 250815T , 215815
1/4-28	#3	2149003	265014UNF	0.281	214815 , 250815T , 215815
5/16-18	LTR F	214900F	265516UNC	0.344	214819 , 250819T , 215819
5/16-24	LTR I	214900I	-265040UNF	0.344	214819 , 250819T , 215819
3/8-16	5/16	214817 , 250817T	265038UNC	0.406	214823 , 250823T , 215823
3/8-24	LTR Q	214900Q	-265040UNF	0.406	214823 , 250823T , 215823