

# NEMA 1, 4, 4X, and 12 Hinged Cover Stainless Steel Wiring Trough

## Applications

Designed to protect internal components and wiring from dust, dirt, and water. This trough can be used indoors or outdoors, as well as in corrosive environments.

## Listings

- UL 870 1, 4, 4X and 12
- IEC 60529, IP66
- UL Files E32576, E470978



## Construction

- Trough and cover fabricated from 304 stainless steel or carbon steel
- #3 intermediate polished finish or polyester powder coat
- Seams are continuously-welded and ground smooth
- External clamps and continuous hinge provided
- External mounting feet included
- Cover is sealed with poured-in-place gasket



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 1, 4, 4X, and 12 Hinged Cover Wiring Trough			
Stainless Steel	Price	Enclosure Overall Size HxWxD	Drawing Link
<a href="#">T2212CHSS</a>	—	2.50 x 2.50 x 12.00 [64 x 64 x 305]	<a href="#">PDF</a>
<a href="#">T2218CHSS</a>	Retired	2.50 x 2.50 x 18.00 [64 x 64 x 457]	<a href="#">PDF</a>
<a href="#">T2224CHSS</a>	—	2.50 x 2.50 x 24.00 [64 x 64 x 610]	<a href="#">PDF</a>
<a href="#">T2236CHSS</a>	—	2.50 x 2.50 x 36.00 [64 x 64 x 914]	<a href="#">PDF</a>
<a href="#">T2248CHSS</a>	—	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	<a href="#">PDF</a>
<a href="#">T2260CHSS</a>	Retired	2.50 x 2.50 x 60.00 [64 x 64 x 1524]	<a href="#">PDF</a>
<a href="#">T2272CHSS</a>	—	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	<a href="#">PDF</a>
<a href="#">T4412CHSS</a>	—	4.00 x 4.00 x 12.00 [102 x 102 x 305]	<a href="#">PDF</a>
<a href="#">T4418CHSS</a>	Retired	4.00 x 4.00 x 18.00 [102 x 102 x 457]	<a href="#">PDF</a>
<a href="#">T4424CHSS</a>	—	4.00 x 4.00 x 24.00 [102 x 102 x 610]	<a href="#">PDF</a>
<a href="#">T4430CHSS</a>	Retired	4.00 x 4.00 x 30.00 [102 x 102 x 762]	<a href="#">PDF</a>
<a href="#">T4436CHSS</a>	—	4.00 x 4.00 x 36.00 [102 x 102 x 914]	<a href="#">PDF</a>
<a href="#">T4448CHSS</a>	—	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	<a href="#">PDF</a>
<a href="#">T4460CHSS</a>	Retired	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	<a href="#">PDF</a>
<a href="#">T4472CHSS</a>	—	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	<a href="#">PDF</a>
<a href="#">T6612CHSS</a>	—	6.00 x 6.00 x 12.00 [152 x 152 x 305]	<a href="#">PDF</a>
<a href="#">T6618CHSS</a>	Retired	6.00 x 6.00 x 18.00 [152 x 152 x 457]	<a href="#">PDF</a>
<a href="#">T6624CHSS</a>	—	6.00 x 6.00 x 24.00 [152 x 152 x 610]	<a href="#">PDF</a>
<a href="#">T6630CHSS</a>	Retired	6.00 x 6.00 x 30.00 [152 x 152 x 762]	<a href="#">PDF</a>
<a href="#">T6636CHSS</a>	—	6.00 x 6.00 x 36.00 [152 x 152 x 914]	<a href="#">PDF</a>
<a href="#">T6648CHSS</a>	—	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	<a href="#">PDF</a>
<a href="#">T6660CHSS</a>	Retired	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	<a href="#">PDF</a>
<a href="#">T6672CHSS</a>	—	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	<a href="#">PDF</a>
<a href="#">T8812CHSS</a>	—	8.00 x 8.00 x 12.00 [203 x 203 x 305]	<a href="#">PDF</a>
<a href="#">T8824CHSS</a>	—	8.00 x 8.00 x 24.00 [203 x 203 x 610]	<a href="#">PDF</a>
<a href="#">T8836CHSS</a>	—	8.00 x 8.00 x 36.00 [203 x 203 x 914]	<a href="#">PDF</a>
<a href="#">T8848CHSS</a>	—	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	<a href="#">PDF</a>
<a href="#">T8860CHSS</a>	Retired	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	<a href="#">PDF</a>
<a href="#">T121224CHSS</a>	—	12.00 x 12.00 x 24.00 [305 x 305 x 610]	<a href="#">PDF</a>
<a href="#">T121236CHSS</a>	—	12.00 x 12.00 x 36.00 [305 x 305 x 914]	<a href="#">PDF</a>
<a href="#">T121248CHSS</a>	—	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	<a href="#">PDF</a>
<a href="#">T121260CHSS</a>	Retired	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



# NEMA 1, 4, 4X, and 12 Hinged Cover Stainless Steel Wiring Trough



## Dimensions

