

# NEMA 1 Single-Door Wall-Mount with Knockouts



## Applications

Designed for use as surface-mounted junction box, service box, switch box and cutout box.

## Construction

- Bodies and doors fabricated from 14- or 16-gauge steel
- 3.0in [76mm] depth enclosures furnished with formed steel hinge non-removable cover
- 4.0in [103mm] and 6.0in [152mm] depth enclosures furnished with clamp style hinges allowing for removable/replaceable covers
- Various sizes of removable concentric knockouts are furnished on all four sides of standard cutout enclosures
- Mounting holes on back of enclosure

## Finish

- ANSI 61 gray polyester powder inside and out

## Listings

- UL 50, 1 [UL File E6924]
- NEMA/EEMAC 1



A Series NEMA 1 Single-Door Wall-Mount with Knockouts					
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD	Knockout Pattern	
				Width Side	Height Side
<a href="#">A040604</a>		16/16	6.44 x 4.44 x 4.38 [164 x 113 x 111]	A-A	A-B-A
<a href="#">A060603</a>		16/16	6.37 x 6.37 x 3.06 [162 x 162 x 78]	A-B-A	A-B-A
<a href="#">A060604</a>		16/16	6.37 x 6.37 x 4.38 [162 x 162 x 111]	A-A	A-B-A
<a href="#">A060606</a>		16/16	6.37 x 6.37 x 6.38 [162 x 162 x 162]	A-B-A	A-B-A
<a href="#">A060804</a>		16/16	8.25 x 6.25 x 4.38 [210 x 159 x 111]	A-B-A	A-B-A
<a href="#">A080804</a>		16/16	8.37 x 8.37 x 4.38 [213 x 213 x 111]	A-B-A	A-B-A
<a href="#">A080806</a>		16/16	8.37 x 8.37 x 6.38 [213 x 213 x 162]	A-B-A	A-B-A
<a href="#">A081004</a>		16/16	10.37 x 8.37 x 4.38 [263 x 213 x 111]	A-B-A	B-A-F-F-A
<a href="#">A081006</a>		16/16	10.37 x 8.37 x 6.38 [263 x 213 x 162]	A-B-A	B-A-F-F-A
<a href="#">A081204</a>		16/16	12.25 x 8.25 x 4.38 [311 x 210 x 111]	A-B-A	B-A-F-F-A-B
<a href="#">A101004</a>		16/16	10.25 x 10.25 x 4.38 [260 x 260 x 111]	B-A-F-F-A	B-A-F-F-A
<a href="#">A101006</a>		16/16	10.25 x 10.25 x 6.38 [260 x 260 x 162]	B-A-F-F-A	B-A-F-F-A
<a href="#">A101204</a>		16/16	12.25 x 10.25 x 4.38 [311 x 260 x 111]	B-A-F-F-A	B-A-F-F-A-B
<a href="#">A101206</a>		16/16	12.25 x 10.25 x 6.38 [311 x 260 x 162]	B-A-F-F-A	B-A-F-F-A-B
<a href="#">A121204</a>		16/16	12.25 x 12.25 x 4.38 [311 x 311 x 111]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">A121206</a>		16/16	12.25 x 12.25 x 6.38 [311 x 311 x 162]	B-A-F-F-A-B	B-A-F-F-A-B
<a href="#">A121504</a>		16/16	15.25 x 12.25 x 4.38 [387 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">A121604</a>		16/16	16.25 x 12.25 x 4.38 [413 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">A121606</a>		16/16	16.25 x 12.25 x 6.38 [413 x 311 x 162]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">A121804</a>		16/16	18.25 x 12.25 x 4.38 [464 x 311 x 111]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">A121806</a>		16/16	18.25 x 12.25 x 6.38 [464 x 311 x 162]	B-A-F-F-A-B	A-B-A-F-F-A-B-A
<a href="#">A151506</a>		16/16	15.25 x 15.25 x 6.38 [387 x 387 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].

Table continued on next page

# NEMA 1 Single-Door Wall-Mount with Knockouts



Table continued from previous page

A Series NEMA 1 Single-Door Wall-Mount with Knockouts						
Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD	Knockout Pattern		
				Width Side	Height Side	
<b>A151804</b>		16/16	18.25 x 15.25 x 4.38 [464 x 387 x 111]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
<b>A161606</b>		16/16	16.25 x 16.25 x 6.38 [413 x 413 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
<b>A181806</b>		16/16	18.25 x 18.25 x 6.38 [464 x 464 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
<b>A182406</b>		14/14	24.25 x 18.25 x 6.39 [616 x 464 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	
<b>A242406</b>		14/14	24.25 x 24.25 x 6.39 [616 x 616 x 162]	A-B-A-F-F-A-B-A	A-B-A-F-F-A-B-A	

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].

## Dimensions

