

NITRA Blowguns (or nozzles) are available in heavy duty palm type with safety tip, pistol grips (both aluminum and plastic), a pocket (pencil) type, and plastic grip with flexible nozzles in various lengths.

Features

- Maximum input pressure 120 psi
- Thread size on inlet 1/4 NPT female (with exception of pocket model which has 1/4" male industrial interchange) quick disconnect
- Maximum pressure = 120 psi

| NITRA™ Pneumatic Blow Guns | | | | | |
|----------------------------|-------|--|--------------------------|---------------|--------|
| Part No. | Price | Description | OHSA Directive No. 100-1 | Parts Per Pkg | Weight |
| HBG-01 | <--> | Pneumatic blow gun, heavy duty palm type with safety tip, 1/4 inch FNPT connection | yes | 1 | 0.4 |
| HBG-02 | <--> | Pneumatic blow gun, plastic pistol grip with 5 inch nozzle, 1/4 inch FNPT connection | no | 1 | 0.3 |
| HBG-03 | <--> | Pneumatic pocket blow gun with twist on/off valve, 1/4 inch industrial interchange quick-disconnect plug | no | 1 | 0.4 |
| HBG-04 | <--> | Pneumatic blow gun, cast aluminum pistol grip with 6 inch nozzle, 1/4 inch FNPT connection | no | 1 | 1.0 |
| HBG-05 | <--> | Pneumatic blow gun, plastic pistol grip with 4 inch flexible nozzle, 1/4 inch FNPT connection | yes | 1 | 0.4 |
| HBG-06 | <--> | Pneumatic blow gun, plastic pistol grip with 8 inch flexible nozzle, 1/4 inch FNPT connection | yes | 1 | 0.4 |
| HBG-07 | <--> | Pneumatic blow gun, plastic pistol grip with 12 inch flexible nozzle, 1/4 inch FNPT connection | yes | 1 | 0.5 |
| HBG-08 | <--> | Pneumatic blow gun, plastic pistol grip with 16 inch flexible nozzle, 1/4 inch FNPT connection | yes | 1 | 0.6 |

O.S.H.A. Certification – Blow Guns HBG-01, -05, -06, -07, and -08 conform to the requirements of Compressed Air Standards as currently described in the U.S. Bureau of Labor Standards, standard 1910.242 (OSHA directive STD01-13-001), when pressurized at the inlet to a maximum of 100 PSIG.



HBG-01



HBG-02



HBG-03



HBG-04



HBG-05



HBG-06



HBG-07



HBG-08

NITRA commercial grade thread sealant tape is made with 100% virgin PTFE for strong chemical resistance. Thread sealant color is white and is USDA and FDA compliant.



| NITRA™ PTFE Thread Sealing Tape | | | | |
|---------------------------------|-------|---|---------------|--------|
| Part No. | Price | Description | Parts Per Pkg | Weight |
| TS12-260 | <--> | NITRA pneumatic PTFE thread sealing tape for use with pipe thread connections. 1/2 inch wide by 260 inch long roll. | 1 | 0.02 |