



Hose Clamps

**HC-58**

| NITRA Adjustable Hose Clamps | | | | |
|------------------------------|---|---------|--------------|-------|
| Part No. | Description | Pcs/Pkg | Weight (lbs) | Price |
| <u>HC-316</u> | NITRA hose clamp, 2-ear, 0.318-0.433in diameter, plated steel. For use with HBV series 3/16in hose. | 10 | 0.1 | |
| <u>HC-14</u> | NITRA hose clamp, 2-ear, 0.425-0.512in diameter, plated steel. For use with HBV series 1/4in hose. | 10 | 0.1 | |
| <u>HC-516</u> | NITRA hose clamp, 2-ear, 0.492-0.591in diameter, plated steel. For use with HBV series 5/16in hose. | 10 | 0.1 | |
| <u>HC-38</u> | NITRA hose clamp, 2-ear, 0.551-0.669in diameter, plated steel. For use with HBV series 3/8in hose. | 10 | 0.1 | |
| <u>HC-12</u> | NITRA hose clamp, 2-ear, 0.638-0.787in diameter, plated steel. For use with HBV series 1/2in hose. | 10 | 0.1 | |
| <u>HC-58</u> | NITRA hose clamp, 2-ear, 0.748-0.906in diameter, plated steel. For use with HBV series 5/8in hose. | 10 | 0.2 | |
| <u>HC-34</u> | NITRA hose clamp, 2-ear, 0.945-1.102in diameter, plated steel. For use with HBV series 3/4in hose. | 10 | 0.3 | |
| <u>HC-1</u> | NITRA hose clamp, 2-ear, 1.154-1.339in diameter, plated steel. For use with HBV series 1in hose. | 10 | 0.3 | |

**HCSS-58**

| NITRA Interlocking Hose Clamps | | | | |
|--------------------------------|---|---------|--------------|-------|
| Part No. | Description | Pcs/Pkg | Weight (lbs) | Price |
| <u>HCSS-316</u> | NITRA hose clamp, interlocking ear, 0.346-0.413in diameter, 304 stainless steel. For use with HBV series 3/16in hose. | 10 | 0.1 | |
| <u>HCSS-14</u> | NITRA hose clamp, interlocking ear, 0.398-0.465in diameter, 304 stainless steel. For use with HBV series 1/4in hose. | 10 | 0.1 | |
| <u>HCSS-516</u> | NITRA hose clamp, interlocking ear, 0.472-0.571in diameter, 304 stainless steel. For use with HBV series 5/16in hose. | 10 | 0.1 | |
| <u>HCSS-38</u> | NITRA hose clamp, interlocking ear, 0.520-0.618in diameter, 304 stainless steel. For use with HBV series 3/8in hose. | 10 | 0.1 | |
| <u>HCSS-12</u> | NITRA hose clamp, interlocking ear, 0.654-0.780in diameter, 304 stainless steel. For use with HBV series 1/2in hose. | 10 | 0.1 | |
| <u>HCSS-58</u> | NITRA hose clamp, interlocking ear, 0.823-0.949in diameter, 304 stainless steel. For use with HBV series 5/8in hose. | 10 | 0.1 | |
| <u>HCSS-34</u> | NITRA hose clamp, interlocking ear, 0.941-1.067in diameter, 304 stainless steel. For use with HBV series 3/4in hose. | 10 | 0.1 | |
| <u>HCSS-1</u> | NITRA hose clamp, interlocking ear, 1.236-1.362in diameter, 304 stainless steel. For use with HBV series 1in hose. | 10 | 0.1 | |



Hose Crimping Tools

NITRA hose crimping tools are designed to work with 2-ear and interlocking ear hose clamps. They come in three styles.

- Straight jaw single action, straight jaw compound action and side jaw compound action styles available
- Made in USA



HCT-ES



HCT-SC



HCT-AC



| Nitra Hose Crimping Tools | | | | |
|---------------------------|---|---------|----------------------|-------|
| Part Number | Description | Pcs/Pkg | Package Weight (lbs) | Price |
| <u>HCT-ES</u> | NITRA hose clamp crimping tool, single action, straight jaw | 1 | 0.8 | |
| <u>HCT-SC</u> | NITRA hose clamp crimping tool, compound action, straight jaw | 1 | 0.9 | |
| <u>HCT-AC</u> | NITRA hose clamp crimping tool, compound action, side jaw | 1 | 0.9 | |