



Bonded Straight Polyurethane Tubing

NITRA™ bonded polyurethane (PUR) tubing is made by continuously bonding standard NITRA polyurethane tubing. The result is a strong, organized, color-coded package that makes installation neater and easier. With its extremely tight outside diameter tolerance, NITRA polyurethane tubing is ideal for use with NITRA push-to-connect fittings.

Features

- Inch and metric sizes available
- Contrasting colors
- Secondary bonding process maintains tubing geometry
- 50 foot package size
- Shore A 98 hardness
- Strong, flexible and kink resistant
- Made in USA

Polyurethane 5/32 in. (4 mm) Bonded Tubing Specifications					
Outside Diameter (in.)	0.156	Working Pressure (psi) @ 70°F	200	Temp. Range	-40°F to +160°F (-40°C to +71°C)
Inside Diameter (in.)	0.093	Burst Pressure (psi)	600	Hardness	Shore A 98
Wall Thickness (in.)	0.031	Vacuum Rating	To 28" Hg	Bend Radius (in.)	0.250
Part Number	Price	Configuration	Color	PKG/Reel Length (feet)	Package Weight (lbs)
<u>2PU532-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	0.65
<u>3PU532-50</u>		Bonded triple tube	Black, clear blue, blue		1.00

Polyurethane 1/4 in. Bonded Tubing Specifications					
Outside Diameter (in.)	0.250	Working Pressure (psi) @ 70°F	180	Temp. Range	-40°F to +160°F (-40°C to +71°C)
Inside Diameter (in.)	0.156	Burst Pressure (psi)	540	Hardness	Shore A 98
Wall Thickness (in.)	0.047	Vacuum Rating	To 28" Hg	Bend Radius (in.)	0.476
Part Number	Price	Configuration	Color	PKG/Reel Length (feet)	Package Weight (lbs)
<u>2PU14-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	1.55
<u>3PU14-50</u>		Bonded triple tube	Black, clear blue, blue		2.25

Polyurethane 3/8 in. Bonded Tubing Specifications					
Outside Diameter (in.)	0.375	Working Pressure (psi) @ 70°F	150	Temp. Range	-40°F to +160°F (-40°C to +71°C)
Inside Diameter (in.)	0.250	Burst Pressure (psi)	450	Hardness	Shore A 98
Wall Thickness (in.)	0.063	Vacuum Rating	To 28" Hg	Bend Radius (in.)	1.00
Part Number	Price	Configuration	Color	PKG/Reel Length (feet)	Package Weight (lbs)
<u>2PU38-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	3.25

Polyurethane 1/2 in. Bonded Tubing Specifications					
Outside Diameter (in.)	0.500	Working Pressure (psi) @ 70°F	150	Temp. Range	-40°F to +160°F (-40°C to +71°C)
Inside Diameter (in.)	0.328	Burst Pressure (psi)	450	Hardness	Shore A 98
Wall Thickness (in.)	0.086	Vacuum Rating	To 28" Hg	Bend Radius (in.)	1.102
Part Number	Price	Configuration	Color	PKG/Reel Length (feet)	Package Weight (lbs)
<u>2PU12-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	6.00



Bonded Straight Polyurethane Tubing

Polyurethane 6 mm Bonded Tubing Specifications					
<i>Outside Diameter (mm)</i>	6.0	<i>Working Pressure (psi) @ 70°F</i>	180	<i>Temp. Range</i>	-40°F to +160°F (-40°C to +71°C)
<i>Inside Diameter (mm)</i>	4.0	<i>Burst Pressure (psi)</i>	540	<i>Hardness</i>	Shore A 98
<i>Wall Thickness (mm)</i>	1.0	<i>Vacuum Rating</i>	To 28" Hg	<i>Bend Radius (mm)</i>	12.0
<i>Part Number</i>	<i>Price</i>	<i>Configuration</i>	<i>Color</i>	<i>PKG/Reel Length (feet)</i>	<i>Package Weight (lbs)</i>
<u>2PU06M-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	1.25

Polyurethane 8 mm Bonded Tubing Specifications					
<i>Outside Diameter (mm)</i>	8.0	<i>Working Pressure (psi) @ 70°F</i>	175	<i>Temp. Range</i>	-40°F to +160°F (-40°C to +71°C)
<i>Inside Diameter (mm)</i>	5.0	<i>Burst Pressure (psi)</i>	525	<i>Hardness</i>	Shore A 98
<i>Wall Thickness (mm)</i>	1.5	<i>Vacuum Rating</i>	To 28" Hg	<i>Bend Radius (mm)</i>	15.0
<i>Part Number</i>	<i>Price</i>	<i>Configuration</i>	<i>Color</i>	<i>PKG/Reel Length (feet)</i>	<i>Package Weight (lbs)</i>
<u>2PU08M-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	2.50

Polyurethane 10 mm Bonded Tubing Specifications					
<i>Outside Diameter (mm)</i>	10.0	<i>Working Pressure (psi) @ 70°F</i>	150	<i>Temp. Range</i>	-40°F to +160°F (-40°C to +71°C)
<i>Inside Diameter (mm)</i>	6.5	<i>Burst Pressure (psi)</i>	450	<i>Hardness</i>	Shore A 98
<i>Wall Thickness (mm)</i>	1.75	<i>Vacuum Rating</i>	To 28" Hg	<i>Bend Radius (mm)</i>	25.0
<i>Part Number</i>	<i>Price</i>	<i>Configuration</i>	<i>Color</i>	<i>PKG/Reel Length (feet)</i>	<i>Package Weight (lbs)</i>
<u>2PU10M-50</u>		Bonded double tube	Black, clear blue	50 ft. Package	3.75