

Hand Taps

Fractional and Metric Thread Hand Taps

High-speed steel fractional and metric size hand taps.



231100


High-Speed Steel Fractional Size Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
	246080UNC3	1		8-32 UNC	1.77	2149029		246100UNF2	1		10-32 UNF	1.77	2149021
	246100UNC3	1		10-24 UNC	1.97	2149025							
	246014UNC3	1		1/4-20 UNC	1.97	2149007							
	246516UNC3	1		5/16-18 UNC	2.20	214900F							

High-Speed Steel Metric Hand Taps													
Coarse Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With	Fine Thread	Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
	231030	1		M3x0.5	40.0	214025 , 215025		235041-2	1		M4x0.5	45.0	214035 , 215035
	231040	1		M4x0.7	45.0	214033 , 215033		235050-2	1		M5x0.5	50.0	214045 , 215045
	231050	1		M5x0.8	50.0	214042 , 215042		235081-2	1		M8x1	56.0	214070 , 215070
	231060	1		M6x1	50.0	214050 , 215050		235122-2	1		M12x1	70.0	214110 , 215110
	231080	1		M8x1.25	56.0	214068 , 215068		235181-2	1		M18x1	80.0	17.0 mm
	231100	1		M10x1.5	70.0	214085 , 215085		235301-2	1		M30x1.5	90.0	28.5 mm
	231120	1		M12x1.75	75.0	214102 , 215102							

NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

High-Speed Steel NPT Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (in.)	Use With
231116NPT	1		1/16-27 NPT	2.56	214813 , 250813T , 215813
231018NPT	1		1/8-27 NPT	2.56	214900R
231014NPT	1		1/4-18 NPT	2.76	214825 , 250825T , 215825
231038NPT	1		3/8-18 NPT	2.95	37/64"
231012NPT	1		1/2-14 NPT	3.15	23/32"




231038NPT

Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

High-Speed Steel Conduit Thread Hand Taps					
Part #	Pcs/Pkg	Price	Thread Size	Overall Length (mm)	Use With
264009	1		PG-9	70.0	14.0 mm
264011	1		PG-11	80.0	17.25 mm
264016	1		PG-16	80.0	21.25 mm
264021	1		PG-21	90.0	26.75 mm
264029	1		PG-29	100.0	35.5 mm



264029

RUKO Hand Taps



245004RO

Drill and Hand Tap Sets		
Part #	Price	Description
245004RO		RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) metric size taps (M3, M4, M5, M6, M8, M10, M12), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.
245004USRO		RUKO hand tap set, high-speed steel (HSS), 15-piece set includes: (7) SAE taps (8-32 UNC, 10-24 UNC, 10-32 UNF, 1/4-20 UNC, 1/4-28 UNF, 5/16-18 UNC, 5/16-24 UNF), (7) jobber length drill bits (one for each tap), (1) tap wrench with two-jaw chuck. Includes heavy-duty plastic case.

RUKO Tools – Hand Tap Wrenches

Hand Tap Wrenches



241103



241010

Hand Tap Wrenches					
Part #	Pcs/Pkg	Price	Description	Construction Material	Use With
241010	1		Sliding T-handle ratcheting tap wrench	Chrome plated steel	M3 to M10, 1/8" to 3/8" taps
241020	1		Sliding T-handle ratcheting tap wrench	Chrome plated steel	M5 to M12, 7/32" to 1/2" taps
241112	1		Two-jaw chuck tap wrench	Die cast zinc housing, steel handles, hardened chuck jaws	M1 to M12, 1/8" to 1/2" taps