


# NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



## Applications

Designed to house electrical and electronic controls, instrumentation and components. Provides protection from dust, dirt, oil and water.

## Construction

- 14-gauge carbon steel
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening
- Door clamps are quick and easy to operate.
- Concealed hinges
- Hasp and staple for padlocking
- Poured-in-place oil- and water-resistant gasket
- Collar studs for mounting optional subpanels
- Ground studs on door and body
- Removable print pocket furnished if height and width of enclosure is greater than 12in [305mm].
- Mounting provision top and bottom of back
- Provision for lifting lugs included on enclosures with height greater than 48in [1219mm] and with depth greater than 16in [406mm].
  - Lifting lug assembly included with the enclosure bolt pack

## Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 12, and 13
- cULus Listed Type 3R, 4 and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount

Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-12H2406LP</a>	<--->	12.00 x 24.00 x 7.07 [305 x 610 x 180]	<a href="#">PDF</a>	<a href="#">SCE-12P24</a>	<--->
<a href="#">SCE-12H2408LP</a>	<--->	12.00 x 24.00 x 9.07 [305 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-12P24</a>	<--->
<a href="#">SCE-16H1206LP</a>	<--->	16.00 x 12.00 x 7.07 [406 x 305 x 180]	<a href="#">PDF</a>	<a href="#">SCE-16P12</a>	<--->
<a href="#">SCE-16H1208LP</a>	<--->	16.00 x 12.00 x 9.07 [406 x 305 x 230]	<a href="#">PDF</a>	<a href="#">SCE-16P12</a>	<--->
<a href="#">SCE-16H1210LP</a>	<--->	16.00 x 12.00 x 11.07 [406 x 305 x 281]	<a href="#">PDF</a>	<a href="#">SCE-16P12</a>	<--->
<a href="#">SCE-16H1606LP</a>	<--->	16.00 x 16.00 x 7.07 [406 x 406 x 180]	<a href="#">PDF</a>	<a href="#">SCE-16P16</a>	<--->
<a href="#">SCE-16H1608LP</a>	<--->	16.00 x 16.00 x 9.07 [406 x 406 x 230]	<a href="#">PDF</a>	<a href="#">SCE-16P16</a>	<--->
<a href="#">SCE-16H2006LP</a>	<--->	16.00 x 20.00 x 7.07 [406 x 508 x 180]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-16H2008LP</a>	<--->	16.00 x 20.00 x 9.07 [406 x 508 x 230]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-20H1206LP</a>	<--->	20.00 x 12.00 x 7.07 [508 x 305 x 180]	<a href="#">PDF</a>	<a href="#">SCE-20P12</a>	<--->
<a href="#">SCE-20H1208LP</a>	<--->	20.00 x 12.00 x 9.07 [508 x 305 x 230]	<a href="#">PDF</a>	<a href="#">SCE-20P12</a>	<--->
<a href="#">SCE-20H1606LP</a>	<--->	20.00 x 16.00 x 7.07 [508 x 406 x 180]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-20H1608LP</a>	<--->	20.00 x 16.00 x 9.07 [508 x 406 x 230]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-20H1610LP</a>	<--->	20.00 x 16.00 x 11.07 [508 x 406 x 281]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-20H1612LP</a>	<--->	20.00 x 16.00 x 13.07 [508 x 406 x 332]	<a href="#">PDF</a>	<a href="#">SCE-20P16</a>	<--->
<a href="#">SCE-20H2006LP</a>	<--->	20.00 x 20.00 x 7.07 [508 x 508 x 180]	<a href="#">PDF</a>	<a href="#">SCE-20P20</a>	<--->
<a href="#">SCE-20H2008LP</a>	<--->	20.00 x 20.00 x 9.07 [508 x 508 x 230]	<a href="#">PDF</a>	<a href="#">SCE-20P20</a>	<--->
<a href="#">SCE-20H2010LP</a>	<--->	20.00 x 20.00 x 11.07 [508 x 508 x 281]	<a href="#">PDF</a>	<a href="#">SCE-20P20</a>	<--->

Note: Dimensions in inches [millimeters].

Table continued on next page

# NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-20H2406LP</a>	<---	20.00 x 24.00 x 7.07 [508 x 610 x 180]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-20H2408LP</a>	<---	20.00 x 24.00 x 9.07 [508 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-20H3006LP</a>	<---	20.00 x 30.00 x 7.07 [508 x 762 x 180]	<a href="#">PDF</a>	<a href="#">SCE-30P20</a>	<---
<a href="#">SCE-24H1206LP</a>	<---	24.00 x 12.00 x 7.07 [610 x 305 x 180]	<a href="#">PDF</a>	<a href="#">SCE-12P24</a>	<---
<a href="#">SCE-24H1208LP</a>	<---	24.00 x 12.00 x 9.07 [610 x 305 x 230]	<a href="#">PDF</a>	<a href="#">SCE-12P24</a>	<---
<a href="#">SCE-24H1210LP</a>	<---	24.00 x 12.00 x 11.07 [610 x 305 x 281]	<a href="#">PDF</a>	<a href="#">SCE-12P24</a>	<---
<a href="#">SCE-24H1606LP</a>	<---	24.00 x 16.00 x 7.07 [610 x 406 x 180]	<a href="#">PDF</a>	<a href="#">SCE-24P16</a>	<---
<a href="#">SCE-24H1608LP</a>	<---	24.00 x 16.00 x 9.07 [610 x 406 x 230]	<a href="#">PDF</a>	<a href="#">SCE-24P16</a>	<---
<a href="#">SCE-24H2006LP</a>	<---	24.00 x 20.00 x 7.07 [610 x 508 x 180]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-24H2008LP</a>	<---	24.00 x 20.00 x 9.07 [610 x 508 x 230]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-24H2010LP</a>	<---	24.00 x 20.00 x 11.07 [610 x 508 x 281]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-24H2012LP</a>	<---	24.00 x 20.00 x 13.07 [610 x 508 x 332]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-24H2016LP</a>	<---	24.00 x 20.00 x 17.07 [610 x 508 x 434]	<a href="#">PDF</a>	<a href="#">SCE-24P20</a>	<---
<a href="#">SCE-24H2406LP</a>	<---	24.00 x 24.00 x 7.07 [610 x 610 x 180]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	<---
<a href="#">SCE-24H2408LP</a>	<---	24.00 x 24.00 x 9.07 [610 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	<---
<a href="#">SCE-24H2410LP</a>	<---	24.00 x 24.00 x 11.07 [610 x 610 x 281]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	<---
<a href="#">SCE-24H2412LP</a>	<---	24.00 x 24.00 x 13.07 [610 x 610 x 332]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	<---
<a href="#">SCE-24H2416LP</a>	<---	24.00 x 24.00 x 17.07 [610 x 610 x 434]	<a href="#">PDF</a>	<a href="#">SCE-24P24</a>	<---
<a href="#">SCE-24H3008LP</a>	<---	24.00 x 30.00 x 9.07 [610 x 762 x 230]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H1606LP</a>	<---	30.00 x 16.00 x 7.07 [762 x 406 x 180]	<a href="#">PDF</a>	<a href="#">SCE-30P16</a>	<---
<a href="#">SCE-30H2006LP</a>	<---	30.00 x 20.00 x 7.07 [762 x 508 x 180]	<a href="#">PDF</a>	<a href="#">SCE-30P20</a>	<---
<a href="#">SCE-30H2008LP</a>	<---	30.00 x 20.00 x 9.07 [762 x 508 x 230]	<a href="#">PDF</a>	<a href="#">SCE-30P20</a>	<---
<a href="#">SCE-30H2010LP</a>	<---	30.00 x 20.00 x 11.07 [762 x 508 x 281]	<a href="#">PDF</a>	<a href="#">SCE-30P20</a>	<---
<a href="#">SCE-30H2406LP</a>	<---	30.00 x 24.00 x 7.07 [762 x 610 x 180]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2408LP</a>	<---	30.00 x 24.00 x 9.07 [762 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2410LP</a>	<---	30.00 x 24.00 x 11.07 [762 x 610 x 281]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2412LP</a>	<---	30.00 x 24.00 x 13.07 [762 x 610 x 332]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2416LP</a>	<---	30.00 x 24.00 x 17.07 [762 x 610 x 434]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2420LP</a>	<---	30.00 x 24.00 x 21.07 [762 x 610 x 535]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H2424LP</a>	<---	30.00 x 24.00 x 25.07 [762 x 610 x 637]	<a href="#">PDF</a>	<a href="#">SCE-30P24</a>	<---
<a href="#">SCE-30H3008LP</a>	<---	30.00 x 30.00 x 9.07 [762 x 762 x 230]	<a href="#">PDF</a>	<a href="#">SCE-30P30</a>	<---
<a href="#">SCE-30H3012LP</a>	<---	30.00 x 30.00 x 13.07 [762 x 762 x 332]	<a href="#">PDF</a>	<a href="#">SCE-30P30</a>	<---
<a href="#">SCE-30H3608LP</a>	<---	30.00 x 36.00 x 9.07 [762 x 914 x 230]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<---
<a href="#">SCE-36H1606LP</a>	<---	36.00 x 16.00 x 7.07 [914 x 406 x 180]	<a href="#">PDF</a>	<a href="#">SCE-36P16</a>	<---
<a href="#">SCE-36H2406LP</a>	<---	36.00 x 24.00 x 7.07 [914 x 610 x 180]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	<---
<a href="#">SCE-36H2408LP</a>	<---	36.00 x 24.00 x 9.07 [914 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	<---
<a href="#">SCE-36H2410LP</a>	<---	36.00 x 24.00 x 11.07 [914 x 610 x 281]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	<---
<a href="#">SCE-36H2412LP</a>	<---	36.00 x 24.00 x 13.07 [914 x 610 x 332]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	<---
<a href="#">SCE-36H2416LP</a>	<---	36.00 x 24.00 x 17.07 [914 x 610 x 434]	<a href="#">PDF</a>	<a href="#">SCE-36P24</a>	<---
<a href="#">SCE-36H3006LP</a>	Retired	36.00 x 30.00 x 7.07 [914 x 762 x 180]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<---

Note: Dimensions in inches [millimeters].

Table continued on next page

# NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount

Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.



Table continued from previous page.

NEMA 3R, 4, 12, and 13 Single-Door Wall-Mount					
Part Number	Price	Size HxWxD	Drawing Link	Optional Subpanel	Price
<a href="#">SCE-36H3008LP</a>	<--->	36.00 x 30.00 x 9.07 [914 x 762 x 230]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<--->
<a href="#">SCE-36H3010LP</a>	<--->	36.00 x 30.00 x 11.07 [914 x 762 x 281]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<--->
<a href="#">SCE-36H3012LP</a>	<--->	36.00 x 30.00 x 13.07 [914 x 762 x 332]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<--->
<a href="#">SCE-36H3016LP</a>	<--->	36.00 x 30.00 x 17.07 [914 x 762 x 434]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<--->
<a href="#">SCE-36H3020LP</a>	<--->	36.00 x 30.00 x 21.07 [914 x 762 x 535]	<a href="#">PDF</a>	<a href="#">SCE-36P30</a>	<--->
<a href="#">SCE-36H3608LP</a>	<--->	36.00 x 36.00 x 9.07 [914 x 914 x 230]	<a href="#">PDF</a>	<a href="#">SCE-36P36</a>	<--->
<a href="#">SCE-36H3612LP</a>	<--->	36.00 x 36.00 x 13.07 [914 x 914 x 332]	<a href="#">PDF</a>	<a href="#">SCE-36P36</a>	<--->
<a href="#">SCE-36H3616LP</a>	<--->	36.00 x 36.00 x 17.07 [914 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-36P36</a>	<--->
<a href="#">SCE-42H2408LP</a>	<--->	42.00 x 24.00 x 9.07 [1067 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-42P24</a>	<--->
<a href="#">SCE-42H3008LP</a>	<--->	42.00 x 30.00 x 9.07 [1067 x 762 x 230]	<a href="#">PDF</a>	<a href="#">SCE-42P30</a>	<--->
<a href="#">SCE-42H3010LP</a>	<--->	42.00 x 30.00 x 11.07 [1067 x 762 x 281]	<a href="#">PDF</a>	<a href="#">SCE-42P30</a>	<--->
<a href="#">SCE-42H3012LP</a>	<--->	42.00 x 30.00 x 13.07 [1067 x 762 x 332]	<a href="#">PDF</a>	<a href="#">SCE-42P30</a>	<--->
<a href="#">SCE-42H3016LP</a>	<--->	42.00 x 30.00 x 17.07 [1067 x 762 x 434]	<a href="#">PDF</a>	<a href="#">SCE-42P30</a>	<--->
<a href="#">SCE-42H3608LP</a>	<--->	42.00 x 36.00 x 9.07 [1067 x 914 x 230]	<a href="#">PDF</a>	<a href="#">SCE-42P36</a>	<--->
<a href="#">SCE-42H3610LP</a>	<--->	42.00 x 36.00 x 11.07 [1067 x 914 x 281]	<a href="#">PDF</a>	<a href="#">SCE-42P36</a>	<--->
<a href="#">SCE-42H3612LP</a>	<--->	42.00 x 36.00 x 13.07 [1067 x 914 x 332]	<a href="#">PDF</a>	<a href="#">SCE-42P36</a>	<--->
<a href="#">SCE-42H3616LP</a>	<--->	42.00 x 36.00 x 17.07 [1067 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-42P36</a>	<--->
<a href="#">SCE-48H2408LP</a>	<--->	48.00 x 24.00 x 9.07 [1219 x 610 x 230]	<a href="#">PDF</a>	<a href="#">SCE-48P24</a>	<--->
<a href="#">SCE-48H3008LP</a>	<--->	48.00 x 30.00 x 9.07 [1219 x 762 x 230]	<a href="#">PDF</a>	<a href="#">SCE-48P30</a>	<--->
<a href="#">SCE-48H3010LP</a>	<--->	48.00 x 30.00 x 11.07 [1219 x 762 x 281]	<a href="#">PDF</a>	<a href="#">SCE-48P30</a>	<--->
<a href="#">SCE-48H3016LP</a>	<--->	48.00 x 30.00 x 17.07 [1219 x 762 x 434]	<a href="#">PDF</a>	<a href="#">SCE-48P30</a>	<--->
<a href="#">SCE-48H3608LP</a>	<--->	48.00 x 36.00 x 9.07 [1219 x 914 x 230]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	<--->
<a href="#">SCE-48H3610LP</a>	<--->	48.00 x 36.00 x 11.07 [1219 x 914 x 281]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	<--->
<a href="#">SCE-48H3612LP</a>	<--->	48.00 x 36.00 x 13.07 [1219 x 914 x 332]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	<--->
<a href="#">SCE-48H3616LP</a>	<--->	48.00 x 36.00 x 17.07 [1219 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	<--->
<a href="#">SCE-48H3620LP</a>	<--->	48.00 x 36.00 x 21.07 [1219 x 914 x 535]	<a href="#">PDF</a>	<a href="#">SCE-48P36</a>	<--->
<a href="#">SCE-60H3608LP</a>	<--->	60.00 x 36.00 x 9.07 [1524 x 914 x 230]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	<--->
<a href="#">SCE-60H3610LP</a>	<--->	60.00 x 36.00 x 11.07 [1524 x 914 x 281]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	<--->
<a href="#">SCE-60H3612LP</a>	<--->	60.00 x 36.00 x 13.07 [1524 x 914 x 332]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	<--->
<a href="#">SCE-60H3616LP</a>	<--->	60.00 x 36.00 x 17.07 [1524 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	<--->
<a href="#">SCE-60H3620LP</a>	<--->	60.00 x 36.00 x 21.07 [1524 x 914 x 535]	<a href="#">PDF</a>	<a href="#">SCE-60P36</a>	<--->
<a href="#">SCE-72H3012LP</a>	<--->	72.00 x 30.00 x 13.07 [1829 x 762 x 332]	<a href="#">PDF</a>	<a href="#">SCE-72P30</a>	<--->
<a href="#">SCE-72H3016LP</a>	<--->	72.00 x 30.00 x 17.07 [1829 x 762 x 434]	<a href="#">PDF</a>	<a href="#">SCE-72P30</a>	<--->
<a href="#">SCE-72H3024LP</a>	<--->	72.00 x 30.00 x 25.07 [1829 x 762 x 637]	<a href="#">PDF</a>	<a href="#">SCE-72P30</a>	<--->
<a href="#">SCE-72H3612LP</a>	<--->	72.00 x 36.00 x 13.07 [1829 x 914 x 332]	<a href="#">PDF</a>	<a href="#">SCE-72P36</a>	<--->
<a href="#">SCE-72H3616LP</a>	<--->	72.00 x 36.00 x 17.07 [1829 x 914 x 434]	<a href="#">PDF</a>	<a href="#">SCE-72P36</a>	<--->

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 12, and 13 Padlocking Single-Door Wall-Mount



## Dimensions

