


Southwire™

TOOLS & EQUIPMENT

Wire Cutters/Pliers Strippers/Shears

Overview

Southwire's pliers and cutters are made from American forged steel and assembled with hot rivet technology. These tools are built to withstand the wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges or wire and cable effortless.



Wire Cutters/Pliers/Strippers/Shears					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
S1020SOLUS	Southwire wire stripper/cutters, for cutting wire and stripping wire, beveled cutting edges, 6in overall length, padded comfort grip handles.	6in	1	0.31 lb	
DCPA8D-US	Southwire diagonal cutters, for cutting wire, induction hardened beveled cutting edges, 15-degree angled head, 8in overall length, comfort grip handles.	8in	1	0.63 lb	
CCP9D-US	Southwire cable shears, for cutting cable and wire, induction hardened shear cutting edges, 9in overall length, comfort grip handles.	9in	1	1.03 lb	
SCP9TPCD-US	Southwire linemans pliers, for cutting, crimper, fish tape pulling, and conduit and box reaming, induction hardened beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	1.07 lb	
TCC9D-US	Southwire crimping pliers, crimps insulated and non-insulated terminals and connectors, induction hardened beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	0.96 lb	



Part No. S1020SOLUS

- Strips and cuts up to 10-20 AWG solid and 12-22 AWWG stranded wire
- Double-dipped grip for comfortable fit
- Serrated nose holds cable for easy twisting and pulling
- Spring-loaded for self-opening action



Part No. TCC9D-US

- Crimps insulated and non-insulated terminals and connectors
- Specially hardened wire cutter in nose
- Tapered nose for working in confined spaces



Part No. DCPA8D-US

- Effectively cuts most hardened wire, ACSR, bolts, screws and nails
- High-leverage design provides maximum cutting power
- Angled head allows for easy work in confined spaces



Part No. CCP9D-US

- Cuts up to 4/0 AWG aluminum, 2/0 AWG copper, and 100-pair 24 AWG communications cable
- Induction hardened blades for maximum durability
- Dipped handles for comfort



Part No. SCP9TPCD-US

- High-leverage design provides maximum cutting power
- Induction hardened cutting blades ensure efficient and lasting cutting surfaces for hard and soft wire
- Features a crimper, fish tape puller and reaming head for added versatility


Southwire™

TOOLS & EQUIPMENT

Cable Shears and Pliers

Overview

Southwire's cable shears and pliers are built to withstand wear-and-tear of any job. The inclusion of beveled cutting edges with heat-treated steel and comfortable handles make working with all gauges of wire and cable effortless.

Cable Shears and Pliers					
Part Number	Description	Tool Length	Qty/Pkg	Weight (lbs)	Price
MP61	Southwire crimping pliers, for cutting cables, cutting copper and brass screws, stripping wire, and crimping insulated and non-insulated terminals and connectors, beveled cutting edges, 9in overall length, comfort grip handles.	9in	1	0.49 lb	



Part No. MP61

- Strips and cuts: 8-22 AWG solid or 10-24 AWG stranded
- Crimps: insulated and non-insulated terminals/connectors
- Shears & re-threads: 10-24, 10-32, 8-32, 6-32, and 4-40 screws


Southwire™

TOOLS & EQUIPMENT

Screwdriver and Nutdriver Sets



Part No. SDSET4MINI



Part No. SDSET8US



SDSET8US Screwdriver Set

- An 8 piece set that includes: 1/4" cabinet tip with 4" shank, 3/16" cabinet tip with 4" shank, 3/16" cabinet tip with 6" shank, 1/4" keystone tip with 4" shank, 5/16" keystone tip with 6" shank, #1 phillips head with 3" shank, #2 phillips with 4" shank, and #2 square tip with 4" shank
- Proudly made in the USA
- Larger cushion grip handle provides ultimate comfort and great torque
- Tether holes provided in handles for tether/lanyard attachment
- Handle end is marked for easy identification of tip type and size

Mini-screwdriver Set

- This 4-piece mini-screwdriver set includes: 1/16", 3/32", & 1/8" slotted tip screwdrivers, as well as #0 Phillips screwdriver
- Comfortable cushioned grip allows firm grip and greater torque
- Precision-machined tips reduce slipping
- Handle end is marked for easy identification of tip type and size

Screwdriver Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
SDSET4MINI	Southwire screwdriver set, 4 pieces, imperial.	8	0.26 lb	
SDSET8US	Southwire screwdriver set, 8 pieces, imperial.	4	2.16 lb	



Part No. NDSET7-US



Part No. ND6N1HD



NDSET7-US Nutdriver Set

- 7 piece set includes: 1/2", 1/4", 3/8", 5/16", 7/16", 3/16", and 11/32" nut drivers
- Proudly made in the USA
- Hollow shaft for screw clearance
- Larger cushion grip handle provides ultimate comfort and great torque
- Nut drivers for the most used nut and bolt sizes
- Tether holes provided in handles for tether/lanyard attachment
- Handles marked for easy identification

Multi-driver

- 6 IN 1 Multi-driver with 3/16", 1/4", 5/16", 3/8", 7/16", 9/16" nut drivers.
- Heavy Duty steel shanks with bolsters for wrench assisted turning
- Comfort grip handle provides extra comfort and maximum torque
- Color coded ends for quick identification of sizes
- Chrome plated finish for corrosion resistance
- Hollow shafts for screw clearance

Nut Drivers and Sets				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
NDSET7-US	Southwire nutdriver set, 7 pieces, imperial.	7	1.95 lb	
ND6N1HD	Southwire nutdriver, 4 pieces, imperial.	4	1 lb	


Southwire™

TOOLS & EQUIPMENT

Fish Tape

Overview

Southwire's SIM^{pull}™ fish tape makes pulling wire or cable through a filled or empty conduit up to 2 inches in diameter easily. The low friction design allows these fish tapes to easily glide through the conduit without binding at turns, joints, or couplings. Spiral extruded polymer reduces the amount of effort required to push or pull the fish tape through EMT, IMC, Rigid or PVC conduit and as an added bonus polymer fish tapes will not rust. Do not confuse these polymer tapes with a fiberglass tape. A polymer fish tape offers greater flexibility than fiberglass fish tapes. These fish tapes will not break when folded or leave uncomfortable splinters. With the swiveling flexible metal leader and the polymer non-conductive tape makes the job SIM^{pull}.

Features

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape.
- Swiveling flexible metal leader easily glides through bends
- Low friction material reduces binding at joints, couplings, or 90-degree bends
- Two lengths 75 or 125 feet
- 580 lbs. tensile strength
- 4.5mm diameter tape
- Weighs less than a steel tape



Part No. FTSP45-75FML



Part No. FTSP45-125FML

Fish Tape				
Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
FTSP45-75FML	Southwire SIMpull fish tape, 75ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	2.77 lb	
FTSP45-125FML	Southwire SIMpull fish tape, 125ft length, spiral extruded polymer, swiveling flexible metal leader, 580lb tensile strength.	1	3.35 lb	


Southwire™

TOOLS & EQUIPMENT

Misc Sets



Part No. HEX-8

Features

- Precision-made hex keys reduce slipping and stripping
- Set stores easily in metal case to reduce lost keys and damage.
- Strong durable body doubles as a handle
- Set includes 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", and 9/64"

Miscellaneous Sets

Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
HEX-8	Southwire hex driver set, 8 pieces, imperial.	8	0.75 lb	



Part No. 60010S

Features

- UL listed CAT IV 600V, CAT III 1000V Test Leads
- 39in test leads
- 1000V AC/DC (Max)
- 10 Amp Current (Max)
- Includes removable CAT III 600V Alligator Clips

Miscellaneous Sets

Part Number	Description	Pcs/Pkg	Weight (lbs)	Price
60010S	Southwire test lead set, CAT IV 600V/CAT III 1000V, 48in length. Alligator clip adapters included.	1	0.31 lb	


Southwire™

TOOLS & EQUIPMENT

Tool Accessories



Part No. BAGESP

Electrician's Shoulder Pouch

- Lightweight, durable bag that can be carried, slung over your shoulder or attached to a belt.
- 11 inside and 5 outside for a total of 16 tool storage pockets
- Side pocket with Flip Lid™ Spill Guard provides secure easy access to small parts such as wire nuts or screws
- 3 different carrying options: Padded shoulder strap, tunnel loop for belt access, or padded handle
- Constructed from 2400d ballistic weave for durability
- Electrical Tape Strap
- Adjustable Hammer/Flashlight Loop
- Two rubber feet keep it stable when setting on a workbench or out on the factory floor.



Part No. HBKND2

EDGEFORCE™ Hawk Bill Knife

- Premium D2 Stainless Steel Holds an edge
- Curved blade for pull cuts and splicing
- Rugged metal handle
- Stonewash black oxide coated blade
- Liner lock keeps blade secure
- Comfort grip for maximum hold and comfort
- Reversible belt clip



Part No. UTILQO

Folding Utility Knife

- Quick open button for easy one hand operation
- Durable metal body with comfort grip for secure hold
- Easy blade replacement
- Rugged metal handle
- Comfort grip for maximum hold and comfort
- Quick open/close button
- Lanyard hole
- Belt clip

Accessories Selection			
Part Number	Description	Weight (lbs)	Price
BAGESP	Southwire tool bag, 2400 denier ballistic weave nylon, 16 compartments.	2 lb	
UTILQO	Southwire EDGEFORCE folding knife, common replaceable 2 point utility blade, utility blade length, 6.01in overall length, metal body with comfort grip and pocket clip.	0.4 lb	
HBKND2	Southwire EDGEFORCE folding knife, hawkbill, 2.60in blade length, 7.24in overall length, metal body with comfort grip and pocket clip.	0.3 lb	