



Wera Bit Drivers, Bits, & Adapters

Tool-Check Tool Sets

Wera Tool-Check systems deliver very compact tool organization for manual and machine use. Green locking elements secure tools during transport, preventing movement and loss. The 1/4" bit ratchet features drop-forged solid steel construction with fine 60-tooth mechanism for a 6° return angle, enabling precise work in confined spaces. Ergonomically shaped ratchet head with easy clockwise/counterclockwise switching ensures comfortable operation. Zyklop sockets include ball stop grooves and rear-end knurling for secure retention and manual screwdriving control. Take it easy tool finder system uses color coding by size and profile for quick tool identification. BiTorsion bits feature integrated torsion zones that prevent premature breakage during high-torque applications. The 870/1 adapter enables 1/4" socket compatibility for all Tool-Check systems. Matte chrome-plated chrome-vanadium construction provides corrosion resistance and durability.

Features


- Green locking elements secure tools during transport and prevent loss
- Drop-forged 60-tooth bit ratchet with 6° return angle for precise work
- Ergonomically shaped ratchet head with easy clockwise/counterclockwise switching
- BiTorsion bits feature torsion zones that prevent premature breakage
- Take it easy tool finder color coding for quick tool identification
- Zyklop sockets with ball stop grooves for secure retention
- Matte chrome-plated chrome-vanadium construction for corrosion resistance
- Includes 870/1 adapter for 1/4" socket compatibility
- Super-compact storage maximizes space efficiency
- Available in metric and imperial configurations



Lockable Storage



Socket and Driver Bit Set



Rapidaptor Quick-Release System



05049055001



SWITCH



FINE TOOTH



FULL STEEL



TAKE IT EASY TOOL FINDER



TAKE IT EASY TOOL FINDER



BITORSION



RAPIDAPTOR TECHNOLOGY



KRAFTFORM ERGONOMICS



ANTI ROLL-OFF




TAKE IT EASY TOOL FINDER



BITORSION



LIMITED LIFETIME WARRANTY



Take-It-Easy Tool Finder



Great for Confined Spaces



Wera Bit Drivers, Bits, & Adapters



Tool-Check PLUS Socket and Driver Bit Sets

05049055001

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 87mm
	Zyklop mini bit ratchet	1/4in x 78mm
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Slotted bit, 25mm long	1.0 x 5.5mm
	Hex-Plus bit, 25mm long	3mm, 4mm, 5mm, 6mm, 8mm
	6-point socket	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm
Description	Price	
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.		

Tool-Check PLUS Socket and Driver Bit Sets

05049060001

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 78mm
	Zyklop mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Slotted bit, 25mm long	1.0 x 5.5mm
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Square bit, 25mm long	#1, (3) #2, #3
	Hex-Plus bit, 25mm long	3/32in, 1/8in, 5/32in, 3/16in, 1/4in
Description	Price	
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, imperial, compact Tool-Check storage system.		
	6-point socket	3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters



Tool-Check PLUS Socket and Driver Bit Sets

05056490001

Product Image		Type	Bit Size
		Bitholding screwdriver	1/4in x 78mm
		Zyklop mini bit ratchet	1/4in
		Rapidaptor bit holder	1/4in x 50mm
		Socket adaptor	1/4in x 25mm
		Phillips bit, 25mm long	(2) #1, (3) #2, #3
		Pozidriv bit, 25mm long	#1, (3) #2, #3
		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
		Slotted bit, 25mm long	1.0 x 5.5mm
		Hex-Plus bit, 25mm long	3.0, 4.0, 5.0, 6.0, 8.0mm
Description	Price	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm

Tool-Check Socket and Driver Bit Sets

05056491001

Product Image		Type	Bit Size
		Bitholding screwdriver	1/4in x 78mm
		Zyklop mini bit ratchet	1/4in
		Rapidaptor bit holder	1/4in x 50mm
		Socket adaptor	1/4in x 25mm
		Phillips bit, 25mm long	(2) #1, (3) #2, #3
		Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
		Slotted bit, 25mm long	1.0 x 5.5mm
		Hex-Plus bit, 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
		6-point socket	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in
Description	Price		

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters



Tool-Check Socket and Driver Bit Sets

05049050001

Product Image		Type	Bit Size
		Zyklop Mini bit ratchet	1/4in
		Rapidaptor bit holder	1/4in x 50mm
		Socket adaptor	1/4in x 25mm
		Phillips bit, 25mm long	(2) #1, (3) #2, #3
		Slotted bit 25mm long	1.0 x 5.5mm
		Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
		Pozidriv bit, 25mm long	#1, (3) #2, #3
Description	Price	Hex-Plus bit 25mm long	3mm, 4mm, 5mm, 6mm, 8mm
Wera Tool-Check standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, external hex, internal hex, slotted and square, 38 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.		6-point socket	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm

Tool-Check Socket and Driver Bit Sets

05073220055

Product Image		Type	Bit Size	
		Zyklop Mini bit ratchet	1/4in	
		Rapidaptor bit holder	1/4in x 50mm	
		Socket adaptor	1/4in x 25mm	
			Slotted bit 25mm long	1.0 x 5.5mm
			Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm
			Phillips bit, 25mm long	(2) P#1, (3) #2, #3
			Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
			Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
			Pozidriv bit 25mm long	#1, (3) #2, #3
			6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm
Description	Price			
Wera Tool-Check standard driver bit and socket set, ratcheting, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.				

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters



Bit-Check Socket and Driver Bit Sets

TW-DB-SET-28R

Product Image		Type	Bit Size
		Zyklop Mini bit ratchet	1/4in
		Rapidaptor bit holder	1/4in x 50mm
		Socket adaptor	1/4in x 25mm
		 Phillips bit, 25mm long	(2) PH1, (3) PH2, PH3
		 Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
		 Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
		 Slotted bit 25mm long	1.0 x 5.5mm
Description	Price	 Hex-Plus bit 25mm long	3/32, 1/8, 5/32, 3/16, 1/4in
Wera Bit-Check standard driver bit set, ratcheting, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.		 Square bit 25mm long	#1, (3) #2, #3

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.