



Signal Devices

Visual 57/58mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon model
- Base mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included on incandescent models
- 2-year warranty



Visual 57/58mm Base Mount Beacons 200, 201 and 202 Series Selection Chart													
Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
35.5 mm Base Mount													
20010000		Red	PDF	Incandescent Permanent Light 57mm	12–240 V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		50 [1.76]		
20020000		Green	PDF										
20030000		Yellow	PDF										
20040000		Clear	PDF										
20050000		Blue	PDF										
20110067		Red	PDF	LED Permanent Light 58mm	115 VAC	< 25 mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C]	up to 100,000h	Polycarbonate cap Polyamide base	66 [2.33]	Up to 2.5 mm ² Screwless CAGE CLAMP® - technology (8–14 AWG)	cULus file E164155, CE, RoHS
20120067		Green	PDF										
20130067		Yellow	PDF										
20140067		Clear	PDF										
20150067		Blue	PDF										
20110075		Red	PDF	Xenon Flashing Light (0.75 Hz flash frequency, 1W flash energy) 58mm	24 VAC/VDC	< 45 mA	-	IP65	4,000,000 flashes		82 [2.89]		
20120075		Green	PDF										
20130075		Yellow	PDF										
20140075		Clear	PDF										
20150075		Blue	PDF										
20210055		Red	PDF		24 VDC	< 100 mA	-						
20220055		Green	PDF										
20230055		Yellow	PDF										
20240055		Clear	PDF										
20250055		Blue	PDF										
20210067		Red	PDF		115 VAC	< 20 mA	-						
20220067		Green	PDF										
20230067		Yellow	PDF										
20240067		Clear	PDF										
20250067		Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
95584035		Bulb for Incandescent Light BA15d Bayonet Socket	5W	24 VDC	up to 5,000h
95584038				230 VAC	
95584057				115 VAC	



Signal Devices

Beacon Accessories

WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201		PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202		PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503		PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ABS blend	8.5 g [0.3 oz]
97581507		PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508		PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522		PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001		PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901		PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902		PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8–17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603		PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605		PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ABS blend	62g [2.19 oz]

