



Signal Devices

Visual 57/58 mm Base Mount Beacons (Tall Lens)

Features

- Beacon with tall lens
- Base mount installation
- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- 2-year warranty



Visual 57/58mm Base Mount Beacons 210, 211, and 212 Series Selection Chart

| Part Number | Price | Color | Drawing Link | Description | Voltage | Current | Starting Current | Operating Temp /Protection | Life Duration | Housing Material | Weight g [oz] | Connection | Agency Approvals |
|-----------------------------|-------|--------|---------------------|--|---|---|------------------|--|-------------------|-------------------------------------|---------------|--|------------------------------|
| 35.5 mm (Base Mount) | | | | | | | | | | | | | |
| 21010000 | | Red | PDF | Incandescent Permanent Light 57mm | 12-240V AC/DC max Depends on bulb selection. (Bulb sold separately) | Depends on bulb selection. (Bulb sold separately) | - | | up to 5,000h | | 55 [1.94] | | |
| 21020000 | | Green | PDF | | | | | | | | | | |
| 21030000 | | Yellow | PDF | | | | | | | | | | |
| 21040000 | | Clear | PDF | | | | | | | | | | |
| 21050000 | | Blue | PDF | | | | | | | | | | |
| 21110067 | | Red | PDF | LED Permanent Light 58mm | 115VAC | < 25 mA | ≤ 0.5 A | -4 to 122°F [-20 to 50°C] IP65 when mounted | up to 100,000h | Polycarbonate cap Polyamide base | 72 [2.53] | 2.5 mm ² Screwless CAGE CLAMP® - technology (18-14 AWG) | cULus file E164155, CE, RoHS |
| 21120067 | | Green | PDF | | | | | | | | | | |
| 21130067 | | Yellow | PDF | | | | | | | | | | |
| 21140067 | | Clear | PDF | | | | | | | | | | |
| 21150067 | | Blue | PDF | | | | | | | | | | |
| 21110075 | | Red | PDF | | | | | | | | | | |
| 21120075 | | Green | PDF | | | | | | | | | | |
| 21130075 | | Yellow | PDF | | | | | | | | | | |
| 21140075 | | Clear | PDF | | | | | | | | | | |
| 21150075 | | Blue | PDF | | | | | | | | | | |
| 21210055 | | Red | PDF | Xenon Flashing Light (0.75 Hz flash frequency, 1W flash energy) 58mm | 24VDC | < 100 mA | - | | 4,000,000 flashes | | 88 [3.10] | | |
| 21220055 | | Green | PDF | | | | | | | | | | |
| 21230055 | | Yellow | PDF | | | | | | | | | | |
| 21240055 | | Clear | PDF | | | | | | | | | | |
| 21250055 | | Blue | PDF | | | | | | | | | | |
| 21210067 | | Red | PDF | | 115VAC | < 20 mA | - | | | | | | |
| 21220067 | | Green | PDF | | | | | | | | | | |
| 21230067 | | Yellow | PDF | | | | | | | | | | |
| 21240067 | | Clear | PDF | | | | | | | | | | |
| 21250067 | | Blue | PDF | | | | | | | | | | |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



| Bulbs for Incandescent Permanent Visual Element | | | | | |
|---|-------|--|---------|------------|---------------|
| Part Number | Price | Description | Wattage | Voltage | Life Duration |
| 95501535 | | Bulb for Incandescent Light BA15d Bayonet Socket | 7W | 24 VAC/DVC | up to 5,000h |
| 95501537 | | | | 115 VAC | |
| 95501538 | | | | 230 VAC | |



Signal Devices

Beacon Accessories

| WERMA Beacons Accessories | | | | | | |
|--|-------|---------------------|---|------------------------------|---|---------------------|
| Part Number | Price | Drawing Link | Description | Operating Temp. | Material | Weight |
| Installation Beacon Accessories | | | | | | |
| 97581201 | | PDF | WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation. | -4 to 122°F [-20 to 50°C] | Polyamide / Fiberglass | 1.13 g [0.04 oz] |
| 97581202 | | PDF | WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation. | | Polyamide / Fiberglass with rubber seal | 2.83 g [0.1 oz] |
| 97581503 | | PDF | WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation. | | Polycarbonate/ABS blend | 8.5 g [0.3 oz] |
| 97581507 | | PDF | WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation. | | | 14.17 g [0.5 oz] |
| 97581508 | | PDF | WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation. | | | 17g [0.6 oz] |
| 97581522 | | PDF | WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation. | | 304 Stainless steel | 0.57 g [0.02 oz] |
| Freestanding Beacon Accessories | | | | | | |
| 96000001 | | PDF | WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included. | -4 to 122°F [-20 to 50°C] | Polyamide | 57g [2.01 oz] |
| 97520901 | | PDF | WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons. | | Polyamide | 0.1 lbs [1.6 oz] |
| 97520902 | | PDF | WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8–17mm diameter cable, IP68. | | Nylon | 0.1 lbs [1.6 oz] |
| 97582603 | | PDF | WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons. | | Wire D 3mm, chromed | 140g [4.93 oz] |
| 97582605 | | PDF | WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons. | | Polycarbonate/ABS blend | 62g [2.19 oz] |

