



Signal Devices

Visual 57/58mm Panel Mount Beacons

Features

- Available in permanent Incandescent or LED, and Xenon flashing models
- 360° visibility
- For use in 22.5 mm standard control panel holes
- Connection by 6.3mm x 0.8mm spades
- Finger-proof when used with insulated spades
- Changeable bulb for incandescent models not included
- Lock nut and rubber seal included
- 2-year warranty



Visual 57/58 mm Beacons 206, 207, 208 Series Selection Chart

Part Number	Price	Lamp Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
22.5 mm Panel Mount													
20610000		Red	PDF	Incandescent Permanent Light	max. 48V	Depends on bulb selection. (bulb sold separately)	-	-4 to 122°F [-20 to 50°C] IP65	Depends on bulb selection. (bulb sold separately)	Polycarbonate cap Polyamide fiberglass Black base	39 [1.38]	22.5 mm Panel Mount 6.3 mm spade connector	cULus file E164155, RoHS
20620000		Green	PDF										
20630000		Yellow	PDF										
20640000		Clear	PDF										
20650000		Blue	PDF										
20710075		Red	PDF	LED Permanent Light	24V AC/DC	< 45 mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap Polyamide fiberglass Black base	56 [1.98]	22.5 mm Panel Mount 6.3 mm spade connector	cULus file E164155, CE, RoHS
20720075		Green	PDF										
20730075		Yellow	PDF										
20740075		Clear	PDF										
20750075		Blue	PDF										
20710067		Red	PDF		115VAC	< 25 mA	-	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap Polyamide fiberglass Black base	56 [1.98]	6.3 mm spade connector	
20720067		Green	PDF										
20730067		Yellow	PDF										
20740067		Clear	PDF										
20750067		Blue	PDF										
20810055		Red	PDF	Xenon Flashing Light (0.75 Hz flash frequency)	24VDC	< 100 mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	4 x 106 flashes	Polycarbonate cap Polyamide fiberglass Black base	74 [2.61]	22.5 mm Panel Mount 6.3 mm spade connector	cULus file E164155, CE, RoHS
20820055		Green	PDF										
20830055		Yellow	PDF										
20840055		Clear	PDF										
20850055		Blue	PDF		115VAC	< 25 mA	-	-4 to 122°F [-20 to 50°C] IP65	4 x 106 flashes	Polycarbonate cap Polyamide fiberglass Black base	74 [2.61]		
20810067		Red	PDF										
20820067		Green	PDF										
20830067		Yellow	PDF										
20840067		Clear	PDF										
20850067		Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Bulbs for Incandescent Permanent Visual Element

Part Number	Price	Description	Wattage	Voltage	Life Duration
95584035		Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h