



Signal Devices

Visual 57/58 mm Bracket Mount Beacons (Tall Lens)

Features

- Beacon with tall lens
- Bracket mount installation
- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- 2-year warranty



Visual 57/58mm Bracket Mount Beacons (Tall Lens) 213, 214, and 215 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
25.8 mm (Bracket Mount)													
21310000		Red	PDF	Incandescent Permanent Light 57mm	12–240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		61 [2.15]		
21320000		Green	PDF										
21330000		Yellow	PDF										
21340000		Clear	PDF										
21350000		Blue	PDF										
21410067		Red	PDF	LED Permanent Light 58mm	115VAC	< 25 mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65 when mounted	up to 100,000h	Polycarbonate cap Polyamide base	78 [2.75]	2.5 mm ² Screwless CAGE CLAMP® - technology (18–14 AWG) Cable gland: m12 x1.5 Cable diameter: 3–6 mm	cULus file E164155, CE, RoHS
21420067		Green	PDF										
21430067		Yellow	PDF										
21440067		Clear	PDF										
21450067		Blue	PDF										
21410075		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100 mA	-		4,000,000 flashes		94 [3.32]		
21420075		Green	PDF										
21430075		Yellow	PDF										
21440075		Clear	PDF										
21450075		Blue	PDF										
21510055		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm	115VAC	< 20 mA	-						
21520055		Green	PDF										
21530055		Yellow	PDF										
21540055		Clear	PDF										
21550055		Blue	PDF										
21510067		Red	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm	115VAC	< 20 mA	-						
21520067		Green	PDF										
21530067		Yellow	PDF										
21540067		Clear	PDF										
21550067		Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
95501535		Bulb for Incandescent Light BA15d Bayonet Socket	7W	24 VAC/VDC	up to 5,000h
95501537				115 VAC	
95501538				230 VAC	



Signal Devices

Beacon Accessories



WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201		PDF	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202		PDF	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503		PDF	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507		PDF	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
97581508		PDF	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
97581522		PDF	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001		PDF	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901		PDF	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
97520902		PDF	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8–17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
97582603		PDF	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
97582605		PDF	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ ABS blend	62g [2.19 oz]

