



# Signal Devices

## Visual 57/58 mm Tube Mount Beacons (Tall Lens)

### Features

- Beacon with tall lens
- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- Tube mount installation 57 and 58 mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- Various mounting accessories available
- 2-year warranty



### Visual 57/58 mm Tube Mount Beacons (Tall Lens) 219 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
<b>M25x1.5 (Tube Mount)</b>													
<a href="#">21910000</a>		Red	<a href="#">PDF</a>	Incandescent Permanent Light 57mm	12-240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		67 [2.37]		
<a href="#">21920000</a>		Green	<a href="#">PDF</a>										
<a href="#">21930000</a>		Yellow	<a href="#">PDF</a>										
<a href="#">21940000</a>		Clear	<a href="#">PDF</a>										
<a href="#">21950000</a>		Blue	<a href="#">PDF</a>										
<a href="#">21911067</a>		Red	<a href="#">PDF</a>	LED Permanent Light 58mm	115VAC	< 25 mA	≤ 0.5A	-4 to 122°F [-20 to 50°C] IP65 when mounted	up to 100,000h	Polycarbonate cap Polyamide base	84 [2.96]		Max. 2.5 mm <sup>2</sup> Screwless CAGE CLAMP® - technology (18-14 AWG)  cULus file E164155, CE, RoHS
<a href="#">21921067</a>		Green	<a href="#">PDF</a>										
<a href="#">21931067</a>		Yellow	<a href="#">PDF</a>										
<a href="#">21941067</a>		Clear	<a href="#">PDF</a>										
<a href="#">21951067</a>		Blue	<a href="#">PDF</a>										
<a href="#">21911075</a>		Red	<a href="#">PDF</a>		24V AC/DC	< 45 mA							
<a href="#">21921075</a>		Green	<a href="#">PDF</a>										
<a href="#">21931075</a>		Yellow	<a href="#">PDF</a>										
<a href="#">21941075</a>		Clear	<a href="#">PDF</a>										
<a href="#">21951075</a>		Blue	<a href="#">PDF</a>										
<a href="#">21912055</a>		Red	<a href="#">PDF</a>	Xenon Flashing Light (1Hz flash frequency, 1W flash energy)  58mm	24VDC	< 100 mA	-		4,000,000 flashes		100 [3.52]		
<a href="#">21932055</a>		Yellow	<a href="#">PDF</a>										
<a href="#">21942055</a>		Clear	<a href="#">PDF</a>										
<a href="#">21952055</a>		Blue	<a href="#">PDF</a>		115VAC	< 20 mA							
<a href="#">21912067</a>		Red	<a href="#">PDF</a>										
<a href="#">21932067</a>		Yellow	<a href="#">PDF</a>										
<a href="#">21942067</a>		Clear	<a href="#">PDF</a>										
<a href="#">21952067</a>		Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

### Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95501535</a>		Bulb for Incandescent Light BA15d Bayonet Socket	7W	24 VAC/DC	up to 5,000h
<a href="#">95501537</a>				115 VAC	
<a href="#">95501538</a>				230 VAC	



# Signal Devices

## Beacon Accessories

WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
<b>Installation Beacon Accessories</b>						
<a href="#">97581201</a>		<a href="#">PDF</a>	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>		<a href="#">PDF</a>	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>		<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>		<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
<a href="#">97581508</a>		<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
<a href="#">97581522</a>		<a href="#">PDF</a>	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
<b>Freestanding Beacon Accessories</b>						
<a href="#">96000001</a>		<a href="#">PDF</a>	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>		<a href="#">PDF</a>	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>		<a href="#">PDF</a>	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8–17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>		<a href="#">PDF</a>	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>		<a href="#">PDF</a>	WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ABS blend	62g [2.19 oz]

