


# Productivity Accessories

## Removable Terminal Blocks

[P1-10RTB](#) or [P1-10RTB-1](#) is compatible with most P1000 I/O modules.



Removable Terminal Block [P1-10RTB](#)



Removable Terminal Block [P1-10RTB-1](#)

Removable Terminal Block Specifications		
Part Number	<a href="#">P1-10RTB</a>	<a href="#">P1-10RTB-1</a>
Price	\$7.25	\$7.25
Use With	Productivity1000 I/O modules	
Number of Positions	10 Screw terminals	10 Spring Clamp terminals
Wire Range	30–16 AWG (0.051–1.31 mm <sup>2</sup> ) Solid/Stranded Conductor 3/64 in. (1.2 mm) insulation max. 1/4 in. (6–7 mm) Strip length	28–16 AWG (0.081–1.31 mm <sup>2</sup> ) Solid/Stranded Conductor 3/64 in. (1.2 mm) insulation max. 19/64 in. (7–8 mm) Strip length
Conductors	USE COPPER CONDUCTORS, 75°C or equivalent.	
Screw Driver	0.1 inch (2.5 mm) maximum*	
Screw Size	M2	N/A
Screw Torque	2.5 lb·in (0.28 N·m)	N/A


\* Recommended screw driver: P/N TW-SD-MSL-1.

[P2-RTB](#) or [P2-RTB-1](#) terminal blocks are compatible with most P2000 I/O modules and with some P1000 I/O modules.

**Note:** P2-RTB supplied with Thermocouple and RTD modules.



Removable Terminal Block [P2-RTB](#)



Removable Terminal Block [P2-RTB-1](#)

Removable Terminal Block Specifications		
Part Number	<a href="#">P2-RTB</a>	<a href="#">P2-RTB-1</a>
Price	\$9.75	\$9.75
Use With:	Productivity1000 and Productivity2000 I/O modules	
Number of positions	18 screw terminals	18 push release terminals
Wire Range	30–16 AWG (0.051–1.31 mm <sup>2</sup> ) Solid/stranded conductor 3/64 in (1.2 mm) insulation max. 1/4 in (6–7 mm) strip length	28–16 AWG (0.081–1.31 mm <sup>2</sup> ) Solid/stranded conductor 3/64 in (1.2 mm) insulation max. 19/64 in (7–8 mm) strip length
Conductors	USE COPPER CONDUCTORS, 75°C or equivalent.	
Screw Driver Width	0.1 in. (2.5 mm) maximum	NA
Screw Size	M2	N/A
Screw Torque	2.5 lb·in (0.28 N·m)	N/A

\* Recommended screw driver: P/N TW-SD-MSL-1.