

# Starter Kit Boxes

## P1AM-100 Starter Kit Components

ProductivityOpen has two starter kits available - P1AM-START1 and P1AM-START2. Each kit allows you to get up and running in short order. Kit components are listed in the tables below.

### P1AM-START1 \$229.00



A convenient start to a project which will use primarily Arduino MKR Zero shields:

- P1AM-100 module - Arduino compatible CPU module
- P1AM-ETH shield - Ethernet communication module
- P1AM-GPIO shield - Header Pin Breakout module
- P1-4ADL2DAL-1 Productivity1000 analog expansion I/O module
- PSL-24-030 power supply – 24VDC (adjustable) output, 1.25 A, 30W, 120/240 VAC or 125–375 VDC nominal input, 1-phase
- P1-10RTB 10-pin terminal block
- P2-RTB 18-pin terminal block
- 3-pin terminal block
- AC power cord
- USB-CBL-AMICB6 USB programming cable

### P1AM-START2 \$159.00



A convenient start to a project which will use primarily Productivity1000 input and output modules:

- P1AM-100 module - Arduino compatible CPU module
- P1-01AC power supply
- P1-08TRS Productivity1000 relay output module
- P1-08SIM Productivity1000 simulator input module
- P2-RTB 18-pin removable terminal block
- 3-pin removable terminal block
- AC power cord
- USB-CBL-AMICB6 USB programming cable