

## Accessories, continued

NOTE: These parts available for sale to North American locations only

### PHOX System Motor Encoder Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#">APCV-EN03ES1-AD</a>	\$107.00	N	3m [9.8 ft]	24AWG	<a href="#">PDF</a>	All PHOX APMC motors
<a href="#">APCV-EN05ES1-AD</a>	\$114.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EN10ES1-AD</a>	\$127.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EN20ES1-AD</a>	\$159.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EF03ES1-AD</a>	\$117.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EF05ES1-AD</a>	\$127.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EF10ES1-AD</a>	\$159.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-EF20ES1-AD</a>	\$221.00		20m [65.6 ft]		<a href="#">PDF</a>	



APCV-EN series encoder cable

### PHOX System Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#">APCV-PN03LS-AD</a>	\$48.00	N	3m [9.8 ft]	24AWG	<a href="#">PDF</a>	All PHOX APMC motors
<a href="#">APCV-PN05LS-AD</a>	\$53.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PN10LS-AD</a>	\$67.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PN20LS-AD</a>	\$94.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PF03LS-AD</a>	\$56.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PF05LS-AD</a>	\$67.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PF10LS-AD</a>	\$95.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-PF20LS-AD</a>	\$147.00		20m [65.6 ft]		<a href="#">PDF</a>	



APCV-PN series power cable

### PHOX System Motor Brake Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#">APCV-BN03QS-AD</a>	\$48.00	N	3m [9.8 ft]	24AWG	<a href="#">PDF</a>	All PHOX APMC motors
<a href="#">APCV-BN05QS-AD</a>	\$52.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BN10QS-AD</a>	\$57.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BN20QS-AD</a>	\$72.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BF03QS-AD</a>	\$53.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BF05QS-AD</a>	\$58.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BF10QS-AD</a>	\$73.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCV-BF20QS-AD</a>	\$102.00		20m [65.6 ft]		<a href="#">PDF</a>	



APCV-BN series brake cable

Note: Each brake cable consists of 4 wires: 24VDC and Common (input to the drive), and BRK+ and BRK- output to the motor brake.